

USP10978 Thermistor Probe




Description

Littelfuse offers Brass probe assemblies suitable for a wide range of temperature sensing applications. If the dimensions and electrical characteristics on this product won't work for your requirements, please contact us for further assistance.

Features

- Tight Tolerance
- 105°C Max Operating Temperature
- ¼"-18 NPT Thread
- PVC Insulated Lead Wire


Dimensions



Dimensions in inches.

A	B	C	D
24.0" ± 1.50"	0.880" ± 0.015"	0.650" ± 0.050"	0.250" ± 0.005"
E	F	G	H
¼" - 18 NPT Thread (RHT)	0.250" ± 0.020"	Strip: 0.250" ± 0.070"	0.562" ± 0.035" Hex

Part Numbering System



Note: Not all combinations of Part Number codes are available. Contact Littelfuse for details.

Specifications

Part Number	Resistance Ohms @ 25°C	Resistance Tol. ± % @ 25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP10978	10000	1	J	-4.4	3892	-55 to +105

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[USP10978](#)