




Thyristor/Diode Modules M## 320

Absolute Maximum Ratings

V_{RRM} V_{DRM} [V]	 MCC	 MCD	 MDC
3000	320-30io2	320-30io2	320-30io2
3200	320-32io2	320-32io2	320-32io2
3400	320-34io2	320-34io2	320-34io2
3600	320-36io2	320-36io2	320-36io2

	VOLTAGE RATINGS	MAXIMUM LIMITS	UNITS
V_{DRM}	Repetitive peak off-state voltage ¹⁾	3000 - 3600	V
V_{DSM}	Non-repetitive peak off-state voltage ¹⁾	3100 - 3700	V
V_{RRM}	Repetitive peak reverse voltage ¹⁾	3000 - 3600	V
V_{RSM}	Non-repetitive peak reverse voltage ¹⁾	3100 - 3700	V

	OTHER RATINGS	MAXIMUM LIMITS	UNITS
$I_{T(AV)M}$	Maximum average on-state current, $T_C = 85^\circ\text{C}$ ²⁾	327	A
$I_{T(AV)M}$	Maximum average on-state current, $T_C = 100^\circ\text{C}$ ²⁾	229	A
$I_{T(RMS)M}$	Nominal RMS on-state current, $T_C = 55^\circ\text{C}$ ²⁾	765	A
$I_{T(d.c.)}$	D.C. on-state current, $T_C = 55^\circ\text{C}$	624	A
I_{TSM}	Peak non-repetitive surge $t_p = 10$ ms, $V_{RM} = 60\%V_{RRM}$ ³⁾	5.0	kA
I_{TSM2}	Peak non-repetitive surge $t_p = 10$ ms, $V_{RM} \leq 10\text{V}$ ³⁾	5.5	kA
I^2t	I^2t capacity for fusing $t_p = 10$ ms, $V_{RM} = 60\%V_{RRM}$ ³⁾	125×10^3	A^2s
I^2t	I^2t capacity for fusing $t_p = 10$ ms, $V_{RM} \leq 10\text{V}$ ³⁾	150×10^3	A^2s
$(di/dt)_{cr}$	Critical rate of rise of on-state current (non-repetitive) ⁴⁾	400	$\text{A}/\mu\text{s}$
V_{RGM}	Peak reverse gate voltage	5	V
$P_{G(AV)}$	Mean forward gate power	4	W
V_{ISOL}	Isolation Voltage ⁵⁾	3000	V
V_{ISOL}	Isolation Voltage ⁶⁾	3600	V
$T_{vj\ op}$	Operating temperature range	-40 to +125	$^\circ\text{C}$
T_{stg}	Storage temperature range	-40 to +125	$^\circ\text{C}$

Notes:

- De-rating factor of 0.13% per $^\circ\text{C}$ is applicable for T_{vj} below 25°C .
- Single phase; 50 Hz, 180° half-sinewave.
- Half-sinewave, 125°C T_{vj} initial.
- $V_D = 67\% V_{DRM}$, $I_{FG} = 2$ A, $t_r \leq 0.5\mu\text{s}$, $T_C = 125^\circ\text{C}$.
- AC RMS voltage, 50 Hz, 1 minute test
- AC RMS voltage, 50 Hz, 1 second test


Characteristics

	PARAMETER	MIN.	TYP.	MAX.	TEST CONDITIONS ¹⁾	UNITS
V_{TM}	Maximum peak on-state voltage	-	-	2.20	$I_{TM} = 785 \text{ A}$, $T_{vj} = 25^\circ\text{C}$	V
V_{T0}	Threshold voltage	-	-	1.15		V
r_T	Slope resistance	-	-	0.80		m Ω
$(dv/dt)_c$	Critical rate of rise of off-state voltage	1000	-	-	$V_D = 67\% V_{DRM}$, linear ramp, Gate o/c	V/ μs
I_{DRM}	Peak off-state current	-	-	200	Rated V_{DRM}	mA
I_{RRM}	Peak reverse current	-	-	200	Rated V_{RRM}	mA
V_{GT}	Gate trigger voltage	-	-	2.50	$T_{vj} = 25^\circ\text{C}$, $V_D = 12 \text{ V}$, $I_T = 3 \text{ A}$	V
I_{GT}	Gate trigger current	-	-	250		mA
V_{GD}	Gate non-trigger voltage	0.35	-	-	67% V_{DRM}	V
I_{GD}	Gate non-trigger current	15	-	-	67% V_{DRM}	mA
I_L	Latching current	-	-	1000	$V_D = 12 \text{ V}$, $T_{vj} = 25^\circ\text{C}$	mA
I_H	Holding current	-	-	300	$V_D = 12 \text{ V}$, $T_{vj} = 25^\circ\text{C}$	mA
t_{gd}	Gate controlled turn-on delay time	-	-	3.0	$I_{FG} = 2 \text{ A}$, $di_g/dt = 1 \text{ A}/\mu\text{s}$, $V_D = 40\% V_{DRM}$, $I_{TM} = 320 \text{ A}$, $di/dt = 10 \text{ A}/\mu\text{s}$, $T_{vj} = 25^\circ\text{C}$	μs
t_q	Turn-off time	-	-	320	$I_{TM} = 320 \text{ A}$, $di/dt = 10 \text{ A}/\mu\text{s}$, $V_R = 100 \text{ V}$, $V_{DR} = 67\% V_{DRM}$, $dv_{DR}/dt = 50 \text{ V}/\mu\text{s}$	μs
R_{thJC}	Thermal resistance, junction to case	-	-	0.0650	Per arm	K/W
				0.0325	Whole Module	K/W
R_{thCH}	Thermal resistance, case to heatsink	-	-	0.0200	Per arm	K/W
				0.0100	Whole Module	K/W
F_1	Mounting force (to heatsink)	5.1	-	6.9	²⁾	Nm
F_2	Mounting force (to terminals)	10.8	-	13.2		Nm
W_t	Weight	-	1.5	-		kg

Notes:

- 1) Unless otherwise indicated $T_{vj}=125^\circ\text{C}$.
- 2) Screws must be lubricated.

Outline Drawing & Ordering Information





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[MCD320-30io2](#) [MCD320-36io2](#) [MDC320-30io2](#) [MDC320-36io2](#)