


HRDI SERIES

Interval Timer



Wiring Diagram



Ordering Information

| MODEL | INPUT VOLTAGE | ADJUSTMENT | TIME DELAY |
|----------|---------------|------------|------------|
| HRDI117S | 12VDC | Fixed | 7s |
| HRDI421 | 120VAC | Onboard | 1 - 100s |
| HRDI422 | 120VAC | Onboard | 10 - 1000s |

If you don't find the part you need, call us for a custom product 800-843-8848

Description

The HRDI Series combines an electromechanical relay output with microcontroller timing circuitry. It offers 12 to 230V operation in five ranges and factory fixed, external, or onboard adjustable time delays with a repeat accuracy of $\pm 0.5\%$. The output contact rating allows for direct operation of heavy loads, such as compressors, pumps, blower motors, heaters, etc. This series is ideal for OEM applications where cost is a factor.

Operation (Interval)

Upon application of input voltage, the time delay begins. The output relay is energized during the time delay. At the end of the time delay, the output de-energizes and remains de-energized until input voltage is removed.

Reset: Removing input voltage resets the time delay and the output.

Features & Benefits

| FEATURES | BENEFITS |
|--|---|
| Microcontroller based | Repeat Accuracy $\pm 0.5\%$ |
| Compact, low cost design | Allows flexibility for OEM applications |
| Isolated, 30A, SPDT, NO output contacts | Allows direct operation of heavy loads: compressors, pumps, blower motors, heaters. |
| Encapsulated | Protects against shock, vibration, and humidity. |

Accessories



P1004-95, P1004-95-X Versa-Pot

Panel mountable, industrial potentiometer recommended for remote time delay adjustment.



P1023-6 Mounting bracket

The 90° orientation of mounting slots makes installation/removal of modules quick and easy.



P0700-7 Versa-Knob

Designed for 0.25 in. (6.35 mm) shaft of Versa-Pot. Semi-gloss industrial black finish.



P1015-13 (AWG 10/12), P1015-64 (AWG 14/16) Female Quick Connect

These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.



P1015-18 Quick Connect to Screw Adapter

Screw adapter terminal designed for use with all modules with 0.25 in. (6.35 mm) male quick connect terminals.



C103PM (AL) DIN Rail

35 mm aluminum DIN rail available in a 36 in. (91.4 cm) length.



P1023-20 DIN Rail Adapter


Allows module to be mounted on a 35 mm DIN type rail with two #10 screws.

Time Delay Relays

Dedicated - Interval

HRDI SERIES

External Resistance vs. Time Delay




This chart applies to externally adjustable part numbers.

The time delay is adjustable over the time delay range selected by varying the resistance across the R_T terminals; as the resistance increases the time delay increases.

When selecting an external R_T, add the tolerances of the timer and the R_T for the full time range adjustment.

Examples: 1 to 50 S adjustable time delay, select time delay range 1 and a 50 K ohm R_T. For 1 to 100 S use a 100 K ohm R_T.

Function Diagram



Specifications

Time Delay

Type

Range

Repeat Accuracy

Tolerance

(Factory Calibration)

Recycle Time

Time Delay vs Temp.

& Voltage

Input

Voltage

Tolerance

12VDC & 24VDC

24 to 230VAC

AC Line Frequency

Power Consumption

Output

Type

Form

Ratings

General Purpose 125/240VAC

Resistive 125/240VAC

28VDC

Motor Load 125VAC

240VAC

Life

Protection

Surge

Circuitry

Dielectric Breakdown

Insulation Resistance

Polarity

Mechanical

Mounting

Dimensions

Termination

Environmental

Operating/Storage

Temperature

Humidity

Weight

Microcontroller circuitry

0.1s - 100m in 5 adjustable ranges or fixed

±0.5 % or 20ms, whichever is greater

±1%, ±5%

≤ 150ms

±2%

12 or 24VDC; 24, 120, or 230VAC

-15% - 20%

-20% - 10%

50/60 Hz

AC ≤ 4VA; DC ≤ 2W

Electromechanical relay

SPDT, non-isolated

SPDT-NO

SPDT-NC

30A

15A

30A

15A

20A

10A

1 hp*

1/4 hp**

2 hp**

1 hp**

Mechanical - 1 x 10⁶;

Electrical - 1 x 10⁵, *3 x 10⁴, **6,000

IEEE C62.41-1991 Level A

Encapsulated

≥ 2000V RMS terminals to mounting surface

≥ 100 MΩ

DC units are reverse polarity protected

Surface mount with one #10 (M5 x 0.8) screw

H 76.7 mm (3"); **W** 51.3 mm (2");

D 38.1 mm (1.5")

0.25 in. (6.35 mm) male quick connect terminals

-40° to 60°C / -40° to 85°C

95% relative, non-condensing

≈ 3.9 oz (111 g)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[HRDI421](#) [HRDI117S](#) [HRDI422](#)