


UNCONTROLLED DOCUMENT



LED LAYOUT TABLE										
-AXXX	LED 1	LED 2	LED 3	LED 4	LED 5	LED 6	LED 7	LED 8	LED 9	LED 10
-A001	RED	-	-	-	-	-	-	-	-	-
-A002	GREEN	-	-	-	-	-	-	-	-	-
-A003	YELLOW	-	-	-	-	-	-	-	-	-
-A004	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED
-A005	RED	YELLOW	GREEN	-	-	-	-	-	-	-
-A006	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	RED
-A007	RED	RED	RED	RED	RED	RED	RED	RED	-	-
-A008	RED	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW	YELLOW
-A009	R/G	-	-	-	-	-	-	-	-	-
-AD10	GREEN	YELLOW	RED	-	-	-	-	-	-	-
-A011	GREEN	GREEN	YELLOW	RED	-	-	-	-	-	-
-AD12	GREEN	RED	-	-	-	-	-	-	-	-
-AD13	RED	GREEN	-	-	-	-	-	-	-	-
-A014	GREEN	GREEN	GREEN	GREEN	GREEN	GREEN	GREEN	RED	-	-
-AD15	UNASSIGNED									

\*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN.=+DECIMAL PRECISION  
-0.00 MAX.=+0.00  
-DECIMAL PRECISION

REV.  
E

PART NUMBER

SFX-LXH307M-AXXX

T-3mm (T-1) MATING RIGHT ANGLE FAULT INDICATOR,  
LOW CURRENT SLECTION LEDS, COLOR DIFFUSED LENS.

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT  
SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE.  
PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



290 E. HELEN ROAD  
PALATINE, IL 60067-6976  
PHONE: +1.847.359.2790  
US WEB: [www.lumex.com](http://www.lumex.com)  
TW WEB: [www.lumex.com.tw](http://www.lumex.com.tw)

DRAWN BY:

CHECKED BY:

APPROVED BY:

DATE: 8.15.96

JC

PAGE: 1 OF 1  
SCALE: N/A

PART NUMBER		REV.
SFX-LXH307M-AXXX		E
REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	E.C.N. #10287.	12.26.96
B	E.C.N. #10373.	8.12.97
C	E.C.N. #10420.	3.5.98
D	E.C.N. #10BRDR. & REDRAWN IN 3D.	3.23.01
E	E.C.N. #11148.	01.24.07

ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^{\circ}\text{C}$				$I_f=20\text{mA}$	
PARAMETER	RED	YELLOW	GREEN	UNITS	TEST COND
PEAK WAVELENGTH	700	585	565	nm	
FORWARD VOLTAGE (TYP.)	2.0	2.1	2.2	nm	
FORWARD VOLTAGE (MAX.)	2.5	2.5	2.6	V <sub>f</sub>	
REVERSE VOLTAGE (TYP.)	5.0	5.0	5.0	V <sub>r</sub>	$I_r=100\mu\text{A}$
AXIAL INTENSITY (TYP.)	6	30	30	mcd	$I_f=20\text{mA}$
AXIAL INTENSITY (MIN.)	1.0	1.0	1.0	mcd	$I_f=2\text{mA}$
VIEWING ANGLE	60	60	60	2x theta	

LED POSITION: PER POSITION IN LED LAYOUT TABLE

EPOXY LENS FINISH: DIFFUSED SAME AS EMITTED COLOR

PARAMETER	COLORS	MAX	UNITS
PEAK FORWARD CURRENT*		150	mA
STEADY CURRENT	(R/Y/G)	25/30/25	mA
POWER DISSIPATION	(R/Y/G)	120/105/105	mW
DERATE FROM 25°C		-1.6	mW/°C
OPERATING, STORAGE TEMP.		-40 TO +85	°C
SOLDERING TEMP.		+260	°C
2.0mm FROM BODY			3 SEC. MAX

\*  $t < 10 \mu s$

NOTES:

1. SSH-LXH307M, MONSANTO VYDYNE NYLON 6/6,  
BLACK HOLDER.
2. SSL-LX3054L SERIES LED, LOW CURRENT SELECTION IS  
BEING USED FOR IMPROVED BRIGHTNESS UNIFORMITY.
3. PACKAGE PARTS IN ANTI-STATIC TUBES.

UNCONTROLLED DOCUMENT

**E**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SFX-LXH307M-A014](#)