


8		7		6		5		4		3		2		1																																																								
W48M- X X X X XX																																																																						
F		<table><tr><th>SWITCH FUNCTION CODE</th><th>SWITCH FUNCTION DESCRIPTION</th></tr><tr><td>E</td><td>MECHANICAL,MOMENTARY,SOLDER TERMINAL</td></tr><tr><td>F</td><td>MECHANICAL,MAINTAINED,SOLDER TERMINAL</td></tr><tr><td>G</td><td>MECHANICAL,MOMENTARY, P.C. TERMINAL</td></tr><tr><td>H</td><td>MECHANICAL,MAINTAINED, P.C. TERMINAL</td></tr></table>		SWITCH FUNCTION CODE	SWITCH FUNCTION DESCRIPTION	E	MECHANICAL,MOMENTARY,SOLDER TERMINAL	F	MECHANICAL,MAINTAINED,SOLDER TERMINAL	G	MECHANICAL,MOMENTARY, P.C. TERMINAL	H	MECHANICAL,MAINTAINED, P.C. TERMINAL	<table><tr><th>HOUSING MATERIAL CODE</th><th>HOUSING DECSRIPTION</th></tr><tr><td>1</td><td>STAINLESS STEEL</td></tr><tr><td>2</td><td>ZINC ALLOY, CHROME PLATED</td></tr><tr><td>3</td><td>AL ALLOY, ANODIZED BLACK</td></tr></table>		HOUSING MATERIAL CODE	HOUSING DECSRIPTION	1	STAINLESS STEEL	2	ZINC ALLOY, CHROME PLATED	3	AL ALLOY, ANODIZED BLACK	<table><tr><th>ILLU. TYPE CODE</th><th>ILLUMINATION TYPE DESCRIPTION</th></tr><tr><td>1</td><td>CENTER SPOT ILLUMINATION</td></tr><tr><td>2</td><td>RING ILLUMINATION</td></tr><tr><td>3</td><td>POWER/STANDBY SYMBOL ILLUMINATION</td></tr></table>		ILLU. TYPE CODE	ILLUMINATION TYPE DESCRIPTION	1	CENTER SPOT ILLUMINATION	2	RING ILLUMINATION	3	POWER/STANDBY SYMBOL ILLUMINATION	<table><tr><th>LED COLOR CODE</th><th>LED COLOR</th></tr><tr><td>A</td><td>AMBER</td></tr><tr><td>R</td><td>RED</td></tr><tr><td>Y</td><td>YELLOW</td></tr><tr><td>B</td><td>BLUE</td></tr><tr><td>G</td><td>GREEN</td></tr><tr><td>W</td><td>WHITE</td></tr><tr><td>RB</td><td>RED/BLUE</td></tr><tr><td>RG</td><td>RED/GREEN</td></tr></table>		LED COLOR CODE	LED COLOR	A	AMBER	R	RED	Y	YELLOW	B	BLUE	G	GREEN	W	WHITE	RB	RED/BLUE	RG	RED/GREEN	<table><tr><th>LED INLET VOLTAGE CODE</th><th>LED INLET VOLTAGE</th></tr><tr><td>IF BLANK*</td><td>(SEE NOTE)</td></tr><tr><td>05</td><td>5V (SEE NOTE3)</td></tr></table>		LED INLET VOLTAGE CODE	LED INLET VOLTAGE	IF BLANK*	(SEE NOTE)	05	5V (SEE NOTE3)	F								
SWITCH FUNCTION CODE	SWITCH FUNCTION DESCRIPTION																																																																					
E	MECHANICAL,MOMENTARY,SOLDER TERMINAL																																																																					
F	MECHANICAL,MAINTAINED,SOLDER TERMINAL																																																																					
G	MECHANICAL,MOMENTARY, P.C. TERMINAL																																																																					
H	MECHANICAL,MAINTAINED, P.C. TERMINAL																																																																					
HOUSING MATERIAL CODE	HOUSING DECSRIPTION																																																																					
1	STAINLESS STEEL																																																																					
2	ZINC ALLOY, CHROME PLATED																																																																					
3	AL ALLOY, ANODIZED BLACK																																																																					
ILLU. TYPE CODE	ILLUMINATION TYPE DESCRIPTION																																																																					
1	CENTER SPOT ILLUMINATION																																																																					
2	RING ILLUMINATION																																																																					
3	POWER/STANDBY SYMBOL ILLUMINATION																																																																					
LED COLOR CODE	LED COLOR																																																																					
A	AMBER																																																																					
R	RED																																																																					
Y	YELLOW																																																																					
B	BLUE																																																																					
G	GREEN																																																																					
W	WHITE																																																																					
RB	RED/BLUE																																																																					
RG	RED/GREEN																																																																					
LED INLET VOLTAGE CODE	LED INLET VOLTAGE																																																																					
IF BLANK*	(SEE NOTE)																																																																					
05	5V (SEE NOTE3)																																																																					
E																E																																																						
D		MECHANICAL CHARACTERISTICS: SWITCH CIRCUITRY: SPST-NO-DB (CONTACT FORM X) SWITCH ACTION: MOMENTARY AND MAINTAINED (PER CHART) BUTTON TRAVEL: 2.3mm [.090] NOMINAL OPERATING FORCE: 306g [3N] NOMINAL CONTACT BOUNCE: 1ms NOMINAL PANEL THICKNESS: 0.5 - 4.5mm[.020 - .177] CONTACTS: GOLD PLATED NUT TORQUE FORCE: MAX11.5 kgf-cm [10 LB-in] ENVIROMENTAL SPECIFICATIONS: ACTUATOR INGRESS PROTECTION: IP67 OPERATING TEMPERATURE: NON-ILLUMINATION TYPE: -40°C to +85°C [-40°F to +185°F] ILLUMINATION TYPE: -40°C to +85°C [-40°F to +185°F]		<table><tr><th colspan="5">LED SPECIFICATION</th></tr><tr><th rowspan="2">LED CODE</th><th rowspan="2">LED SINGLE COLOR</th><th>Vf(VDC)</th><th rowspan="2">If (mA)</th><th rowspan="2">CIRCUITRY</th></tr><tr><th>TYP.</th></tr><tr><td>R</td><td>RED</td><td>2.0</td><td>20</td><td rowspan="6"></td></tr><tr><td>A</td><td>AMBER</td><td>2.0</td><td>20</td></tr><tr><td>Y</td><td>YELLOW</td><td>2.0</td><td>20</td></tr><tr><td>G</td><td>GREEN</td><td>3.0</td><td>20</td></tr><tr><td>B</td><td>BLUE</td><td>3.1</td><td>20</td></tr><tr><td>W</td><td>WHITE</td><td>3.3</td><td>20</td></tr><tr><th rowspan="2">LED CODE</th><th colspan="2">BICOLOR LED</th><th>Vf(VDC)</th><th rowspan="2">If (mA)</th><th rowspan="2">CIRCUITRY</th></tr><tr><th>COLOR1</th><th>COLOR2</th><th>TYP.</th></tr><tr><td>RB</td><td>RED</td><td>BLUE</td><td>2.0(RED) 3.3(BLUE)</td><td>20</td><td rowspan="3"></td></tr><tr><td>RG</td><td>RED</td><td>GREEN</td><td>2.0(RED) 3.4(GREEN)</td><td>20</td></tr><tr><td colspan="5">NOTE: Hand Soldering Temperature (4mmabove from Body) : 320°C for 3 seconds</td></tr></table>		LED SPECIFICATION					LED CODE	LED SINGLE COLOR	Vf(VDC)	If (mA)	CIRCUITRY	TYP.	R	RED	2.0	20		A	AMBER	2.0	20	Y	YELLOW	2.0	20	G	GREEN	3.0	20	B	BLUE	3.1	20	W	WHITE	3.3	20	LED CODE	BICOLOR LED		Vf(VDC)	If (mA)	CIRCUITRY	COLOR1	COLOR2	TYP.	RB	RED	BLUE	2.0(RED) 3.3(BLUE)	20		RG	RED	GREEN	2.0(RED) 3.4(GREEN)	20	NOTE: Hand Soldering Temperature (4mmabove from Body) : 320°C for 3 seconds					POWER ILLUMINATION SEALING WASHER T=0.8 (SUPPLIED IN BULK) SPECIAL HEX NUT HEX 22.1, M19*P1.0 T=2.2 (SUPPLIED IN BULK) RING ILLUMINATION		D	
LED SPECIFICATION																																																																						
LED CODE	LED SINGLE COLOR	Vf(VDC)	If (mA)	CIRCUITRY																																																																		
		TYP.																																																																				
R	RED	2.0	20																																																																			
A	AMBER	2.0	20																																																																			
Y	YELLOW	2.0	20																																																																			
G	GREEN	3.0	20																																																																			
B	BLUE	3.1	20																																																																			
W	WHITE	3.3	20																																																																			
LED CODE	BICOLOR LED		Vf(VDC)	If (mA)	CIRCUITRY																																																																	
	COLOR1	COLOR2	TYP.																																																																			
RB	RED	BLUE	2.0(RED) 3.3(BLUE)	20																																																																		
RG	RED	GREEN	2.0(RED) 3.4(GREEN)	20																																																																		
NOTE: Hand Soldering Temperature (4mmabove from Body) : 320°C for 3 seconds																																																																						
C		ELECTRICAL SPECIFICATIONS: CURRENT RATING: MOMENTARY: 250mA@12VDC, 100K cycles 150mA@28VDC, 150K cycles 100mA@48VDC, 100K cycles 10mA@12VDC, 1,000K cycles MAINTAINED : 50,000 CYCLES NOMINAL DIELECTRIC STRENGTH: 1,000VAC INSULATION RESISTANCE: 1G OHM CONTACT RESISTANCE: 50m OHMS MAX INITIAL LED SPECIFICATIONS: SEE LED SPECIFICATION		CENTER SPOT ILLUMINATION		C																																																																
B		NOTE 1.CURRENT LIMITING RESISTOR IS REQUIRED TO LIMIT LED FORWARD CURRENT TO 20mA 2. SUPPLY HEX NUT AND SEALING WASHER BULK PACKED. 3.INNER RESISTOR ONLY FOR LED :RED / BLUE / GREEN / WHITE.								B																																																												
A				<table><tr><td>DWG TYPE</td><td>DRAWN</td><td rowspan="2">TOLERANCES: UNLESS OTHERWISE NOTED X.X ± 0.5 X.XX ± 0.25 ANGULAR ± 5°</td><td colspan="2" rowspan="2">DWG TITLE W48M-MECHANICAL MOMENTARY/MAINTAIN, NONE/CENTER SPOT/ POWER STANDBY SYMBOL ILLUMINATION</td><td colspan="4" rowspan="5"></td></tr><tr><td>SALES DRAWING</td><td>K.Y.</td></tr><tr><td>STATUS</td><td>RELEASE</td><td>REVIEW</td><td colspan="6">DWG NO.</td></tr><tr><td colspan="2" rowspan="2">This document is the intellectual property of ITW Electronic Business Asia Co., Limited and may contain confidential, proprietary, privileged information protected by law. Neither this document nor any information it contains can be reproduced, transformed to any other format, or distributed, without written permission by ITW Electronic Business Asia Co., Limited. 本文作為安達電子電器股份有限公司之智慧財產，非經許可不得翻取、複製、轉變成其他形式使用或散佈</td><td>APPROVED</td><td>THIRD ANGLE PROJECTION</td><td colspan="5" rowspan="2">W48M-E,F,G,H</td></tr><tr><td>v.w.</td><td></td></tr><tr><td colspan="2"></td><td>DATE</td><td>REF:</td><td>管制文件 非管制文件</td><td>Unit</td><td>SCALE</td><td>REV</td><td>RoHS Compliant</td><td rowspan="3">SHEET 1 OF 3</td></tr><tr><td colspan="2"></td><td>2017/8/26</td><td>48M-1,2,5,6,A,B</td><td></td><td>mm</td><td>3:2</td><td>2</td><td></td></tr></table>		DWG TYPE	DRAWN	TOLERANCES: UNLESS OTHERWISE NOTED X.X ± 0.5 X.XX ± 0.25 ANGULAR ± 5°	DWG TITLE W48M-MECHANICAL MOMENTARY/MAINTAIN, NONE/CENTER SPOT/ POWER STANDBY SYMBOL ILLUMINATION						SALES DRAWING	K.Y.	STATUS	RELEASE	REVIEW	DWG NO.						This document is the intellectual property of ITW Electronic Business Asia Co., Limited and may contain confidential, proprietary, privileged information protected by law. Neither this document nor any information it contains can be reproduced, transformed to any other format, or distributed, without written permission by ITW Electronic Business Asia Co., Limited. 本文作為安達電子電器股份有限公司之智慧財產，非經許可不得翻取、複製、轉變成其他形式使用或散佈		APPROVED	THIRD ANGLE PROJECTION	W48M-E,F,G,H					v.w.				DATE	REF:	管制文件 非管制文件	Unit	SCALE	REV	RoHS Compliant	SHEET 1 OF 3			2017/8/26	48M-1,2,5,6,A,B		mm	3:2	2		A														
DWG TYPE	DRAWN	TOLERANCES: UNLESS OTHERWISE NOTED X.X ± 0.5 X.XX ± 0.25 ANGULAR ± 5°	DWG TITLE W48M-MECHANICAL MOMENTARY/MAINTAIN, NONE/CENTER SPOT/ POWER STANDBY SYMBOL ILLUMINATION																																																																			
SALES DRAWING	K.Y.																																																																					
STATUS	RELEASE	REVIEW	DWG NO.																																																																			
This document is the intellectual property of ITW Electronic Business Asia Co., Limited and may contain confidential, proprietary, privileged information protected by law. Neither this document nor any information it contains can be reproduced, transformed to any other format, or distributed, without written permission by ITW Electronic Business Asia Co., Limited. 本文作為安達電子電器股份有限公司之智慧財產，非經許可不得翻取、複製、轉變成其他形式使用或散佈		APPROVED	THIRD ANGLE PROJECTION	W48M-E,F,G,H																																																																		
		v.w.																																																																				
		DATE	REF:	管制文件 非管制文件	Unit	SCALE	REV	RoHS Compliant	SHEET 1 OF 3																																																													
		2017/8/26	48M-1,2,5,6,A,B		mm	3:2	2																																																															
8		7		6		5		4		3		2		1																																																								



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[W48M-F12B](#)