






PART NUMBER		SML-LX0606SISUGCTR	REV	E
REV	E.C.N. NUMBER AND REVISION COMMENTS			DATE
A	E.C.N. #11148			05.29.07
B	E.C.N. #11508			03.05.09
C	E.C.N. #11581			12.21.09
D	E.C.N. #11964			07.02.15
E	ECN-Lumex201700010			04.10.17



RECOMMENDED SOLDER PAD LAYOUT



ELECTRO-OPTICAL CHARACTERISTIC TA=25°C

PARAMETER		MIN	TYP	MAX	UNITS	TEST COND
PEAK WAELENGHT	R	-	645	-	nm	If=20mA
	G	-	575	-		
FORWARD VOLTAGE	R	-	1.9	2.5	Vf	If=20mA
	G	-	2	2.5		
REVERSE VOLTAGE (R/G)		-	-	5	Vr	IR=10uA
LUMINOUS INTENSITY	R	40	-	80	mcd	If=20mA
	G	20	-	55		
VIEWING ANGLE		-	120	-	2x theta1/2	If=20mA
EMITTED COLOR		R/G				
EPOXY LENS FINISH		WATER CLEAR				

ABSOLUTE MAXIMUM RATINGS TA=25°C

PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT (R/G)*	180/150	mA
FORWARD CURRENT	30/30	mA
POWER DISIPATION (R/G)	75/75	mW
STORAGE TEMPERATURE	-40 to +85	°C
OPERATING TEMPERATURE	-40 to +85	°C

*t<10us

CUSTOM: MOISTURE SENSITIVE DEVICE
PER JEDEC LEVEL 3 STANDARDS

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= ^{+DECIMAL PRECISION}/_{-0.00} MAX= ^{+0.00}/_{-DECIMAL PRECISION}



N. GARY AVE.
CAROL STREAM, IL 60188
PHONE : 800-278-5666
FAX : 630-315-2150
WEB : WWW.LUMEX.COM425

1.6(L)*1.5(W)*0.7(H)mm, SURFACE MOUNT LED, AlInGaP RED/AlInGaP GREEN BICOLOR LED, WATER CLEAR LENS, TAPE & REEL



****THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT.****

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE : 2017.04.10
PAGE : 1 OF 2
SCALE : NTF
UNIT : mm [INCH]

DRAWN BY : E.C.
CHKD BY : G.Y.
APRVD BY : R.C.
Pb

PART NUMBER		SML-LX0606SISUGCTR	REV	E
REV	E.C.N. NUMBER AND REVISION COMMENTS			DATE
A	E.C.N. #11148			05.29.07
B	E.C.N. #11508			03.05.09
C	E.C.N. #11581			12.21.09
D	E.C.N. #11964			07.02.15
E	ECN-Lumex201700010			04.10.17



*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= ^{+DECIMAL PRECISION}_{-0.00} MAX.= ^{+0.00}_{-DECIMAL PRECISION}



N. GARY AVE.
CAROL STREAM, IL 60188
PHONE : 800-278-5666
FAX : 630-315-2150
WEB : WWW.LUMEX.COM425

1.6(L)*1.5(W)*0.7(H)mm, SURFACE MOUNT LED, AlInGaP RED/AlInGaP GREEN BICOLOR LED, WATER CLEAR LENS, TAPE & REEL

****THE SPECIFICATIONS MAY CHANGE AT ANY TIME WITHOUT NOTICE DUE TO NEW MATERIALS OR PRODUCT IMPROVEMENT.****

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

DATE : 2017.04.10	DRAWN BY : E.C.
PAGE : 2 OF 2	CHKD BY : G.Y.
SCALE : NTF	APRVD BY : R.C.
UNIT : mm [INCH]	(Pb)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SML-LX0606SISUGCTR](#)