

# D Series

## Miniature Snap-in Power Rocker Switches

### Features/Benefits

- **Momentary and maintained models**
- **PC and quick connect terminals**
- **Recessed bracket available — prevents accidental actuation**
- **RoHS compliant**
- **Gold plated options available**

### Typical Applications

- **Small appliances**
- **Computers and peripherals**
- **Medical instrumentation**



UL 61058-1



### Specifications

CONTACT RATING:

D101, D102, D103, D105, D108, D201, D202, D203

GP (general purpose)

4 AMPS 125 VAC 50/60 Hz T85 10,000 cycles

2 AMPS 250 VAC 50/60 Hz T85 10,000 cycles

R (resistive)

4 AMPS 30 VDC T85 10,000 cycles

D501, D502, D503, D508, D601, D602, D608

GP (general purpose)

10 AMPS 125 VAC 50/60 Hz T85 10,000 cycles

5 AMPS 250 VAC 50/60 Hz T85 10,000 cycles

R (resistive)

10 AMPS 30 VDC T85 10,000 cycles

0.4VA @ 20V AC/DC (gold plating) available upon request

ELECTRICAL LIFE: 10,000 make-and-break cycles at full load.

INSULATION RESISTANCE:  $10^9 \Omega$  min.

DIELECTRIC STRENGTH: 1,000 Vrms min. @ sea level.

### Materials

ACTUATOR & HOUSING: 6/6 nylon (UL 94V-2), color black, finish: matte.

MOVABLE CONTACTS: D10X and D20X Models: Copper, silver plated.  
D50X and D60X Models: Coin silver, silver plated.

STATIONARY CONTACTS AND TERMINALS: Copper or brass, silver plated. Gold plating available.

CONTACT SPRING: Music wire or stainless steel.

OPERATING TEMPERATURE: -30°C to +65°C

**NOTE:** Specifications and materials listed above are for standard switches. For information on specific and custom switches, consult Customer Service Center.

### Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages G-61 through G-65. For additional options not shown in catalog, consult Customer Service Center.

Switch Function	Actuator	Actuator Color	Mounting Style/Color	Terminations	Actuator Markings	Contact Material
<b>D101</b> SPDT, On-None-On	<b>J1</b> Rocker	<b>2</b> Black	<b>S2</b> Snap-in, black	<b>15</b> Quick connect	<b>NONE</b> No marking	<b>QA</b> Silver
<b>D102</b> SPST, On-None-Off	<b>J5</b> Lever	<b>1</b> White	<b>B2</b> Recessed snap-in actuator guard, black	<b>A</b> Right angle, PC thru-hole	<b>D</b> ON-OFF	Gold plating options available contact Customer Service
<b>D103</b> SPDT, On-Off-On		<b>3</b> Red	<b>G2</b> Actuator guard, black	<b>02</b> PC Thru-hole	<b>H</b> 0 I	
<b>D105</b> SPDT, Mom.-Off-Mom.			<b>S1</b> Snap-in, white	<b>05</b> Twisted quick connect	<b>N</b> Large dot	
<b>D108</b> SPDT, Mom.-None-On				<b>06</b> Extended PC thru-hole	<b>P</b> 0 -	
<b>D201</b> DPDT, On-None-On				<b>17</b> Wireable quick connect	<b>R</b> Red rectangle on end	
<b>D202</b> DPST, On-None-Off					<b>U</b> Large dot on end	
<b>D203</b> DPDT, On-Off-On						
<b>D501</b> SPDT, On-None-On						
<b>D502</b> SPST, On-None-Off						
<b>D503</b> SPDT, On-Off-On						
<b>D508</b> SPDT, Mom.-None-On						
<b>D601</b> DPDT, On-None-On						
<b>D602</b> DPST, On-None-Off						
<b>D608</b> DPDT, Mom.-None-On						










15 May 20




# D Series Miniature Snap-in Power Rocker Switches

## SWITCH FUNCTION



NO. POLES	MODEL NO.	AMP RATING*	SWITCH FUNCTION			CONNECTED TERMINALS			SCHEMATIC
			POS. 1	POS. 2	POS. 3	POS. 1	POS. 2	POS. 3	
									
SP	D102 D502	4 10	ON	NONE	OFF	1-1A	N/A	OPEN	SPST 
	D101 D501	4 10	ON	NONE	ON			OPEN	1-1B
	D103 D503	4 10		OFF					
	D105	4		MOM.			OFF		
	D108 D508	4 10	MOM.	NONE	ON		N/A		



### SPDT




ACTUATOR SHOWN IN POSITION 1

TERMINAL NOS.  
FOR REF. ONLY

Part number shown: D101J12S215QA

DP	<b>D202</b>	4	ON	NONE	OFF	1-1A, 2-2A	N/A	OPEN	DPST	
	<b>D602</b>	10								
	<b>D201</b>	4	ON	NONE	ON		1-1B, 2-2B	DPDT		
	<b>D601</b>	10								
	<b>D203</b>	4		OFF						
<b>D608</b>	10	MOM.	NONE		N/A					

### DPDT



ACTUATOR SHOWN IN POSITION 1

TERMINAL NOS.  
FOR REF. ONLY

Part number shown: D201J12S215QA


MOM. = Momentary

\*AMP RATING: see G-60

See CONTACT MATERIALS, page G-64.



Rocker



Dimensions are shown: Inches (mm)

Specifications and dimensions subject to change

[www.ckswitches.com](http://www.ckswitches.com)


**C&K**

15 May 20


# D Series Miniature Snap-in Power Rocker Switches



## J1 ROCKER



## J5 LEVER




OPTION CODE	ACTUATOR COLOR
2	BLACK
1	WHITE
3	RED

**NOTE:** Actuator finish: matte. Other colors available, consult Customer Service Center.

'J5' actuator available only with DP models D201, D202, D601 and D602.

## MOUNTING STYLE/COLOR


### S SNAP-IN



OPTION CODE	HOUSING COLOR
2	(STD.) BLACK
1	WHITE


**NOTE:** Frame finish on housing: matte. Other colors available, consult Customer Service Center.

### B2 RECESSED SNAP-IN ACTUATOR GUARD, BLACK




**NOTE:** Vertical mount, SP models only.

### G2 ACTUATOR GUARD, BLACK




**NOTE:** Vertical mount, SP models only.

### PANEL MOUNTING



PANEL THICKNESS	DIM 'A' SP & DP MODELS 'S' MOUNTING STYLE	DIM 'A' WITH 'G2' OPTION SP MODELS ONLY	DIM 'A' SP MODELS 'B' MOUNTING STYLE
.030-.049 (0,76) (1,24)	.756 (19,20)	.764 (19,41)	1.068 (27,13)
.049-.079 (1,24) (2,01)	.764 (19,41)	.780 (19,81)	1.076 (27,33)
.079-.118 (2,01) (3,00)	.780 (19,81)	n/a	1.092 (27,74)

**NOTE:** Blank insert available for SP models only, see page G-64.



Third Angle Projection



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change



15 May 20




## TERMINATIONS




## TERMINATIONS

Figure 1 shows two mechanical components, SP and DP, with their typical dimensions. The SP component has a width of .122 TYP (3, 10). The DP component has a width of .400 (10, 16) and a height of .031 50 TYP (0, 79).




DX02: .050 DIA  
DX06: .075 DIA



## ACTUATORS

**U** LARGE DOT ON END



Third Angle Projection

**C&K**

[www.ckswitches.com](http://www.ckswitches.com)

## D Series Miniature Snap-in Power Rocker Switches

OPTION CODE	CONTACT AND TERMINAL MATERIAL	RATINGS
QA	SILVER <sup>1</sup>	D101, D102, D103, D105, D108, D201, D202, D203
		GP (general purpose) 4 AMPS 125 VAC 50/60 Hz T85 10,000 cycles
		2 AMPS 250 VAC 50/60 Hz T85 10,000 cycles
		R (resistive) 4 AMPS 30 VDC T85 10,000 cycles
		D501, D502, D503, D508, D601, D602, D608
		GP (general purpose) 10 AMPS 125 VAC 50/60 Hz T85 10,000 cycles
		5 AMPS 250 VAC 50/60 Hz T85 10,000 cycles
		R (resistive) 10 AMPS 30 VDC T85 10,000 cycles


<sup>1</sup>MOVABLE CONTACT: D10X and D20X MODELS: Copper, silver plated.  
D50X and D60X MODELS: Coin silver, silver plated.



0.4VA @ 20V AC/DC Gold plated options available contact Customer Service.


## AVAILABLE HARDWARE

**Insert  
SP Only**




**PART NO.**  
**057190200** BLACK  
Material: Nylon 6/6  
Finish: Matte

**Recessed Actuator Guard,  
SP Only**



**599D02000** BLACK  
Material: 6/6 Nylon  
Finish: Matte



### Actuator Guard



**PART NO.**  
**104C22000**  
Material: PBT thermoplastic  
Finish: Matte

## PART NO.

**216C00000** IP54 SPLASH PROOF RUBBER BOOT



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change



15 May 20

G-65

**www.ckswitches.com**



G

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## C&K Switches:

[D602J11S202PQF](#) [D501J12S215PQF](#) [D501J12S2APQF](#) [D501J12S2AHQF](#) [D502J12S215PQF](#) [D601J12S215PQF](#)  
[D602J12S215PQF](#) [D602J1-2-S2-05-H-QF](#) [D502J12S217PQF](#) [D101J12S205QF](#) [D101J12S217NQF](#)  
[D102J12B215HQF](#) [D102J12B217PQF](#) [D201J12S202QF](#) [D202J12S217HQF](#) [D502J12S2AQF](#) [D601J12S202QF](#)  
[D602J12S217HQF](#) [D101J12S215HQF](#) [D101J12S215PQF](#) [D101J12S2APQF](#) [D102J12B215PQF](#) [D102J12S205PQF](#)  
[D102J12S215HQF](#) [D102J12S215PQF](#) [D102J12S215RQF](#) [D102J12S217PQF](#) [D102J12S2APQF](#)  
[D102J13S215HQF](#) [D102J13S217PQF](#) [D105J19S205QA](#) [D201J12S215UQF](#) [D202J12S205PQF](#) [D202J12S215PQF](#)  
[D202J12S217PQF](#) [D202J13S205PQF](#) [D501J12B215QF](#) [D501J12S202HQF](#) [D501J12S202PQF](#) [D501J12S205QF](#)  
[D501J12S215QF](#) [D502J12B215PQF](#) [D502J12S206QF](#) [D502J12S215DQF](#) [D502J12S215QF](#) [D502J12S2AHQF](#)  
[D502J12S2APQF](#) [D502J17S215NQA](#) [D601J12S205QF](#) [D601J12S215QF](#) [D602J11S115PQF](#) [D602J11S206PQF](#)  
[D602J12S205PQF](#) [D602J12S215QF](#) [D602J12S205HQF](#) [D502J12S105PQF](#) [D601J13S215PQF](#) [D602J12S202PQF](#)  
[D202-J1-2-S2-05QA](#) [D101J12G215PQA](#) [D602J12S217PQA](#) [D601J17S215QA](#) [D102J13S205PQA](#)  
[D102J12G202DQA](#)