

HWB6 SEALED POWER DISTRIBUTION MODULE

Compact Hard-Wired PDM for 280 Style Components



Description

The HWB6 Compact Hard-Wired Box features 6 cavities that accept 2.8mm fuse components and is the perfect fit for accessory circuits and overflow circuits from your main Power Distribution module. The HWB6 can hold plug-in components including MINI fuses and MINI format circuit breakers. The HWB6 features durable construction, an IP67/IP69K rating, and a compact size. The user can customize their own circuitry utilizing direct wire-to-component connections which are crimped to the wire harness with grommets to form the sealing for the lower parts of the HWB6.

Features and Benefits

- AssureLatch™ yellow positive-sealing latches keep the cover securely in place while allowing for fast service.
- Accepts any MINI (280 style) fuses or circuit breakers.
- Compact size allows the unit to be installed in vehicles with limited space.
- Ideal for accessory circuits, overflow circuits from main
- IP67/IP69k sealed units can be installed virtually anywhere on the vehicle and stands up to road splash and salt spray.
- TPAs (terminal position assurance locks) give secondary locking protection of the wire leads, which help keeps leads securely in place.
- Wires plug into the back of the unit using industry-standard TE Connectivity MCP terminals.
- Tethers available to prevent loss of cover during service.
- Clear cover available to help identify fuse condition
- HWB18, HWB12 & HWB6 share the same mounting bracket so electrical system modification can be performed without bracket or sheet metal alterations.
- A UL certification for this fuseholder means it can be used as a component in material handling and electric-battery-powered industrial truck applications with confidence that it meets the requirements of UL 583 standards.

Specifications Overview

Max Fuse Rating:	30A per circuit
Max Continuous Current:	68A
Number of Cavities	6
Operating Temp:	-40 °C to +105 °C
Ingress Protection:	IP67/IP69K


Applications

- Accessory circuits
- Overflow circuits

Web Resources

Download 2D print and technical resources at:
littelfuse.com/hwb6

Ordering Information

PART NUMBER	COVER		AssureLatch™		MOUNTING BRACKET
	BLACK	CLEAR			
PDM32001ZXM		•	•		
PDM32002ZXM	•		•	•	
PDM32003ZXM		•	•		Straight
PDM32004ZXM	•		•	•	Straight

UR file number: AU6325

TPA: Terminal Position Assurance secondary locks for wire terminals

Accessories and Service Parts

PART NUMBER	DESCRIPTION
868-059	Base
873-019-001	Tall cover in clear
873-019-002	Tall cover in black (UR)
904-059	Silicone seal
883-086	1 pcs. AssureLatch™ with thumb release
883-085	TPA
890009470	Tether
868-964	90° mounting bracket

HWB6 SEALED POWER DISTRIBUTION MODULE

Specifications


Max Fuse Rating	30A per circuit
Max Continuous Current	68A
Number of Cavities	6
Recommended Mounting	M6 bolt and lock washer
Mounting Bracket Torque	5.5-6.5 Nm
Temperature Range	-40 °C to +105 °C
Ingress Protection Rating	IP67/IP69K
Dimensions	70.9x64.3x36.4 mm
Wire Sizes	0.35-2.50 mm ²
Mating Terminals & Seals	TE Connectivity MCP Series. Sold separately.
Accessories	Optional: Cover tether, 90° angle bracket

Mating Terminals and Seals Compatibility

Wire Size Range (mm ²)	Insulation Diameter (mm) FLR	Materials and Finish	Part Number Strip Form	TE Cable Seal Part Number	Cable Seal Color
0.35–0.50	1.2–1.4	1-xxx-1/1-xxx-3	968882	828904-1	Blue
0.5–1.0	1.4–2.1	1-xxx-1/1-xxx-2/1-xxx-3	968855	828904-2	Blue
1.0–2.5	2.2–3.0	1-xxx-1/1-xxx-3	968857	828905-1	White
Empty Cavity	—	—	Cable Seal Plug	828922-1	Natural

Sold separately. Available from TE Connectivity.

Dimensions in millimeters



Visit [Littelfuse.com](https://www.littelfuse.com) for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[PDM32003ZXM](#) [PDM32004ZXM](#) [PDM32001ZXM](#) [PDM32002ZXM](#)