



RESISTANCE @ +25°C = 10,000 Ω NOMINAL
 ACCURACY (+15 TO +80°C) = ± 0.50°C
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +140°C

MAXIMUM TEMPERATURE FOR BEST LONG-TERM STABILITY = +80°C

LEAD WIRE: 34 AWG (0.0063" DIAMETER), TWO CONDUCTOR,
 SOLID CONDUCTOR, POLYIMIDE INSULATED,
 0.0086" X 0.0175" NOMINAL O.D.

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	ADDED NOMINAL WIRE O.D.	09/18/17	DD
NONE	RELEASE TO PRODUCTION	09/18/17	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT U.S. SENSOR corp.	
DRAWN BY	DAN DANKERT		
DATE	09/18/17	714-639-1000 www.ussensor.com	
REV	"A"	THERMISTOR PROBE	
LAYER	0 OF 2	P/N USP19407	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[USP19407](#)