

Features

- Up to +1dBm RF
- +3-5 dBm LO Drive
- Low Profile
- Tape and reel packaging available
- 260°C Reflow Compatible

Description

M/A-COM Technology Solutions MAMXES0108 is a Low Cost, Broadband, high performance Double Balanced Mixer designed for use in high volume wireless applications. The device has been optimised by careful selection of the Schottky Diode and Balun Transformer for excellent performance. MAMXES0108 is available in an SM-89 surface mount package and reflows using standard soldering.

Product Image



Absolute Maximum Ratings ^{1,2}


Parameter	Absolute Maximum
Impedance	50 Ohms nominal
RF Power	1 Watt
Internal Load Dissipation	0.125 Watt
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +125°C

1. Exceeding any one or combination of these limits may cause permanent damage to this device.
2. M/A-COM does not recommend sustained operation near these survivability limits.

Pin Configuration

Function	Pin No.
LO	1
RF	4
IF	5
GND	2,3,6

Component Dimensions



* Restrictions on Hazardous Substances, European Union Directive 2002/95/EC.

1

ADVANCED: Data Sheets contain information regarding a product M/A-COM Technology Solutions is considering for development. Performance is based on target specifications, simulated results, and/or prototype measurements. Commitment to develop is not guaranteed.
PRELIMINARY: Data Sheets contain information regarding a product M/A-COM Technology Solutions has under development. Performance is based on engineering tests. Specifications are typical. Mechanical outline has been fixed. Engineering samples and/or test data may be available. Commitment to produce in volume is not guaranteed.

• North America Tel: 800.366.2266 • Europe Tel: +353.21.244.6400
 • India Tel: +91.80.43537383 • China Tel: +86.21.2407.1588
 Visit www.macomtech.com for additional data sheets and product information.


M/A-COM Technology Solutions Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Electrical Specifications: $T_A = 25^\circ\text{C}$, $Z_0 = 50\Omega$
LO=+3,4,5dBm


Parameter	Frequency	Units	Min.	Typ.	Max.
Conversion Loss	0.5 - 500MHz (LO=5dBm)	dB	6.2	7.0	7.8
	0.5 - 500MHz (LO=4dBm)	dB	6.2	7.15	7.8
	0.5 - 500MHz (LO=3dBm)	dB	6.2	7.30	7.8
LO-RF Isolation	0.5 - 500MHz	dB	30	40	—
LO-IF Isolation	0.5 - 500MHz	dB	30	40	—
1dB Compression		dBm	—	—	+1

Typical Performance Curves


Conversion Loss




LO-RF Isolation



LO-IF Isolation



Tape Specification



Item	Dimension
Ao	7.00mm +/-0.1mm
Bo	8.60mm +/-0.1mm
Ko	3.90mm +/-0.1mm
W	16.00mm +/-0.3mm
P1	12.00mm +/-0.1mm

Ordering Information

Part Number	Package
MAMXES0108	Tape and Reel (900 piece Reel)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[MAMXES0108](#)