

S8X5ECSx




Description

The S8X5ECSx offers a high static dv/dt with a low turn off (t_q) time. It is specifically designed for GFCI (Ground Fault Circuit Interrupter) and AFCI (Arc Fault Circuit Interrupter), RCD (Residual Current Device) and RCBO (Residual Current Circuit Breaker with Overload Protection) applications. All SCR junctions are glass-passivated to ensure long term reliability and parametric stability.

Main Features

| Symbol | Value | Unit |
|----------------------------|-----------|---------|
| $I_{T(RMS)}$ | 0.5 | A |
| V_{DRM}/V_{RRM} | 800 | V |
| $V_{DSM} (t_p = 50 \mu s)$ | 1150 | V |
| $V_{RSM} (t_p = 50 \mu s)$ | 900 | V |
| I_{GT} | 20 to 100 | μA |

Schematic Symbol



Features

- Thru-hole packages
- Surge current capability < 20Amps
- Blocking voltage (V_{DRM}/V_{RRM}) capability - up to 800V
- Non-repetitive direct surge peak off-state voltage (V_{DSM}) up to 1150V
- Non-repetitive reverse surge peak off-state voltage (V_{RSM}) up to 900V
- High dv/dt noise immunity
- Improved turn-off time (t_q)
- Sensitive gate for direct microprocessor interface
- Halogen free and RoHS compliant

Absolute Maximum Ratings

| Symbol | Parameter | Value | Unit |
|--------------|--------------------------------------------------------------------------------------------|------------------------------------------------|----------------|
| $I_{T(RMS)}$ | RMS on-state current (full sine wave) | $T_c = 85^\circ C$ 0.5 | A |
| $I_{T(AV)}$ | Average on-state current | $T_c = 85^\circ C$ 0.3 | A |
| I_{TSM} | Non repetitive surge peak on-state current (Sine half wave, T_j initial = $25^\circ C$) | $F = 50Hz$ 10 $F = 60Hz$ 12 | A |
| I^2t | I^2t Value for fusing | $t_p = 10 ms$ $F = 50 Hz$ 0.5 | A^2s |
| di/dt | Critical rate of rise of on-state current $I_G = 10mA$ | $T_j = 125^\circ C$ 80 | $A/\mu s$ |
| I_{GM} | Peak Gate Current | $t_p = 20 \mu s$ $T_j = 125^\circ C$ 0.5 | A |
| $P_{G(AV)}$ | Average gate power dissipation | $T_j = 125^\circ C$ 0.2 | W |
| T_{sig} | Storage junction temperature range | — | -40 to 150 |
| T_j | Operating junction temperature range | — | -40 to 125 |

Electrical Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise specified)

| Symbol | Description | Test Conditions | Limit | Value | | Unit |
|-----------|--------------------------------------------|---------------------------------------------------------------------------------------------------------|-------|---------|----------|------------------|
| | | | | S8X5ECS | S8X5ECS2 | |
| I_{GT} | DC Gate Trigger Current | $V_D = 6\text{V}$ $R_L = 100\ \Omega$ | Min. | 20 | 20 | μA |
| | | | Max. | 100 | 50 | μA |
| V_{GT} | DC Gate Trigger Voltage | $V_D = 6\text{V}$ $R_L = 100\ \Omega$ | Max. | 0.8 | | V |
| V_{GRM} | Peak Reverse Gate Voltage | $I_{RG} = 10\ \mu\text{A}$ | Min. | 8 | | V |
| I_H | Holding Current | $R_{GK} = 1\ \text{k}\Omega$ Initial Current = 20mA | Max. | 3 | | mA |
| dv/dt | Critical Rate-of-Rise of Off-State Voltage | $T_J = 125^\circ\text{C}$ $V_D = 67\%$ of V_{DRM} Exp. Waveform $R_{GK} = 1\ \text{k}\Omega$ | Min. | 40 | | V/ μs |
| V_{GD} | Gate Non-Trigger Voltage | $V_D = 1/2 V_{DRM}$ $R_{GK} = 1\ \text{k}\Omega$ $T_J = 125^\circ\text{C}$ | Min. | 0.2 | | V |
| t_q | Turn-Off Time | $I_T = 0.5\text{A}$ | Max. | 35 | | μs |
| t_{gt} | Turn-On Time | $I_G = 10\text{mA}$ $P_W = 15\ \mu\text{sec}$ $I_T = 1.6\text{A(pk)}$ | Typ. | 2.3 | | μs |

Static Characteristics ($T_J = 25^\circ\text{C}$, unless otherwise specified)

| Symbol | Description | Test Conditions | Limit | Value | Unit |
|---------------------|------------------------------------|-----------------------------------------------------------|-------|-------|------------------|
| V_{TM} | Peak On-State Voltage | 0.5A device $I_{TM} = 4\text{A}$ $t_p = 380\ \mu\text{s}$ | MAX. | 1.8 | V |
| V_{TO} | Threshold Voltage | - | MAX. | 1.03 | V |
| R_D | Dynamic Resistance | - | MAX. | 106 | $\text{m}\Omega$ |
| I_{DRM} / I_{RRM} | Off-State Current, Peak Repetitive | $T_J = 25^\circ\text{C}$ | MAX. | 3 | μA |
| | | $T_J = 125^\circ\text{C}$ | MAX. | 500 | μA |

Thermal Resistances

| Symbol | Description | Test Conditions | Value | Unit |
|---------------|-----------------------|------------------------------------------|-------|---------------------------|
| $R_{th(JC)}$ | Junction to case (AC) | $I_T = 0.8\text{A}_{(RMS)}$ ¹ | 35 | $^\circ\text{C}/\text{W}$ |
| $R_{th(j-a)}$ | Junction to ambient | $I_T = 0.8\text{A}_{(RMS)}$ ¹ | 150 | $^\circ\text{C}/\text{W}$ |

1. 60Hz AC resistive load condition, 100% conduction.

Figure 1: Normalized DC Gate Trigger Current For All Quadrants vs. Junction Temperature




Figure 2: Normalized DC Holding Current vs. Junction Temperature




Figure 3: Normalized DC Gate Trigger Voltage vs. Junction Temperature




Figure 4: On-State Current vs. On-State Voltage (Typical)




Figure 5: Power Dissipation (Typical) vs. RMS On-State Current




Figure 6: Maximum Allowable Case Temperature vs. On-State Current





Figure 7: Surge Peak On-State Current vs. Number of Cycles




Supply Frequency: 60Hz Sinusoidal
Load: Resistive
RMS On-State Current ($I_{T(RMS)}$): Max Rated Value at Specific Case Temperature

- Notes:
1. Gate control may be lost during and immediately following surge current interval.
 2. Overload may not be repeated until junction temperature has returned to steady-state rated value.

Soldering Parameters

| | | |
|--------------------------------------------------------|------------------------------------|-------------------------|
| Reflow Condition | | Pb – Free assembly |
| Pre Heat | - Temperature Min ($T_{s(min)}$) | 150°C |
| | - Temperature Max ($T_{s(max)}$) | 200°C |
| | - Time (min to max) (t_s) | 60 – 180 secs |
| Average ramp up rate (Liquidus Temp) (T_L) to peak | | 5°C/second max |
| $T_{s(max)}$ to T_L - Ramp-up Rate | | 5°C/second max |
| Reflow | - Temperature (T_L) (Liquidus) | 217°C |
| | - Time (min to max) (t_s) | 60 – 150 seconds |
| Peak Temperature (T_p) | | 260 ^{+0/-5} °C |
| Time within 5°C of actual peak Temperature (t_p) | | 20 – 40 seconds |
| Ramp-down Rate | | 5°C/second max |
| Time 25°C to peak Temperature (T_p) | | 8 minutes Max. |
| Do not exceed | | 280°C |



Physical Specifications

| | |
|------------------------|---------------------------------------------------------|
| Terminal Finish | 100% Matte Tin-plated. |
| Body Material | UL Recognized compound meeting flammability rating V-0. |
| Lead Material | Copper Alloy |


Design Considerations

Careful selection of the correct component for the application's operating parameters and environment will go a long way toward extending the operating life of the Thyristor. Good design practice should limit the maximum continuous current through the main terminals to 75% of the component rating. Other ways to ensure long life for a power discrete semiconductor are proper heat sinking and selection of voltage ratings for worst case conditions. Overheating, overvoltage (including dv/dt), and surge currents are the main killers of semiconductors. Correct mounting, soldering, and forming of the leads also help protect against component damage.

Reliability/Environmental Tests

| Test | Specifications and Conditions |
|----------------------------------|----------------------------------------------------------------------------|
| AC Blocking | MIL-STD-750, M-1040, Cond A Applied Peak AC voltage @ 125°C for 1008 hours |
| Temperature Cycling | MIL-STD-750, M-1051, 1000 cycles; -55°C to +150°C; 15-min dwell-time |
| Temperature/Humidity | EIA / JEDEC, JESD22-A101 1008 hours; 320V - DC: 85°C; 85% rel humidity |
| UHAIST | JESD22-A118, 96 hours, 130°C, 85%RH |
| High Temp Storage | MIL-STD-750, M-1031, 1008 hours; 150°C |
| Low-Temp Storage | 1008 hours; -40°C |
| Resistance to Solder Heat | MIL-STD-750 Method 2031 |
| Solderability | ANSI/J-STD-002, category 3, Test A |
| Lead Bend | MIL-STD-750, M-2036 Cond E |

Dimensions – TO-92




| Dimension | Inches | | Millimeters | |
|-----------|--------|-------|-------------|-------|
| | Min | Max | Min | Max |
| A | 0.175 | 0.205 | 4.450 | 5.200 |
| B | 0.170 | 0.210 | 4.320 | 5.330 |
| C | 0.500 | | 12.70 | |
| D | 0.135 | | 3.430 | |
| E | 0.125 | 0.165 | 3.180 | 4.190 |
| F | 0.080 | 0.105 | 2.040 | 2.660 |
| G | 0.016 | 0.021 | 0.407 | 0.533 |
| H | 0.045 | 0.055 | 1.150 | 1.390 |
| I | 0.095 | 0.105 | 2.420 | 2.660 |
| J | 0.015 | 0.020 | 0.380 | 0.500 |


Packing Option

| Part Number | Marking | Weight | Packing Mode | Base Quantity |
|-------------|----------|--------|--------------|---------------|
| S8X5ECS | S8X5ECS | 0.217G | Bulk | 2500 |
| S8X5ECSRP | S8X5ECS | 0.217G | Tape & Reel | 2000 |
| S8X5ECSAP | S8X5ECS | 0.217G | Ammo Pack | 2000 |
| S8X5ECS2 | S8X5ECS2 | 0.217G | Bulk | 2500 |
| S8X5ECS2RP | S8X5ECS2 | 0.217G | Tape & Reel | 2000 |
| S8X5ECS2AP | S8X5ECS2 | 0.217G | Ammo Pack | 2000 |


TO-92 (3-lead) Reel Pack (RP) Radial Leaded Specifications




TO-92 (3-lead) Ammo Pack (AP) Radial Leaded Specifications



Part Numbering System



Part Marking System



Line1 = Littelfuse Part Number
Y = Last Digit of Calendar Year
M = Letter Month Code (A-L for Jan-Dec)
L = Location Code
DD = Calendar Date

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[S8X5ECSAP](#) [S8X5ECS](#) [S8X5ECSRP](#) [S8X5ECS2](#) [S8X5ECS2AP](#) [S8X5ECS2RP](#)