

### SMCJ-HR Series



#### Description

The SMCJ-HR High Reliability series is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.

#### Agency Approvals

| Agency                                                                            | Agency File Number |
|-----------------------------------------------------------------------------------|--------------------|
|  | E230531            |


#### Maximum Ratings and Thermal Characteristics (T<sub>A</sub>=25°C unless otherwise noted)

| Parameter                                                                                            | Symbol                            | Value      | Unit |
|------------------------------------------------------------------------------------------------------|-----------------------------------|------------|------|
| Peak Pulse Power Dissipation at T <sub>A</sub> =25°C by 10/1000µs waveform (Fig.1)(Note 1), (Note 2) | P <sub>PPM</sub>                  | 1500       | W    |
| Power Dissipation on infinite heat sink at T <sub>A</sub> =50°C                                      | P <sub>M(AV)</sub>                | 6.5        | W    |
| Peak Forward Surge Current, 8.3ms Single Half Sine Wave (Note 3)                                     | I <sub>FSM</sub>                  | 200        | A    |
| Maximum Instantaneous Forward Voltage at 100A for Unidirectional only (Note 4)                       | V <sub>F</sub>                    | 3.5/5.0    | V    |
| Operating Junction and Storage Temperature Range                                                     | T <sub>J</sub> , T <sub>STG</sub> | -65 to 150 | °C   |
| Typical Thermal Resistance Junction to Lead                                                          | R <sub>uJL</sub>                  | 15         | °C/W |
| Typical Thermal Resistance Junction to Ambient                                                       | R <sub>uJA</sub>                  | 75         | °C/W |

#### Notes:

1. Non-repetitive current pulse, per Fig. 3 and derated above T<sub>A</sub> = 25°C per Fig. 2.
2. Mounted on copper pad area of 0.31x0.31" (8.0 x 8.0mm) to each terminal.
3. Measured on 8.3ms single half sine wave or equivalent square wave for unidirectional device only, duty cycle=4 per minute maximum.

#### Functional Diagram



#### Features

- For surface mounted applications in order to optimize board space
- Low profile package
- Built-in strain relief
- V<sub>BR</sub> @T<sub>J</sub> = V<sub>BR</sub>@25°C x (1+αT x (T<sub>J</sub> - 25))  
(αT: Temperature Coefficient)
- Glass passivated chip junction
- 1500W peak pulse power capability at 10/1000µs waveform, repetition rate (duty cycles): 0.01 %
- Fast response time: typically less than 1.0ps from 0V to BV min
- Excellent clamping capability
- Low incremental surge resistance
- Typical I<sub>R</sub> less than 1µA above 12V
- High Temperature soldering guaranteed: 260°C/40 seconds at terminals
- Plastic package has Underwriters laboratory flammability 94V-O
- Meet MSL level1, per J-STD-020, LF maximum peak of 260°C
- Matte tin lead-free plated
- Halogen free and RoHS compliant
- 2nd level interconnect is Pb-free per IPC/JEDEC J-STD-609A.01
- Recognized to UL 497B as an Isolated Loop Circuit Protector

#### Applications

TVS devices are ideal for the protection of I/O Interfaces, V<sub>CC</sub> bus and other vulnerable circuits used in Telecom, Computer, Industrial and Consumer electronic applications.

### Electrical Characteristics

| Part Number (Uni) | Part Number (Bi) | Marking |     | Reverse Stand off Voltage $V_R$ (Volts) | Breakdown Voltage $V_{BR}$ (Volts) @ $I_T$ |        | Test Current $I_T$ (mA) | Maximum Clamping Voltage $V_C$ @ $I_{PP}$ (V) | Maximum Peak Pulse Current $I_{PP}$ (A) | Maximum Reverse Leakage $I_R$ @ $V_R$ ( $\mu$ A) | Agency Approval  |
|-------------------|------------------|---------|-----|-----------------------------------------|--------------------------------------------|--------|-------------------------|-----------------------------------------------|-----------------------------------------|--------------------------------------------------|-----------------------------------------------------------------------------------------------------|
|                   |                  | UNI     | BI  |                                         | MIN                                        | MAX    |                         |                                               |                                         |                                                  |                                                                                                     |
| SMCJ5.0A-HR       | SMCJ5.0CA-HR     | GDE     | BDE | 5.0                                     | 6.40                                       | 7.00   | 10                      | 9.2                                           | 163.0                                   | 800                                              | X                                                                                                   |
| SMCJ6.0A-HR       | SMCJ6.0CA-HR     | GDG     | BDG | 6.0                                     | 6.67                                       | 7.37   | 10                      | 10.3                                          | 145.7                                   | 800                                              | X                                                                                                   |
| SMCJ6.5A-HR       | SMCJ6.5CA-HR     | GDK     | BDK | 6.5                                     | 7.22                                       | 7.98   | 10                      | 11.2                                          | 134.0                                   | 500                                              | X                                                                                                   |
| SMCJ7.0A-HR       | SMCJ7.0CA-HR     | GDM     | BDM | 7.0                                     | 7.78                                       | 8.60   | 10                      | 12.0                                          | 125.0                                   | 200                                              | X                                                                                                   |
| SMCJ7.5A-HR       | SMCJ7.5CA-HR     | GDP     | BDP | 7.5                                     | 8.33                                       | 9.21   | 1                       | 12.9                                          | 116.3                                   | 100                                              | X                                                                                                   |
| SMCJ8.0A-HR       | SMCJ8.0CA-HR     | GDR     | BDR | 8.0                                     | 8.89                                       | 9.83   | 1                       | 13.6                                          | 110.3                                   | 50                                               | X                                                                                                   |
| SMCJ8.5A-HR       | SMCJ8.5CA-HR     | GDT     | BDT | 8.5                                     | 9.44                                       | 10.40  | 1                       | 14.4                                          | 104.2                                   | 20                                               | X                                                                                                   |
| SMCJ9.0A-HR       | SMCJ9.0CA-HR     | GDV     | BDV | 9.0                                     | 10.00                                      | 11.10  | 1                       | 15.4                                          | 97.4                                    | 10                                               | X                                                                                                   |
| SMCJ10A-HR        | SMCJ10CA-HR      | GDX     | BDX | 10.0                                    | 11.10                                      | 12.30  | 1                       | 17.0                                          | 88.3                                    | 5                                                | X                                                                                                   |
| SMCJ11A-HR        | SMCJ11CA-HR      | GDZ     | BDZ | 11.0                                    | 12.20                                      | 13.50  | 1                       | 18.2                                          | 82.5                                    | 1                                                | X                                                                                                   |
| SMCJ12A-HR        | SMCJ12CA-HR      | GEE     | BEE | 12.0                                    | 13.30                                      | 14.70  | 1                       | 19.9                                          | 75.4                                    | 1                                                | X                                                                                                   |
| SMCJ13A-HR        | SMCJ13CA-HR      | GEG     | BEG | 13.0                                    | 14.40                                      | 15.90  | 1                       | 21.5                                          | 69.8                                    | 1                                                | X                                                                                                   |
| SMCJ14A-HR        | SMCJ14CA-HR      | GEK     | BEK | 14.0                                    | 15.60                                      | 17.20  | 1                       | 23.2                                          | 64.7                                    | 1                                                | X                                                                                                   |
| SMCJ15A-HR        | SMCJ15CA-HR      | GEM     | BEM | 15.0                                    | 16.70                                      | 18.50  | 1                       | 24.4                                          | 61.5                                    | 1                                                | X                                                                                                   |
| SMCJ16A-HR        | SMCJ16CA-HR      | GEP     | BEP | 16.0                                    | 17.80                                      | 19.70  | 1                       | 26.0                                          | 57.7                                    | 1                                                | X                                                                                                   |
| SMCJ17A-HR        | SMCJ17CA-HR      | GER     | BER | 17.0                                    | 18.90                                      | 20.90  | 1                       | 27.6                                          | 54.4                                    | 1                                                | X                                                                                                   |
| SMCJ18A-HR        | SMCJ18CA-HR      | GET     | BET | 18.0                                    | 20.00                                      | 22.10  | 1                       | 29.2                                          | 51.4                                    | 1                                                | X                                                                                                   |
| SMCJ20A-HR        | SMCJ20CA-HR      | GEV     | BEV | 20.0                                    | 22.20                                      | 24.50  | 1                       | 32.4                                          | 46.3                                    | 1                                                | X                                                                                                   |
| SMCJ22A-HR        | SMCJ22CA-HR      | GEX     | BEX | 22.0                                    | 24.40                                      | 26.90  | 1                       | 35.5                                          | 42.3                                    | 1                                                | X                                                                                                   |
| SMCJ24A-HR        | SMCJ24CA-HR      | GEZ     | BEZ | 24.0                                    | 26.70                                      | 29.50  | 1                       | 38.9                                          | 38.6                                    | 1                                                | X                                                                                                   |
| SMCJ26A-HR        | SMCJ26CA-HR      | GFE     | BFE | 26.0                                    | 28.90                                      | 31.90  | 1                       | 42.1                                          | 35.7                                    | 1                                                | X                                                                                                   |
| SMCJ28A-HR        | SMCJ28CA-HR      | GFG     | BFG | 28.0                                    | 31.10                                      | 34.40  | 1                       | 45.4                                          | 33.1                                    | 1                                                | X                                                                                                   |
| SMCJ30A-HR        | SMCJ30CA-HR      | GFK     | BFK | 30.0                                    | 33.30                                      | 36.80  | 1                       | 48.4                                          | 31.0                                    | 1                                                | X                                                                                                   |
| SMCJ33A-HR        | SMCJ33CA-HR      | GFM     | BFM | 33.0                                    | 36.70                                      | 40.60  | 1                       | 53.3                                          | 28.2                                    | 1                                                | X                                                                                                   |
| SMCJ36A-HR        | SMCJ36CA-HR      | GFP     | BFP | 36.0                                    | 40.00                                      | 44.20  | 1                       | 58.1                                          | 25.9                                    | 1                                                | X                                                                                                   |
| SMCJ40A-HR        | SMCJ40CA-HR      | GFR     | BFR | 40.0                                    | 44.40                                      | 49.10  | 1                       | 64.5                                          | 23.3                                    | 1                                                | X                                                                                                   |
| SMCJ43A-HR        | SMCJ43CA-HR      | GFT     | BFT | 43.0                                    | 47.80                                      | 52.80  | 1                       | 69.4                                          | 21.7                                    | 1                                                | X                                                                                                   |
| SMCJ45A-HR        | SMCJ45CA-HR      | GFV     | BFV | 45.0                                    | 50.00                                      | 55.30  | 1                       | 72.7                                          | 20.6                                    | 1                                                | X                                                                                                   |
| SMCJ48A-HR        | SMCJ48CA-HR      | GFX     | BFX | 48.0                                    | 53.30                                      | 58.90  | 1                       | 77.4                                          | 19.4                                    | 1                                                | X                                                                                                   |
| SMCJ51A-HR        | SMCJ51CA-HR      | GFZ     | BFZ | 51.0                                    | 56.70                                      | 62.70  | 1                       | 82.4                                          | 18.2                                    | 1                                                | X                                                                                                   |
| SMCJ54A-HR        | SMCJ54CA-HR      | GGE     | BGE | 54.0                                    | 60.00                                      | 66.30  | 1                       | 87.1                                          | 17.3                                    | 1                                                | X                                                                                                   |
| SMCJ58A-HR        | SMCJ58CA-HR      | GGG     | BGG | 58.0                                    | 64.40                                      | 71.20  | 1                       | 93.6                                          | 16.1                                    | 1                                                | X                                                                                                   |
| SMCJ60A-HR        | SMCJ60CA-HR      | GGK     | BGK | 60.0                                    | 66.70                                      | 73.70  | 1                       | 96.8                                          | 15.5                                    | 1                                                | X                                                                                                   |
| SMCJ64A-HR        | SMCJ64CA-HR      | GGM     | BGM | 64.0                                    | 71.10                                      | 78.60  | 1                       | 103.0                                         | 14.6                                    | 1                                                | X                                                                                                   |
| SMCJ70A-HR        | SMCJ70CA-HR      | GGP     | BGP | 70.0                                    | 77.80                                      | 86.00  | 1                       | 113.0                                         | 13.3                                    | 1                                                | X                                                                                                   |
| SMCJ75A-HR        | SMCJ75CA-HR      | GGR     | BGR | 75.0                                    | 83.30                                      | 92.10  | 1                       | 121.0                                         | 12.4                                    | 1                                                | X                                                                                                   |
| SMCJ78A-HR        | SMCJ78CA-HR      | GGT     | BGT | 78.0                                    | 86.70                                      | 95.80  | 1                       | 126.0                                         | 11.9                                    | 1                                                | X                                                                                                   |
| SMCJ85A-HR        | SMCJ85CA-HR      | GGV     | BGV | 85.0                                    | 94.40                                      | 104.00 | 1                       | 137.0                                         | 11.0                                    | 1                                                | X                                                                                                   |
| SMCJ90A-HR        | SMCJ90CA-HR      | GGX     | BGX | 90.0                                    | 100.00                                     | 111.00 | 1                       | 146.0                                         | 10.3                                    | 1                                                | X                                                                                                   |
| SMCJ100A-HR       | SMCJ100CA-HR     | GGZ     | BGZ | 100.0                                   | 111.00                                     | 123.00 | 1                       | 162.0                                         | 9.3                                     | 1                                                | X                                                                                                   |
| SMCJ110A-HR       | SMCJ110CA-HR     | GHE     | BHE | 110.0                                   | 122.00                                     | 135.00 | 1                       | 177.0                                         | 8.5                                     | 1                                                | X                                                                                                   |
| SMCJ120A-HR       | SMCJ120CA-HR     | GHG     | BHG | 120.0                                   | 133.00                                     | 147.00 | 1                       | 193.0                                         | 7.8                                     | 1                                                | X                                                                                                   |
| SMCJ130A-HR       | SMCJ130CA-HR     | GHK     | BHK | 130.0                                   | 144.00                                     | 159.00 | 1                       | 209.0                                         | 7.2                                     | 1                                                | X                                                                                                   |
| SMCJ150A-HR       | SMCJ150CA-HR     | GHM     | BHM | 150.0                                   | 167.00                                     | 185.00 | 1                       | 243.0                                         | 6.2                                     | 1                                                | X                                                                                                   |
| SMCJ154A-HR       | SMCJ154CA-HR     | GHN     | BHN | 154                                     | 172                                        | 190    | 1                       | 249                                           | 6.1                                     | 1                                                | -                                                                                                   |
| SMCJ160A-HR       | SMCJ160CA-HR     | GHP     | BHP | 160.0                                   | 178.00                                     | 197.00 | 1                       | 259.0                                         | 5.8                                     | 1                                                | X                                                                                                   |
| SMCJ170A-HR       | SMCJ170CA-HR     | GHR     | BHR | 170.0                                   | 189.00                                     | 209.00 | 1                       | 275.0                                         | 5.5                                     | 1                                                | X                                                                                                   |

**Note:**

1. Each lot of parts will pass group B test requirement.

### Screen Process



|                                                                                                            |                                   |
|------------------------------------------------------------------------------------------------------------|-----------------------------------|
| 100% vision inspection                                                                                     | MIL-STD-750 method 2074           |
| 100%High Temperature Storage Life (168hrs,150C)                                                            | MIL-STD-750 method 1031           |
| 100% X-RAY inspection                                                                                      | MIL-STD-750 method 2076           |
| 100% Temperature cycle test (-55-150C, 20 cycles, dwell time 15 min)                                       | MIL-STD-750 method 1051           |
| 100% Reflow (2X)                                                                                           | JEDEC J-STD-020                   |
| 100% surge test (2x)                                                                                       | MIL-STD-750 method 4066           |
| 100% HTRB(150C, Bias=VR(80% breakdown voltage), 96hrs),for Bi-direction products, 96hrs for each direction | MIL-STD-750 method 1038           |
| Final electrical test( 100% 3 sigma limit, 100% dynamic test and PAT limit)                                | MIL-STD-750 method 4016.4021.4011 |

**Note:** Up-screen program can be specified by customer's request via contacting Littelfuse service

### Group B Test Requirement

| Screen           | Method                              | Condition                                                           | Requirement                                                                                                   |
|------------------|-------------------------------------|---------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|
| Surge test       | 10/1000 $\mu$ s Peak Pluse Waveform | Maximum Clamping Voltage ( $V_C$ ) @ Peak Plus Current ( $I_{pp}$ ) | Sample size 45 perform 10x<br>Accept 0 failures                                                               |
| Burn - In (HTRB) | MIL -STD-750, Method 1038.5         | Applied Voltage<br>100% $V_R$ @150°C                                | Sample size 45<br>340 hours (680 hours for bi-direction products, each direction 340 hours) Accept 0 failures |
| Electrical test  | --                                  | $I_R$ @ $V_R$ , $V_{BR}$ @ $I_T$                                    | Sample size 45<br>Accept 0 failures                                                                           |


### I-V Curve Characteristics




**$P_{PPM}$  Peak Pulse Power Dissipation** -- Max power dissipation  
 **$V_R$  Stand-off Voltage** -- Maximum voltage that can be applied to the TVS without operation  
 **$V_{BR}$  Breakdown Voltage** -- Maximum voltage that flows through the TVS at a specified test current ( $I_T$ )  
 **$V_C$  Clamping Voltage** -- Peak voltage measured across the suppressor at a specified  $I_{ppm}$  (peak impulse current)  
 **$I_R$  Reverse Leakage Current** -- Current measured at  $V_R$   
 **$V_F$  Forward Voltage Drop for Uni-directional**

### Ratings and Characteristic Curves ( $T_A=25^\circ\text{C}$ unless otherwise noted)


**Figure 1 - TVS Transients Clamping Waveform**




**Figure 2 - Peak Pulse Power Rating**




**Figure 3 - Pulse Derating Curve**




**Figure 4 - Pulse Waveform**




**Figure 5 - Typical Junction Capacitance**



**Figure 6 - Steady State Power Dissipation Derating Curve**




**Figure 7 - Maximum Non-Repetitive Peak Forward Surge Current Uni-Directional Only**



### Soldering Parameters

|                                                                        |                                    |                    |
|------------------------------------------------------------------------|------------------------------------|--------------------|
| <b>Reflow Condition</b>                                                |                                    | Lead-free assembly |
| <b>Pre Heat</b>                                                        | - Temperature Min ( $T_{s(min)}$ ) | 150°C              |
|                                                                        | - Temperature Max ( $T_{s(max)}$ ) | 200°C              |
|                                                                        | - Time (min to max) ( $t_s$ )      | 60 – 180 secs      |
| <b>Average ramp up rate (Liquidus Temp (<math>T_L</math>) to peak)</b> |                                    | 3°C/second max     |
| <b><math>T_{s(max)}</math> to <math>T_L</math> - Ramp-up Rate</b>      |                                    | 3°C/second max     |
| <b>Reflow</b>                                                          | - Temperature ( $T_L$ ) (Liquidus) | 217°C              |
|                                                                        | - Time (min to max) ( $t_s$ )      | 60 – 150 seconds   |
| <b>Peak Temperature (<math>T_p</math>)</b>                             |                                    | 260 $^{+0/-5}$ °C  |
| <b>Time within 5°C of actual peak Temperature (<math>t_p</math>)</b>   |                                    | 20 – 40 seconds    |
| <b>Ramp-down Rate</b>                                                  |                                    | 6°C/second max     |
| <b>Time 25°C to peak Temperature (<math>T_p</math>)</b>                |                                    | 8 minutes Max.     |
| <b>Do not exceed</b>                                                   |                                    | 280°C              |




### Physical Specifications

|                 |                                                                   |
|-----------------|-------------------------------------------------------------------|
| <b>Weight</b>   | 0.007 ounce, 0.21 grams                                           |
| <b>Case</b>     | JEDEC DO214AB. Molded plastic body over glass passivated junction |
| <b>Polarity</b> | Color band denotes positive end (cathode) except Bidirectional.   |
| <b>Terminal</b> | Matte Tin-plated leads, Solderable per JESD22-B102                |

### Environmental Specifications


|                           |                          |
|---------------------------|--------------------------|
| <b>High Temp. Storage</b> | JESD22-A103              |
| <b>HTRB</b>               | JESD22-A108              |
| <b>Thermal Shock</b>      | JESD22-A106              |
| <b>MSL</b>                | JEDEC-J-STD-020, Level 1 |
| <b>H3TRB</b>              | JESD22-A101              |
| <b>RSH</b>                | JESD22-B106              |

### Dimensions




| Dimensions | Inches |       | Millimeters |       |
|------------|--------|-------|-------------|-------|
|            | Min    | Max   | Min         | Max   |
| A          | 0.114  | 0.126 | 2.900       | 3.200 |
| B          | 0.260  | 0.280 | 6.600       | 7.110 |
| C          | 0.220  | 0.245 | 5.590       | 6.220 |
| D          | 0.079  | 0.103 | 2.060       | 2.620 |
| E          | 0.030  | 0.060 | 0.760       | 1.520 |
| F          | 0.002  | 0.008 | 0.051       | 0.203 |
| G          | 0.305  | 0.320 | 7.750       | 8.130 |
| H          | 0.006  | 0.012 | 0.152       | 0.305 |
| I          | 0.129  | -     | 3.300       | -     |
| J          | 0.094  | -     | 2.400       | -     |
| K          | -      | 0.165 | -           | 4.200 |
| L          | 0.094  | -     | 2.400       | -     |

### Part Numbering System





### Part Marking System



### Packaging

| Part number  | Component Package | Quantity | Packaging Option                | Packaging Specification |
|--------------|-------------------|----------|---------------------------------|-------------------------|
| SMCJxxxXX-HR | DO-214AB          | 500      | Tape & Reel – 16mm tape/7" reel | EIA STD RS-481          |

### Tape and Reel Specification



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[SMCJ8.5CA-HR](#) [SMCJ7.5A-HR](#) [SMCJ8.5A-HR](#) [SMCJ5.0A-HR](#) [SMCJ6.5A-HR](#) [SMCJ6.0A-HR](#) [SMCJ7.5CA-HR](#)  
[SMCJ8.0CA-HR](#) [SMCJ5.0CA-HR](#) [SMCJ6.5CA-HR](#) [SMCJ7.0A-HR](#) [SMCJ6.0CA-HR](#) [SMCJ9.0CA-HR](#) [SMCJ7.0CA-](#)  
[HR](#) [SMCJ8.0A-HR](#) [SMCJ9.0A-HR](#) [SMCJ130CA-HR](#) [SMCJ130A-HR](#) [SMCJ13CA-HR](#) [SMCJ13A-HR](#) [SMCJ64CA-HR](#)  
[SMCJ43CA-HR](#) [SMCJ64A-HR](#) [SMCJ78A-HR](#) [SMCJ51CA-HR](#) [SMCJ48A-HR](#) [SMCJ17CA-HR](#) [SMCJ110A-HR](#)  
[SMCJ100CA-HR](#) [SMCJ170A-HR](#) [SMCJ15CA-HR](#) [SMCJ20A-HR](#) [SMCJ28CA-HR](#) [SMCJ75CA-HR](#) [SMCJ40A-HR](#)  
[SMCJ36CA-HR](#) [SMCJ70A-HR](#) [SMCJ28A-HR](#) [SMCJ150CA-HR](#) [SMCJ60CA-HR](#) [SMCJ90A-HR](#) [SMCJ85A-HR](#)  
[SMCJ18CA-HR](#) [SMCJ58CA-HR](#) [SMCJ24A-HR](#) [SMCJ12A-HR](#) [SMCJ110CA-HR](#) [SMCJ14CA-HR](#) [SMCJ12CA-HR](#)  
[SMCJ90CA-HR](#) [SMCJ54CA-HR](#) [SMCJ45A-HR](#) [SMCJ48CA-HR](#) [SMCJ160CA-HR](#) [SMCJ26A-HR](#) [SMCJ26CA-HR](#)  
[SMCJ11A-HR](#) [SMCJ22CA-HR](#) [SMCJ24CA-HR](#) [SMCJ20CA-HR](#) [SMCJ54A-HR](#) [SMCJ33A-HR](#) [SMCJ75A-HR](#)  
[SMCJ78CA-HR](#) [SMCJ30A-HR](#) [SMCJ11CA-HR](#) [SMCJ10CA-HR](#) [SMCJ10A-HR](#) [SMCJ43A-HR](#) [SMCJ100A-HR](#)  
[SMCJ120CA-HR](#) [SMCJ36A-HR](#) [SMCJ30CA-HR](#) [SMCJ58A-HR](#) [SMCJ45CA-HR](#) [SMCJ51A-HR](#) [SMCJ33CA-HR](#)  
[SMCJ22A-HR](#) [SMCJ150A-HR](#) [SMCJ85CA-HR](#) [SMCJ70CA-HR](#) [SMCJ40CA-HR](#) [SMCJ60A-HR](#) [SMCJ14A-HR](#)  
[SMCJ160A-HR](#) [SMCJ16A-HR](#) [SMCJ170CA-HR](#) [SMCJ15A-HR](#) [SMCJ18A-HR](#) [SMCJ16CA-HR](#) [SMCJ120A-HR](#)  
[SMCJ17A-HR](#)