


CK ROTARY SWITCH


ELECTRICAL & MECHANICAL SPECIFICATION

Switch Rating:	1A @ 24V ac/dc	Life:	>10,000 Cycles
Proof Voltage:	1,500V ac (Initial)	Operating Torque (nominal):	Standard 8.6 ±1 cNm
Insulation Resistance:	>999 MΩ at 500V dc (Initial)		Light Action 3.5 ± 0.5 cNm
Contact Resistance	<20 mΩ (Initial)	End Stop Torque (nominal):	0.80 Nm
Contact/Terminal Material:	Brass CZ108 Ag Plated	Moulding Material:	Polyamide 6.6 G.F
Operating Temperature:	-30°C to +85°C		

FEATURES

Single wafer switch	Shorting (make before break 30° indexing only) or non-shorting (break before make)	Solder or PCB terminals
Maximum 12 positions		Gold flashed or gold plated terminals/contacts available
Up to 4 poles per switch	Moulded stop or adjustable stops to restrict number of positions	
Standard 30° indexing, 60° and 90° available	Continuous rotation also available	Spindles with special flats, slots or knurls
Moulded 27.5mm diameter	Made in UK	Rear drive versions
	UL-V0 rated material available	No bush versions





SPINDLE FLAT ANGLE - AVAILABLE IN 15° INCREMENTS

SCREWDRIVER SLOT - AVAILABLE IN 45° INCREMENTS



ORDERING CODE FOR NON-STANDARD SWITCHES

C K									
SPINDLE LENGTH FMF IN FULL MM									
Index Angles & NO. OF POLES	NO OF WAYS (POSITIONS)	MBB or BBM	Contact Type	Contact Plating	SPINDLE DIAM.	SPINDLE FLAT DEPTH	BUSH DIAM.	LENGTH OF SPINDLE FLAT	ANGLE OF FLAT (°)
A 30° 1 Pole	A 2	A BBM	Solder	SILVER	A 6mm	Nil	M10	A 2 N 15	A 0 N 195
B 2	B 3	B MBB*	Solder		B 6mm	5mm	M10	B 3 O No Flat	B 15 O
C 3	C 4	C BBM	PCB		C 6.35mm	Nil	9.52 mm	C 4 P 16	C 30 P 210
D 4	D 5	D MBB*	PCB		D 6.35mm	5.5mm	9.52 mm	D 5 Q 17	D 45 Q 225
E 60° 1 Pole	E 6	E BBM	Solder	GOLD PLATE				E 6 R 18	E 60 R 240
F 2	F 7	F MBB*	Solder					F 7 S 19	F 75 S 255
G 3	G 8	G BBM	PCB					G 8 T 20	G 90 T 270
H 4	H 9	H MBB*	PCB					H 9 U 21	H 105 U 285
I 90° 1 Pole	I 10	I BBM	Solder	GOLD FLASH				I 10 V 22	I 120 V 300
J 2	J 11	J MBB*	Solder					J 11 W 23	J 135 W 315
K 3	K 12	K BBM	PCB					K 12 X 24	K 150 X 330
	Z No Stop	L MBB*	PCB					L 13 Y 25	L 165 Y 345
								M 14 Z Full	M 180


*30° INDEX ANGLE ONLY

STANDARD PART NUMBERS

BASIC TYPES	SPINDLE DIAMETER	SPINDLE LENGTH FROM MOUNTING FACE	8mm LONG BUSH	SPINDLE FLAT LENGTH	ANGLE OF SPINDLE FLAT	SPINDLE FLAT THICKNESS
IMPERIAL	6.35mm	38mm	9.52 x 32 TPI	30mm	90°	5.5mm
METRIC	6.00mm	50mm	M10 x 0.75	No Flat	-	-

CIRCUITRY AT 30° INDEXING	STANDARD METRIC			STANDARD IMPERIAL	
	PLATING FINISH	Shorting (MBB)	Non- Shorting (BBM)	Shorting (MBB)	Non- Shorting (BBM)
1 POLE 12 POSITION	STOP INCLUDED				
Solder Tag	Silver	CK1039	CK1029	CK1034	CK1024
	Gold Flash	CK1508	CK1503	CK1516	CK1520
	Gold Plate	CK2444	CK1672	CK2458	CK2459
Printed Circuit Board	Silver	CK1059	CK1049	CK1054	CK1044
	Gold Flash	CK1512	CK1506	CK1524	CK1528
	Gold Plate	CK1475	CK1312	CK2460	CK2461
1 POLE 12 POSITION	CONTINUOUS ROTATION				
Solder Tag	Silver	CK1038	CK1028	CK1033	CK1023
	Gold Flash	CK1533	CK1537	CK1541	CK1545
	Gold Plate	CK2445	CK2446	CK2462	CK2463
Printed Circuit Board	Silver	CK1058	CK1048	CK1053	CK1043
	Gold Flash	CK1534	CK1538	CK1542	CK1546
	Gold Plate	CK2447	CK2448	CK2464	CK2465
2 POLE 6 POSITION	STOP INCLUDED				
Solder Tag	Silver	CK1040	CK1030	CK1035	CK1025
	Gold Flash	CK1509	CK1496	CK1517	CK1521
	Gold Plate	CK2449	CK1726	CK2466	CK2467
Printed Circuit Board	Silver	CK1060	CK1050	CK1055	CK1045
	Gold Flash	CK1513	CK1473	CK1525	CK1529
	Gold Plate	CK2450	CK1850	CK2468	CK2469
2 POLE 6 POSITION	CONTINUOUS ROTATION				
Solder Tag	Silver	CK1114	CK1118	CK1120	CK1121
	Gold Flash	CK1535	CK1539	CK1543	CK1547
	Gold Plate	CK2451	CK2452	CK2470	CK2471
Printed Circuit Board	Silver	CK1119	CK1113	CK1122	CK1089
	Gold Flash	CK1536	CK1540	CK1544	CK1548
	Gold Plate	CK2453	CK2454	CK2472	CK2473
3 POLE 4 POSITION	STOP INCLUDED				
Solder Tag	Silver	CK1041	CK1031	CK1036	CK1026
	Gold Flash	CK1510	CK1504	CK1518	CK1522
	Gold Plate	CK2455	CK1577	CK2474	CK2475
Printed Circuit Board	Silver	CK1061	CK1051	CK1056	CK1046
	Gold Flash	CK1514	CK1500	CK1526	CK1530
	Gold Plate	CK2456	CK1952	CK2476	CK2477
4 POLE 3 POSITION	STOP INCLUDED				
Solder Tag	Silver	CK1042	CK1032	CK1037	CK1027
	Gold Flash	CK1511	CK1505	CK1519	CK1523
	Gold Plate	CK1673	CK1822	CK2478	CK2479
Printed Circuit Board	Silver	CK1062	CK1052	CK1057	CK1047
	Gold Flash	CK1515	CK1507	CK1527	CK1531
	Gold Plate	CK2457	CK1953	CK2480	CK2481

CUSTOMER TO COMPLETE OR DELETE AS REQUIRED



	A	B	C
IMPERIAL	Ø6.35		Ø9.52 x 32TPI
METRIC	Ø6.00		M10 x 0.75

	D	E	F
IMPERIAL			
METRIC			

INDEXING				INDEXING				INDEXING				INDEXING			
1 POLE				2 POLE				3 POLE				4 POLE			
POSITIONS				POSITIONS				POSITIONS				POSITIONS			
MBB	BBM	SOL	PCB	MBB	BBM	SOL	PCB	MBB	BBM	SOL	PCB	MBB	BBM	SOL	PCB
IMPORTANT! WAFERS FLATS & SLOTS VIEWED FROM THE FRONT OF SWITCH IN EXTREME ANTICLOCKWISE POSITION (POSITION 1)															
SPECIAL REQUIREMENTS				OPTIONS Stops are adjustable 2-12 positions. Continuous rotation (No Stops) available. Make before break (MBB) or Break before Make (BBM) rotors available. Solder Tag (SOL) or PCB pin (PCB) – indicate on wafer.											
CUSTOMER:				DATE:				CUSTOMER REFERENCE NUMBER:							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lorlin:

CK1028	CK1033	CK1036	CK1037	CK1038	CK1039	CK1040	CK1041	CK1042	CK1048	CK1050	CK1051
CK1052	CK1053	CK1058	CK1089	CK1113	CK1114	CK1118	CK1119	CK1120	CK1121	CK1122	CK1312
CK1473	CK1475	CK1496	CK1500	CK1503	CK1504	CK1505	CK1506	CK1507	CK1508	CK1509	CK1510
CK1511	CK1512	CK1513	CK1514	CK1515	CK1516	CK1517	CK1518	CK1519	CK1520	CK1521	CK1522
CK1523	CK1524	CK1526	CK1528	CK1530	CK1531	CK1533	CK1534	CK1535	CK1536	CK1537	CK1538
CK1539	CK1540	CK1541	CK1542	CK1543	CK1544	CK1545	CK1546	CK1547	CK1548	CK1577	CK1672
CK1673	CK1726	CK1822	CK1850	CK1952	CK1953	CK2444	CK2445	CK2446	CK2447	CK2448	CK2449
CK2450	CK2451	CK2452	CK2453	CK2454	CK2455	CK2456	CK2457	CK2458	CK2459	CK2460	CK2461
CK2462	CK2463	CK2464	CK2465								