


**Sales Outline Drawing**Revision **B****May not be suitable for all medical and aerospace applications.****Specifications: Contact Mallory Sonalert to discuss your application.**

Impedance ( $\Omega$ )	$8 \pm 15\%$ at 1000 Hz at 1.0V
Rated Power (W)	0.3
Max Power (W)	0.5
Resonance Freq Fo (Hz)	$560 \pm 20\%$ at 1.0V
Frequency Range (Hz)	Fo ~ 7000
Output S.P.L. (dB)	$92 \pm 3$ at .3w/.1m 1.0k, 1.2k, 1.5k, 2.0kHz $78 \pm 3$ at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHz
Magnet Size (mm)	$\varnothing 8.0 \times 1.0$
Magnet	Nd-Fe-B
Frame Material	Metal
Operating Temp	-20 to 55°C
Weight (g)	2.3
Options	For other options contact factory

**Dimensions:  $\pm 0.5$**  (units: mm)**ROHS Compliant**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PSR20N08AK](#)