


**May not be suitable for all medical and aerospace applications.  
Specifications: Contact Mallory Sonalert to discuss your application.**

Impedance ( $\Omega$ )	$50 \pm 15\%$ at 1000 Hz at 1.0 V
Rated Power (W)	0.6
Max Power (W)	1.0
Resonance Freq $F_0$ (Hz)	$500 \pm 15\%$ at 1.0 V
Frequency Range (Hz)	$F_0 \sim 10000$
Output S.P.L. (dB)	$96 \pm 3$ at .6w/.1m 0.8k, 1.0k, 1.2k, 1.5kHz $78 \pm 3$ at 1w/1m 0.8k, 1.0k, 1.2k, 1.5kHz
Frame Material	Metal
Operating Temp	-40 to 85°C
Weight (g)	3.6
Options	For other options contact factory

**Dimensions:  $\pm 0.3$**  (units: mm)

**ROHS Compliant**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PSR23N50AK](#)