


DATE	REVISIONS	REV
8-9-93	CHG'D LEAD LENGTHS/	A
8-27-93	CHG'D LEAD LENGTHS/	B
8-19-94	CHG'D HOLDER BOTTOM & SAFE OP. SPECS./	C
11-29-94	UPDATED SPECS./	D
2-8-95	CHG'D. HOLDER BOTTOM./	E
10-9-95	REF ECN 10100./	F
2-6-96	REF ECN 10104./	G

DRAWING NUMBER SSF-LXH240LIID	REV G
----------------------------------	----------

ELECTRO-OPTICAL CHARACTERISTICS TA=25 °C If=20mA

PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		635 (RED)		nm	
FORWARD VOLTAGE		2.0	2.8	V _f	
REVERSE VOLTAGE	5.0			V _r	I _r =100uA
AXIAL INTENSITY		15		mcd	I _f =20mA
		1.0		mcd	I _f =2mA
VIEWING ANGLE		80		2x theta	
EMITTED COLOR:		RED			
EPOXY LENS FINISH:		RED DIFFUSED			



LIMITS OF SAFE OPERATION AT 25 DEG. C

PARAMETER	MAX	UNITS
Ⓓ PEAK FORWARD CURRENT*	150	mA
STEADY CURRENT	30	mA
Ⓓ POWER DISSIPATION	105	mW
DERATE FROM 25 °C	-1.6	mW/ °C
Ⓒ OPERATING, STORAGE TEMP.	-40 TO +85	°C
Ⓒ LEAD SOLDERING TEMP.	+260	°C
Ⓒ 2.0mm FROM BODY		3 SEC. MAX

* t<10μs

BILL OF MATERIALS:

- SSH-LXH240 HOLDER. MATERIAL: BLACK NYLON 94V-0.
- SSL-LX3044LID LED (2 PIECES).

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

SS/MS

LUMEX OPTO COMPONENTS INC.		292 E. HELLEN ROAD PALATINE, ILLINOIS 60067 (708) 359-2790	
CONFIDENTIAL INFORMATION THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX OPTO/COMPONENTS, INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX OPTO/COMPONENTS, INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.			
DATE: 1-12-93	DWN:	CHK'D:	APPD:
SCALE: N/A			
T-3mm LED, RIGHT ANGLE FAULT INDICATOR, RED DIFFUSED, SPECIAL LOW CURRENT SELECTION			
PAGE 1 OF 1	DRAWING NUMBER SSF-LXH240LIID		REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumex:](#)

[SSF-LXH240LIID](#)