





PART NUMBER	SSL-LX5093SRC/X	REV.	F
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV.
01.05.95	UPDATED SPECS.		A
09.30.96	E.C.N. #10251.		B
05.31.01	E.C.N. #10BRDR. & REDRAWN IN 3D.		C
09.13.01	E.C.N. #10788.		D
10.25.06	E.C.N. #11148.		E
09.27.12	E.C.N. #10BRDR. & REDRAWN.		F

ELECTRO-OPTICAL CHARACTERISTICS Ta=25°C If=20mA					
PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		660		nm	
FORWARD VOLTAGE		1.7	2.2	Vf	
REVERSE VOLTAGE	4.0			Vr	Ir=100μA
AXIAL INTENSITY	/DU 1000	1200		mcd	If=20mA
	/DV 1300	1500		mcd	If=20mA
	/DW 1600	1800		mcd	If=20mA
	/E 2000	2800		mcd	If=20mA
	/F 3500	4000		mcd	If=20mA
VIEWING ANGLE		30		2x theta	
EMITTED COLOR:	RED				
EPOXY LENS FINISH:	WATER CLEAR				

LIMITS OF SAFE OPERATION AT 25°C		
PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT*	150	mA
STEADY CURRENT	30	mA
POWER DISSIPATION	100	mW
DERATE FROM 25°C	-1.2	mW/°C
OPERATING TEMP.	-40 TO +85	°C
STORAGE TEMP.	-40 TO +85	°C
SOLDERING TEMP.	+260	°C
2.0mm FROM BODY	3	SEC.

* t<10μS

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= ^{+DECIMAL PRECISION} _{-0.00} MAX= ^{+0.00} _{-DECIMAL PRECISION}

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSL-LX5093SRC/DV](#) [SSL-LX5093SRC/DW](#) [SSL-LX5093SRC/DU](#)