

Features

- Low $V_{ce(sat)}$, Fast Switching
- $V_{ce(sat)}$ with Positive Temperature Coefficient
- High Ruggedness, Good Thermal Stability
- Very Tight Parameter Distribution
- Halogen Free. "Green" Device (Note 1)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings


- Operating Junction Temperature Range : -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- IGBT Thermal Resistance: 0.45°C/W Junction to Case
- Diode Thermal Resistance: 0.6°C/W Junction to Case
- Thermal Resistance: 40°C/W Junction to Ambient

Parameter	Symbol	Rating	Unit
Collector-Emitter Voltage	V_{CE}	1200	V
DC Collector Current ⁽²⁾	$T_C=25^\circ\text{C}$	80	A
	$T_C=100^\circ\text{C}$	40	
Pulsed Collector Current ⁽³⁾	$I_{C,pluse}$	160	A
Diode Forward Current ⁽²⁾	$T_C=25^\circ\text{C}$	80	A
	$T_C=100^\circ\text{C}$	40	
Diode Pulsed Current ⁽³⁾	$I_{F,pluse}$	160	A
Gate-Emitter Voltage	V_{GE}	±20	V
Transient Gate-Emitter Voltage ⁽⁴⁾		±30	
Short Circuit Withstand Time ⁽⁵⁾ $V_{GE}=15\text{V}, V_{CC}=600\text{V}, T_J \leq 150^\circ\text{C}$	t_{SC}	10	μs
Power Dissipation	$T_C=25^\circ\text{C}$	277	W
	$T_C=100^\circ\text{C}$	111	

Note:


1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. Limited by T_{Jmax} .
3. T_p limited by T_{Jmax} .
4. $T_p \leq 10\mu\text{s}$, Duty Cycle < 1%
5. Allowed number of short circuits: <1000; time between short circuits: >1s.

Internal Structure



Trench and Field Stop IGBT 1200V 40A

TO-247



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.787	0.866	20.00	22.00	
B	0.598	0.638	15.20	16.20	
C	0.185	0.208	4.70	5.30	
D	0.035	0.059	0.90	1.50	
E	0.059	0.094	1.50	2.40	
F	0.067	0.091	1.70	2.30	
J	0.019	0.031	0.48	0.80	
K	0.748	0.833	19.00	21.15	
P	0.122	0.189	3.10	4.80	
Q	0.118	0.150	3.00	3.80	Φ
V	0.106	0.134	2.70	3.40	
G	0.197	0.224	5.00	5.70	

Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Collector-Emitter Breakdown Voltage	V _{(BR)CES}	V _{GE} =0V, I _C =0.25mA	1200			V
Collector-Emitter Saturation Voltage	V _{CE(sat)}	V _{GE} =15V, I _C =40A		1.85	2.2	V
Diode Forward Voltage	V _F	V _{GE} =0V, I _F =20A		2.3		V
G-E Threshold Voltage	V _{GE(th)}	I _C =1mA, V _{CE} =V _{GE}	5	6	7	V
C-E Leakage Current	I _{CES}	V _{CE} =1200V, V _{GE} =0V			0.1	mA
		V _{CE} =1200V, V _{GE} =0V, T _J =150°C			4	
G-E Leakage Current	I _{GES}	V _{CE} =0V, V _{GE} =20V			250	nA
Transconductance	g _{FS}	V _{CE} =20V, I _C =40A		20		S
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{CE} =30V, V _{GE} =0V, f=1MHz		3129		pF
Output Capacitance	C _{oss}			166		
Reverse Transfer Capacitance	C _{rss}			93		
Gate Charge	Q _g	V _{CC} =600V, I _C =40A, V _{GE} =15V		240		nC
IGBT Switching Characteristics						
Turn-On Delay Time	t _{d(on)}	V _{CC} =600V, I _C =40A, V _{GE} =-15/15V, R _G =10Ω, Inductive load		160		ns
Rise Time	t _r			84		
Turn-Off Delay Time	t _{d(off)}			237		
Fall Time	t _f			164		
Turn-On Energy	E _{on}			5.02		mJ
Turn-Off Energy	E _{off}			2.72		
Total Switching Energy	E _{ts}			7.74		
Diode Characteristics						
Reverse Recovery Time	t _{rr}	V _R =600V, I _F =40A, di _F /dt=292A/μs		367		ns
Reverse Recovery Charge	Q _{rr}			1.79		μC
Peak Reverse Recovery Current	I _{rrm}			10.4		A

Curve Characteristics

Fig. 1 - Typical Output Characteristics




Fig. 2 - Gate Charge




Fig. 3 - Capacitance Characteristics





Fig. 4 - Power Derating Curve



Ordering Information

Device	Packing
Part Number-BP	Tube: 30pcs/Tube, 1800pcs/Ctn

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[MIW40N120F-BP](#)