

Features

- Low switching losses
- Maximum junction temperature 175°C
- Positive temperature coefficient
- High ruggedness, temperature stable
- High short circuit capability(5μs)
- Halogen Free. "Green" Device (Note 1)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)

Applications

- High frequency switching application
- Medical applications
- Uninterruptible power supply
- Motion/servo control

Maximum Ratings


- Operating Junction Temperature Range : -40°C to +175°C
- Storage Temperature Range: -55°C to +150°C
- IGBT Thermal Resistance: 0.42°C/W Junction to Case
- Diode Thermal Resistance: 1.05°C/W Junction to Case
- Thermal Resistance: 40°C/W Junction to Ambient

Parameter		Symbol	Rating	Unit
Collector-Emitter Voltage		V_{CE}	650	V
DC Collector Current ⁽²⁾	$T_C=25^{\circ}\text{C}$	I_C	100	A
	$T_C=100^{\circ}\text{C}$		50	
Pulsed Collector Current ⁽³⁾ $V_{GE}=15\text{V}$		I_{CM}	200	A
Diode Forward Current ⁽²⁾	$T_C=25^{\circ}\text{C}$	I_F	60	A
	$T_C=100^{\circ}\text{C}$		30	
Diode Pulsed Current ⁽³⁾		$I_{F,puls}$	120	A
Gate-Emitter Voltage		V_{GE}	± 20	V
Transient Gate-Emitter Voltage			± 30	
Short Circuit Withstand Time $V_{GE}=15\text{V}, V_{CC}=400\text{V}, V_{CEM}\leq 650\text{V}$		t_{SC}	5	μs
Power Dissipation	$T_J=25^{\circ}\text{C}$	P_D	357	W

Note:


1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. Limited by T_{Jmax} .
3. T_p limited by T_{Jmax} .

Internal Structure



Trench and Field Stop IGBT 650V 50A

TO-247AB



DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.189	0.205	4.80	5.20	
A1	0.087	0.103	2.21	2.61	
A2	0.073	0.085	1.85	2.15	
b	0.039	0.055	1.00	1.40	
b2	0.075	0.087	1.91	2.21	
C	0.020	0.028	0.50	0.70	
D	0.815	0.839	20.70	21.30	
D1	0.640	0.663	16.25	16.85	
E	0.610	0.634	15.50	16.10	
E1	0.512	0.535	13.00	13.60	
E2	0.189	0.205	4.80	5.20	
E3	0.091	0.106	2.30	2.70	
L	0.772	0.796	19.62	20.22	
L1	-	0.169	-	4.30	
P	0.134	0.150	3.40	3.80	Φ
P1		0.287	-	7.30	Φ
S	0.242		6.15		TYP
H1	0.214		5.44		TYP
b3	0.110	0.126	2.80	3.20	





Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Collector-Emitter Breakdown Voltage	$V_{(BR)CES}$	$V_{GE}=0V, I_C=250\mu A$	650			V
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$V_{GE}=15V, I_C=50A, T_J=25^\circ C$		1.95	2.40	V
		$V_{GE}=15V, I_C=50A, T_J=125^\circ C$		2.30		
		$V_{GE}=15V, I_C=50A, T_J=150^\circ C$		2.40		
G-E Threshold Voltage	$V_{GE(th)}$	$I_C=800\mu A, V_{GE}=V_{CE}$	4.5	5.0	5.5	V
C-E Leakage Current	I_{CES}	$V_{CE}=650V, V_{GE}=0V, T_J=25^\circ C$			0.25	mA
		$V_{CE}=650V, V_{GE}=0V, T_J=150^\circ C$			4.00	
G-E Leakage Current	I_{GES}	$V_{CE}=0V, V_{GE}=\pm 20V$			100	nA
Dynamic Characteristics						
Input Capacitance	C_{ies}	$V_{CE}=25V, V_{GE}=0V, f=1MHz$		2.07		nF
Reverse Transfer Capacitance	C_{res}			0.83		
Gate Charge	Q_g	$V_{CC}=300V, I_C=50A, V_{GE}=15V$		0.21		μC
Short Circuit Collector Current	I_{sc}	$V_{GE}=15V, t_{sc}\leq 5\mu s, V_{CC}=400V, T_J\leq 150^\circ C$		250		A
IGBT Switching Characteristics						
Turn-On Delay Time	$t_{d(on)}$	$V_{CC}=300V, I_C=50A, V_{GE}=-15\sim 15V, R_G=20\Omega, L_s=60nH$		28		ns
Rise Time	t_r			50		
Turn-Off Delay Time	$t_{d(off)}$			129		
Fall Time	t_f			51		
Turn-On Energy	E_{on}	$V_{CC}=300V, I_C=50A, V_{GE}=-15\sim 15V, R_G=20\Omega, L_s=60nH, T_J=125^\circ C$		1.49		mJ
Turn-Off Energy	E_{off}			0.67		
Turn-On Delay Time	$t_{d(on)}$			35		ns
Rise Time	t_r			60		
Turn-Off Delay Time	$t_{d(off)}$			220		
Fall Time	t_f			60		
Turn-On Energy	E_{on}	$V_{CC}=300V, I_C=50A, V_{GE}=-15\sim 15V, R_G=20\Omega, L_s=60nH, T_J=150^\circ C$		2.21		mJ
Turn-Off Energy	E_{off}			1.02		
Turn-On Delay Time	$t_{d(on)}$			38		ns
Rise Time	t_r			64		
Turn-Off Delay Time	$t_{d(off)}$			230		
Fall Time	t_f			63		
Turn-On Energy	E_{on}			2.54		mJ
Turn-Off Energy	E_{off}			1.15		





Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Diode Static Characteristics						
Diode Forward Voltage	V _F	I _F =30A, T _J =25℃		2.00	2.50	V
		I _F =30A, T _J =125℃		1.95		
		I _F =30A, T _J =150℃		1.95		
Diode Dynamic Characteristics						
Reverse Recovery Current	I _{rr}	V _R =300V, I _F =50A, di/dt=-437A/μs, T _J =25℃		5		A
Reverse Recovery Charge	Q _{rr}			0.09		μC
Diode Reverse Recovery Time	t _{rr}			35		ns
Reverse Recovery Energy	E _{rec}			0.03		mJ
Reverse Recovery Current	I _{rr}	V _R =300V, I _F =50A, di/dt=-437A/μs, T _J =125℃		7.2		A
Reverse Recovery Charge	Q _{rr}			0.18		μC
Diode Reverse Recovery Time	t _{rr}			70		ns
Reverse Recovery Energy	E _{rec}			0.06		mJ
Reverse Recovery Current	I _{rr}	V _R =300V, I _F =50A, di/dt=-437A/μs, T _J =150℃		8.4		A
Reverse Recovery Charge	Q _{rr}			0.20		μC
Diode Reverse Recovery Time	t _{rr}			78		ns
Reverse Recovery Energy	E _{rec}			0.07		mJ



Curve Characteristics



Curve Characteristics



Curve Characteristics



Ordering Information

Device	Packing
Part Number-BP	Tube: 30pcs/Tube, 1800pcs/Ctn

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[MIW50N65RA-BP](#)