


LED Indicators ~ Panel ~ Dome Lens



SSI-LXR3612XX-150 Series

T-3mm Chrome Indicator, Protruded LED, 6" Leads



FEATURES / OPTIONS

- ▶ State-of-the-Art, High Brightness LED Chip Technology
- ▶ Choice of LED Colors and Lens Finishes
- ▶ Bi-Color Styles Optional
- ▶ Insulated Lead Lengths Optional
- ▶ Easy Installation Through Panel
- ▶ Small Volumes Acceptable
- ▶ Available Without Insulated Leads (Bare LED Pins)
- ▶ Black Anodized Holder Optional
- ▶ Blinking LED
- ▶ With Internal Resistor for 5V and 12V Operation
- ▶ With Connector


APPLICATIONS / USES

- ▶ Front Panel Status Indicators
- ▶ Alarm/Warning Indicators
- ▶ Front Panel Circuit Fault Indicators
- ▶ Instrument Control Panels
- ▶ Medical Diagnostics Indicators
- ▶ Industrial Automation Control Panels

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Operating Current (mA)	Operating TYP. Vf (V)	Brightness TYP. Mcd	@ mA	View Angle° 2θ	Component LED Used
HIGH BRIGHTNESS										
SSI-LXR3612SID-150	AlInGaP	Super High Intensity Red	636	Red Diffused	5-25	2	100	20	60	SSL-LX3054SID
SSI-LXR3612SOD-150	AlInGaP	Super Orange	610	Orange Diffused	5-25	2	100	20	60	SSL-LX3054SOD
SSI-LXR3612SUGD-150	AlInGaP	Super Ultra Green	574	Green Diffused	5-25	2.2	180	20	60	SSL-LX3054SUGD
SSI-LXR3612SYD-150	AlInGaP	Super Yellow	590	Yellow Diffused	5-25	2	250	20	60	SSL-LX3054SYD
SSI-LXR3612USBD-150	InGaN/SiC	Ultra Super Blue	470	Blue Diffused	5-25	3.5	80	20	60	SSL-LX3054USBD
SSI-LXR3612UWW-150	InGaN/SiC	Ultra White	-	White Diffused	5-25	3.5	500	20	30	SSL-LX3054UWW
STANDARD BRIGHTNESS										
SSI-LXR3612GD-150	GaP	Green	565	Green diffused	5-25	2.2	40	20	60	SSL-LX3054GD
SSI-LXR3612ID-150	GaAsP	High Intensity Red	635	Red Diffused	5-25	2	40	20	60	SSL-LX3054ID
SSR-LXR3612SRD-150	GaAlAs	Super Red	660	Red Diffused	5-25	1.7	80	20	60	SSL-LX3054SRD
SSI-LXR3612YD-150	GaAsP	Yellow	585	Yellow Diffused	5-25	2.1	12	20	60	SSL-LX3054YD

SSI-LXH387XX-150 Series

T-4.9mm Freznel Lens Indicator, 6" Leads



FEATURES / OPTIONS

- ▶ State-of-the-Art, High Brightness LED Chip Technology
- ▶ Choice of LED Colors and Lens Finishes
- ▶ Bi-Color Styles Optional
- ▶ Insulated Lead Lengths Optional
- ▶ Easy Installation Through Panel
- ▶ Small Volumes Acceptable
- ▶ Available Without Insulated Leads (Bare LED Pins)
- ▶ Blinking LED
- ▶ With Internal Resistor for 5V and 12V Operation
- ▶ With Connector

APPLICATIONS / USES

- ▶ Front Panel Status Indicators
- ▶ Alarm/Warning Indicators
- ▶ Front Panel Circuit Fault Indicators
- ▶ Instrument Control Panels
- ▶ Medical Diagnostics Indicators
- ▶ Industrial Automation Control Panels

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Operating Current (mA)	Operating TYP. Vf (V)	Brightness TYP. Mcd	@ mA	View Angle° 2θ	Component LED Used
HIGH BRIGHTNESS										
SSI-LXH387SID-150	AlInGaP	Super High Intensity Red	636	Red Diffused	5-25	2	60	20	120	SSL-LX433SID
SSI-LXH387SOD-150	AlInGaP	Super Orange	610	Orange Diffused	5-25	2	60	20	120	SSL-LX433SOD
SSI-LXH387SUGD-150	AlInGaP	Super Ultra Green	574	Green Diffused	5-25	2.2	60	20	120	SSL-LX433SUGD
SSI-LXH387SYD-150	AlInGaP	Super Yellow	590	Yellow Diffused	5-25	2	60	20	120	SSL-LX433SYD
SSI-LXH387USBD-150	InGaN/SiC	Ultra Super Blue	470	Blue Diffused	5-25	3.5	60	20	120	SSL-LX433USBD
STANDARD BRIGHTNESS										
SSI-LXH387GD-150	GaP	Green	565	Green diffused	5-25	2.2	6	20	120	SSL-LX433GD
SSI-LXH387ID-150	GaAsP	High Intensity Red	635	Red Diffused	5-25	2.0	4	20	120	SSL-LX433ID
SSI-LXH387SRD-150	GaAlAs	Super Red	660	Red Diffused	5-25	1.7	25	20	120	SSL-LX433SRD
SSI-LXH387YD-150	GaAsP	Yellow	585	Yellow Diffused	5-25	2.1	6	20	120	SSL-LX433YD



USA/Canada +1-800-278-5666
Europe +49-6081-964380
Asia +886-3-5821124



www.lumex.com



USA/Canada +1-847-359-8904
Europe +49-6081-964381
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSI-LXR3612YD-150](#) [SSI-LXR3612SYD-150](#) [SSI-LXH387USBD-150](#)