

## Features

- High Dense Cell Design for Extremely Low  $R_{DS(ON)}$
- Exceptional On-Resistance and Maximum DC Current Capability
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1
- Halogen Free. "Green" Device (Note 1)
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)


## Maximum Ratings

- Operating Junction Temperature Range:  $-55^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$
- Storage Temperature Range:  $-55^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$
- Thermal Resistance:  $96^{\circ}\text{C/W}$  Junction to Ambient<sup>(Note 3)</sup>

Parameter	Symbol	Rating	Unit
Drain -Source Voltage	$V_{DS}$	30	V
Gate -Source Voltage	$V_{GS}$	$\pm 12$	V
Drain Current-Continuous	$I_D$	5.8	A
Drain Current-Pulsed <sup>(Note 2)</sup>	$I_{DM}$	30	A
Power Dissipation	$P_D$	1.3	W

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

## Internal Structure




1. GATE
2. SOURCE
3. DRAIN

Marking: R0<sub>A</sub>


## N-Channel MOSFET

## SOT-23



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.110	0.120	2.80	3.04	
B	0.083	0.104	2.10	2.64	
C	0.047	0.055	1.20	1.40	
D	0.034	0.041	0.85	1.05	
E	0.067	0.083	1.70	2.10	
F	0.018	0.024	0.45	0.60	
G	0.0004	0.006	0.01	0.15	
H	0.035	0.043	0.90	1.10	
J	0.003	0.007	0.08	0.18	
K	0.012	0.020	0.30	0.51	
L	0.007	0.020	0.20	0.50	

## Suggested Solder Pad Layout



**ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise specified)**

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	30			V
Gate-Threshold Voltage <sup>(Note 4)</sup>	V <sub>GS(th)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	0.7		1.2	V
Gate-Body Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> =± 12V, V <sub>DS</sub> =0V			±100	nA
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =24V, V <sub>GS</sub> =0V			1	μA
Drain-Source On-Resistance <sup>(Note 4)</sup>	R <sub>DS(on)</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> =5.8A		21	27	mΩ
		V <sub>GS</sub> =4.5V, I <sub>D</sub> =5.0A		25	33	
		V <sub>GS</sub> =2.5V, I <sub>D</sub> =4.0A		33	51	
Forward Transconductance	g <sub>FS</sub>	V <sub>DS</sub> =5V, I <sub>D</sub> =5.0A	8.0			S
Dynamic Characteristics <sup>(Note 5)</sup>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> =15V,V <sub>GS</sub> =0V, f=1MHz			1155	pF
Output Capacitance	C <sub>oss</sub>			108		
Reverse Transfer Capacitance	C <sub>rss</sub>			84		
Gate Resistance	R <sub>g</sub>	V <sub>DS</sub> =0V,V <sub>GS</sub> =0V,f =1MHz			3.6	Ω
Switching Characteristics <sup>(Note 5)</sup>						
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>GS</sub> =10V,R <sub>L</sub> =2.7Ω,V <sub>DS</sub> =15V, , R <sub>GEN</sub> =3Ω			5	ns
Turn-On Rise Time	t <sub>r</sub>				7	
Turn-Off Delay Time	t <sub>d(off)</sub>				40	
Turn-Off Fall Time	t <sub>f</sub>				6	
Drain-Source Diode Characteristics and Maximum Ratings						
Diode Forward voltage <sup>(Note 4)</sup>	V <sub>SD</sub>	V <sub>GS</sub> =0V,I <sub>S</sub> =1A			1.0	V

Notes:

2. Repetitive Rating : Pulse width limited by maximum junction temperature.
3. Surface Mounted on FR4 Board,  $t < 5$  sec.
4. Pulse Test: Pulse Width $\leq 300\mu A$ , Duty Cycle $\leq 2\%$ .
5. Guaranteed by Design, Not Subject to Production Testing.

## Curve Characteristics

Fig. 1 - Output Characteristics




Fig. 2 - Transfer Characteristics




Fig. 3 -  $R_{DS(ON)} - I_D$




Fig. 4 -  $R_{DS(ON)} - V_{GS}$




Fig. 5 -  $I_S - V_{SD}$





Fig. 6 - Threshold Voltage



## Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:3Kpcs/Reel

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[SI3400A-TP](#)