

Features

- SiC MOSFET Technology
- High Blocking Voltage with Low On-resistance
- Low Capacitance
- Halogen Free. "Green" Device (Note 1)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant (Note2)("P" Suffix Designates RoHS Compliant. See Ordering Information)

Maximum Ratings

- Operating Junction Temperature Range : -55°C to +175°C
- Storage Temperature Range: -55°C to +175°C
- Typical Thermal Resistance: 1.2°C/W Junction to Case

Applications



- Solar Inverters
- Switch Mode Power Supplies
- High Voltage DC/DC Converters
- Power Factor Correction (PFC)
- Motor Drives

Parameter		Symbol	Rating	Unit
Drain-Source Voltage		V_{DS}	1700	V
Gate-Source Voltage		V_{GSmax}	-5/+25	V
Gate-Source Voltage		V_{GSop}	-3/+20	V
Continuous Drain Current $V_{GS}=20V$	$T_c=25^{\circ}C$	I_D	6	A
	$T_c=110^{\circ}C$		3.9	
Pulsed Drain Current (Note 3)		I_{DM}	24	A
Single Pulse Avalanche Energy (Note4)		E_{AS}	259	mJ
Total Power Dissipation	$T_c=25^{\circ}C$	P_D	125	W
	$T_c=110^{\circ}C$		54	

Note:

1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. High Temperature Solder Exemptions Applied, see EU Directive Annex 7a.
3. Pulse Test: Pulse Width Limited by T_{jmax} .
4. EAS Condition: $T_J=25^{\circ}C$, $V_{DD}=50V$, $V_{GS}=20V$, $R_g=25\Omega$, $L=10mH$, $I_{AS}=7.2A$.


Internal Structure



Device Code: SICW400N170A
Date Code: YYWW (Year & Week)

N-CHANNEL MOSFET

TO-247AB



DIMENSIONS

DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.189	0.205	4.80	5.20	
A1	0.087	0.103	2.21	2.61	
A2	0.073	0.085	1.85	2.15	
b	0.039	0.055	1.00	1.40	
b2	0.075	0.087	1.91	2.21	
C	0.020	0.028	0.50	0.70	
D	0.815	0.839	20.70	21.30	
D1	0.640	0.663	16.25	16.85	
E	0.610	0.634	15.50	16.10	
E1	0.512	0.535	13.00	13.60	
E2	0.189	0.205	4.80	5.20	
E3	0.091	0.106	2.30	2.70	
L	0.772	0.796	19.62	20.22	
L1	-	0.169	-	4.50	
P	0.134	0.150	3.40	3.80	Φ
P1		0.287	-	7.30	Φ
S	0.242		6.15		TYP
H1	0.214		5.44		TYP
b3	0.110	0.126	2.80	3.20	

Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} =0V, I _D =250uA	1700			V
Gate-Source Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =20V			±250	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =1700V, V _{GS} =0V			10	μA
Gate-Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =5mA	2		4.5	V
Drain-Source On-Resistance	R _{DS(on)}	V _{GS} =20V, I _D =3A		400	500	mΩ
		V _{GS} =18V, I _D =3A		440	550	mΩ
		V _{GS} =16V, I _D =3A		520	650	mΩ
Internal Gate Resistance	R _g	f=1MHz		3		Ω
Diode Characteristics						
Continuous Body Diode Current	I _S	V _{GS} =-3V		6		A
Diode Forward Voltage	V _{SD}	V _{GS} =-3V, I _{SD} =1A		4.2		V
Reverse Recovery Time	t _{rr}	V _{GS} =-3/+20V, I _{SD} =6A, V _R =400V, dI _F /dt=100A/μs		17		ns
Reverse Recovery Charge	Q _{rr}			5		nC
Peak Reverse Recovery Current	I _{rrm}			0.6		A
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{DS} =1000V,V _{GS} =0V,f=1MHz		333		pF
Output Capacitance	C _{oss}			19		
Reverse Transfer Capacitance	C _{rss}			4		
Total Gate Charge	Q _g	V _{DS} =800V,V _{GS} =-3/+20V I _D =6A		31		nC
Gate-Source Charge	Q _{gs}			2.2		
Gate-Drain Charge	Q _{gd}			16		
Gate Plateau Voltage	V _{pl}			6		V
Turn-On Delay Time	t _{d(on)}	V _{DD} =800V, V _{GS} =-3/+20V, R _{G(ext)} =25Ω, I _{DS} =6A		34		ns
Turn-On Rise Time	t _r			22		
Turn-Off Delay Time	t _{d(off)}			39		
Turn-Off Fall Time	t _f			34		

Curve Characteristics

Fig. 1 - Typical Output Characteristic($T_J=25^\circ\text{C}$)




Fig. 2 - Typical Output Characteristic ($T_J=175^\circ\text{C}$)




Fig. 3 - Typical Transfer Characteristic




Fig. 4 - On-Resistance vs. Drain Current




Fig. 5 On-Resistance vs Gate Voltage





Fig. 6 - On-Resistance vs Temperature



Curve Characteristics

Fig. 7 - Normalized On-Resistance vs Temperature




Fig. 8 - Body Diode Characteristic




Fig. 9 - Body Diode Characteristic




Fig. 10 - Output capacitor stored energy




Fig. 11 - Threshold Voltage vs Temperature





Fig. 12 - Typical Gate Charge



Curve Characteristics

Fig. 13 - Capacitance Characteristics




Fig. 14 - Capacitance Characteristics




Fig. 15 - Drain Current Derating vs Case Temperature




Fig. 16 - Junction to Case Transient Thermal Impedance




Fig. 17 - Safe Operation Area





Fig. 18 - Power Derating



Ordering Information

Device	Packing
SICW400N170A-BP	Tube:30pcs/Tube, 1.8K/Ctn

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp.** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[SICW400N170A-BP](#)