


Discrete LEDs ~ Dome Lens



SSL-LX306F4 Series

T-3mm, 6mm Tall Lens, Flangeless



FEATURES / OPTIONS

- ▶ State-of-the-Art, High Brightness Chip Technology
- ▶ Choice of Colors and Lens Finishes
- ▶ Lead Frame / Lens Casting Reliability
- ▶ Easy-to-Solder Leads, Tin Finish
- ▶ Available Bulk or on Tape and Reel
- ▶ Lead Trimming and Forming Available
- ▶ Custom Shapes, Easily Tooled, Low Minimum
- ▶ Blinking LED
- ▶ With Internal Resistor for 5V and 12V Operation


APPLICATIONS / USES

- ▶ Board or Panel Indication or Illumination
- ▶ Backlighting of Overlays and Graphics
- ▶ Annunciator and Control Panels
- ▶ Keyboards and Switches
- ▶ Telecom Switches and Central Station Equipment
- ▶ Signs, Warning Lights, Displays

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Operating Current (mA)	Operating TYP. Vf (V)	Brightness TYP. Mcd	@ mA	View Angle° 2θ
HIGH BRIGHTNESS									
SSL-LX306F4SID	AlInGaP	Super High Intensity Red	636	Red Diffused	5-25	2	100	20	60
SSL-LX306F4SOD	AlInGaP	Super Orange	610	Orange Diffused	5-25	2	100	20	60
SSL-LX306F4SUGD	AlInGaP	Super Ultra Green	574	Green Diffused	5-25	2.2	180	20	60
SSL-LX306F4SYD	AlInGaP	Super Yellow	590	Yellow Diffused	5-25	2	250	20	60
SSL-LX306F4USBD	InGaP/SiC	Ultra Super Blue	470	Blue Diffused	5-25	3.5	80	20	60
STANDARD BRIGHTNESS									
SSL-LX306F4GD	GaP	Green	565	Green Diffused	5-25	2.2	10	20	60
SSL-LX306F4ID	GaAsP	High Intensity Red	635	Red Diffused	5-25	2	10	20	60
SSL-LX306F4SRD	GaAlAs	Super Red	660	Red Diffused	5-25	1.7	50	20	60
SSL-LX306F4YD	GaAsP	Yellow	585	Yellow Diffused	5-25	2.1	20	20	60

SSL-LX308F4 Series

T-3mm, 7.75mm Tall Lens, Flangeless



FEATURES / OPTIONS

- ▶ State-of-the-Art, High Brightness Chip Technology
- ▶ Choice of Colors and Lens Finishes
- ▶ Lead Frame / Lens Casting Reliability
- ▶ Easy-to-Solder Leads, Tin Finish
- ▶ Available Bulk or on Tape and Reel
- ▶ Lead Trimming and Forming Available
- ▶ Custom Shapes, Easily Tooled, Low Minimum
- ▶ Blinking LED
- ▶ With Internal Resistor for 5V and 12V Operation

APPLICATIONS / USES

- ▶ Board or Panel Indication or Illumination
- ▶ Backlighting of Overlays and Graphics
- ▶ Annunciator and Control Panels
- ▶ Keyboards and Switches
- ▶ Telecom Switches and Central Station Equipment
- ▶ Signs, Warning Lights, Displays

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Operating Current (mA)	Operating TYP. Vf (V)	Brightness TYP. Mcd	@ mA	View Angle° 2θ
HIGH BRIGHTNESS									
SSL-LX308F4SID	AlInGaP	Super High Intensity Red	636	Red Diffused	5-25	2	100	20	60
SSL-LX308F4SOD	AlInGaP	Super Orange	610	Orange Diffused	5-25	2	100	20	60
SSL-LX308F4SUGD	AlInGaP	Super Ultra Green	574	Green Diffused	5-25	2.2	180	20	60
SSL-LX308F4SYD	AlInGaP	Super Yellow	590	Yellow Diffused	5-25	2	250	20	60
SSL-LX308F4USBD	InGaP/SiC	Ultra Super Blue	470	Blue Diffused	5-25	3.5	80	20	60
STANDARD BRIGHTNESS									
SSL-LX308F4GD	GaP	Green	565	Green Diffused	5-25	2.2	20	20	60
SSL-LX308F4ID	GaAsP	High Intensity Red	635	Red Diffused	5-25	2	20	20	60
SSL-LX308F4YD	GaAsP	Yellow	585	Yellow Diffused	5-25	2.1	20	20	60



USA/Canada 1-800-278-5666
Asia +886-3-5821124



www.lumex.com



USA/Canada 1-847-359-8904
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSL-LX308F4ID](#) [SSL-LX308F4YD](#) [SSL-LX306F4YD](#)