

Features

- For Surface Mount Applications
- VZ – Tolerance: $\pm 5\%$
- Halogen Free. "Green" Device (Note 1)
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant (Note 2) ("P" Suffix Designates Compliant. See Ordering Information)

Maximum Ratings

- Operating Junction Temperature Range: -65°C to $+150^{\circ}\text{C}$
- Storage Temperature Range: -65°C to $+150^{\circ}\text{C}$
- Thermal Resistance : 100°C/W Junction to Ambient
- Thermal Resistance : 75°C/W Junction to Lead

Parameter	Symbol	Rating	Conditions
Power Dissipation	P_D	1.0W	$T_L=75^{\circ}\text{C}$
Zener Current	I_Z	P_D/V_Z mA	
Maximum Forward Voltage	V_F	1.2V	$I_F=100\text{mA}$

Note:

1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. High Temperature Solder Exemption Applied, see EU Directive Annex 7a.


Internal Structure

Description	Simplified outline	Graphic symbol
Uni-directional		

XXXX = Marking code


1.0 Watt Surface Mount Silicon Zener Diodes 5.1V to 100V

SMA (DO-214AC) LEAD FRAME



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.075	0.096	1.90	2.44	
B	0.050	0.064	1.27	1.63	
C	0.002	0.008	0.051	0.203	
D	---	0.020	---	0.51	
E	0.030	0.060	0.76	1.52	
F	0.065	0.091	1.65	2.32	
G	0.189	0.220	4.80	5.59	
H	0.157	0.187	4.00	4.75	
J	0.090	0.115	2.25	2.92	

SUGGESTED SOLDER PAD LAYOUT



Electrical Characteristics @ 25°C Unless Otherwise Specified

Part Number	Nominal Zener Voltage			Test Current	Maximum Dynamic Impedance Resistance			Maximum Reverse leakage Current		Maximum DC Zener Current	Marking Code		
	VZ@IZT				IZT	ZZT at IZT	ZZK at IZK	IZK	IR			VR	IZM
	Min(V)	Nom(V)	Max(V)										
SMAJ4733A	4.85	5.1	5.36	49	7	550	1	10	1.0	177	733A		
SMAJ4734A	5.32	5.6	5.88	45	5	600	1	10	2.0	161	734A		
SMAJ4735A	5.89	6.2	6.51	41	2	700	1	10	3.0	146	735A		
SMAJ4736A	6.46	6.8	7.14	37	3.5	700	1	10	4.0	133	736A		
SMAJ4737A	7.13	7.5	7.88	34	4	700	0.5	10	5.0	121	737A		
SMAJ4738A	7.79	8.2	8.61	31	4.5	700	0.5	10	6.0	110	738A		
SMAJ4739A	8.65	9.1	9.56	28	5	700	0.5	10	7.0	100	739A		
SMAJ4740A	9.50	10.0	10.50	25	7	700	0.25	10	7.6	91	740A		
SMAJ4741A	10.45	11.0	11.55	23	8	700	0.25	5	8.4	83	741A		
SMAJ4742A	11.40	12.0	12.60	21	9	700	0.25	5	9.1	76	742A		
SMAJ4743A	12.35	13.0	13.65	19	10	700	0.25	5	9.9	69	743A		
SMAJ4744A	14.25	15.0	15.75	17	14	700	0.25	5	11.4	61	744A		
SMAJ4745A	15.20	16.0	16.80	15.5	16	700	0.25	5	12.2	57	745A		
SMAJ4746A	17.10	18.0	18.90	14.0	20	750	0.25	5	13.7	50	746A		
SMAJ4747A	19.00	20.0	21.00	12.5	22	750	0.25	5	15.2	45	747A		
SMAJ4748A	20.90	22.0	23.10	11.5	23	750	0.25	5	16.7	41	748A		
SMAJ4749A	22.80	24.0	25.20	10.5	25	750	0.25	5	18.2	38	749A		
SMAJ4750A	25.65	27.0	28.35	9.5	35	750	0.25	5	20.6	34	750A		
SMAJ4751A	28.50	30.0	31.50	8.5	40	1000	0.25	5	22.8	30	751A		
SMAJ4752A	31.35	33.0	34.65	7.5	45	1000	0.25	5	25.1	27	752A		
SMAJ4753A	34.20	36.0	37.80	7	50	1000	0.25	5	27.4	25	753A		
SMAJ4754A	37.05	39.0	40.95	6.5	60	1000	0.25	5	29.7	23	754A		
SMAJ4755A	40.85	43.0	45.15	6	70	1500	0.25	5	32.7	22	755A		
SMAJ4756A	44.65	47.0	49.35	5.5	80	1500	0.25	5	35.8	19	756A		
SMAJ4757A	48.45	51.0	53.55	5	95	1500	0.25	5	38.8	18	757A		
SMAJ4758A	53.20	56.0	58.80	4.5	110	2000	0.25	5	42.6	16	758A		
SMAJ4759A	58.90	62.0	65.10	4	125	2000	0.25	5	47.1	14	759A		
SMAJ4760A	64.60	68.0	71.40	3.7	150	2000	0.25	5	51.7	13	760A		
SMAJ4761A	71.25	75.0	78.75	3.3	175	2000	0.25	5	56.0	12	761A		
SMAJ4762A	77.90	82.0	86.10	3	200	3000	0.25	5	62.2	11	762A		
SMAJ4763A	86.45	91.0	95.55	2.8	250	3000	0.25	5	69.2	10	763A		
SMAJ4764A	95.00	100.0	105.00	2.5	350	3000	0.25	5	76.0	9	764A		

Curve Characteristics

Fig. 1 - Pulse Derating Curve




Fig. 2 - Typical Zener Breakdown Characteristics




Fig. 3- Typical Zener Breakdown Characteristics




Fig. 4- Typical Zener Breakdown Characteristics





Fig. 5- Typical Forward Characteristics



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:7.5Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[SMAJ4742A-TP](#) [SMAJ4750A-TP](#) [SMAJ4754A-TP](#) [SMAJ4736A-TP](#) [SMAJ4752A-TP](#) [SMAJ4744A-TP](#) [SMAJ4741A-TP](#) [SMAJ4735A-TP](#) [SMAJ4738A-TP](#) [SMAJ4748A-TP](#) [SMAJ4751A-TP](#) [SMAJ4745A-TP](#) [SMAJ4739A-TP](#) [SMAJ4740A-TP](#) [SMAJ4753A-TP](#) [SMAJ4747A-TP](#) [SMAJ4749A-TP](#) [SMAJ4743A-TP](#) [SMAJ4737A-TP](#) [SMAJ4746A-TP](#) [SMAJ4764A-TP](#) [SMAJ4762A-TP](#) [SMAJ4763A-TP](#) [SMAJ4761A-TP](#) [SMAJ4757A-TP](#) [SMAJ4755A-TP](#) [SMAJ4760A-TP](#) [SMAJ4759A-TP](#) [SMAJ4756A-TP](#) [SMAJ4758A-TP](#) [SMAJ4733A-TP](#) [SMAJ4734A-TP](#)