

DATE	REVISIONS	REV		DRAWING NUMBER SSB-COB13432GW	REV																																				
<div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> </div> <div style="width: 45%;"> </div> </div> <div style="margin-top: 20px;"> </div> <div style="margin-top: 20px; text-align: center;"> </div>																																									
<div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>ELECTRO-OPTICAL CHARACTERISTICS TA=25 °C If=780mA</p> <table border="1" style="width:100%; border-collapse: collapse;"> <thead> <tr> <th>PARAMETER</th> <th>MIN</th> <th>TYP</th> <th>MAX</th> <th>UNITS</th> <th>TEST COND</th> </tr> </thead> <tbody> <tr> <td>PEAK WAVELENGTH</td> <td></td> <td>565 (GREEN)</td> <td></td> <td>nm</td> <td></td> </tr> <tr> <td>SPECTRAL LINE HALF WIDTH</td> <td></td> <td>30</td> <td></td> <td>nm</td> <td></td> </tr> <tr> <td>FORWARD VOLTAGE</td> <td>4.0</td> <td>4.5</td> <td></td> <td>V</td> <td>If=780mA</td> </tr> <tr> <td>REVERSE CURRENT</td> <td></td> <td></td> <td>200</td> <td>uA</td> <td>Vr=8V</td> </tr> <tr> <td>LUMINOUS INTENSITY</td> <td>450</td> <td></td> <td></td> <td>cd/m²</td> <td>If=780mA</td> </tr> </tbody> </table> </div> <div style="width: 45%;"> <p>NOTES:</p> <ol style="list-style-type: none"> 1. STAMP DATE CODE ON SIDE AS SHOWN. 2. P/N SSB-COB13432GW AT BOTTOM OF P.C.B. </div> </div>						PARAMETER	MIN	TYP	MAX	UNITS	TEST COND	PEAK WAVELENGTH		565 (GREEN)		nm		SPECTRAL LINE HALF WIDTH		30		nm		FORWARD VOLTAGE	4.0	4.5		V	If=780mA	REVERSE CURRENT			200	uA	Vr=8V	LUMINOUS INTENSITY	450			cd/m ²	If=780mA
PARAMETER	MIN	TYP	MAX	UNITS	TEST COND																																				
PEAK WAVELENGTH		565 (GREEN)		nm																																					
SPECTRAL LINE HALF WIDTH		30		nm																																					
FORWARD VOLTAGE	4.0	4.5		V	If=780mA																																				
REVERSE CURRENT			200	uA	Vr=8V																																				
LUMINOUS INTENSITY	450			cd/m ²	If=780mA																																				
<div style="display: flex; justify-content: space-between;"> <div style="width: 45%;"> <p>LIMITS OF SAFE OPERATION AT 25 DEG. C</p> <table border="1" style="width:100%; border-collapse: collapse;"> <thead> <tr> <th>PARAMETER</th> <th>MAX</th> <th>UNITS</th> </tr> </thead> <tbody> <tr> <td>PEAK FORWARD CURRENT</td> <td>975</td> <td>mA</td> </tr> <tr> <td>REVERSE VOLTAGE</td> <td>8V</td> <td>Vr</td> </tr> <tr> <td>POWER DISSIPATION</td> <td>4.39</td> <td>W</td> </tr> <tr> <td>DERATE FROM 25 °C</td> <td>61.3</td> <td>mW/ °C</td> </tr> <tr> <td>OPERATING TEMP.</td> <td>-40 TO +85</td> <td>°C</td> </tr> <tr> <td>STORAGE TEMP.</td> <td>-40 TO +85</td> <td>°C</td> </tr> </tbody> </table> </div> <div style="width: 45%;"> <div style="text-align: center; margin-bottom: 10px;"> </div> <p>290 E. HELLEN ROAD PALATINE, ILLINOIS 60067 (847) 359-2790</p> </div> </div>						PARAMETER	MAX	UNITS	PEAK FORWARD CURRENT	975	mA	REVERSE VOLTAGE	8V	Vr	POWER DISSIPATION	4.39	W	DERATE FROM 25 °C	61.3	mW/ °C	OPERATING TEMP.	-40 TO +85	°C	STORAGE TEMP.	-40 TO +85	°C															
PARAMETER	MAX	UNITS																																							
PEAK FORWARD CURRENT	975	mA																																							
REVERSE VOLTAGE	8V	Vr																																							
POWER DISSIPATION	4.39	W																																							
DERATE FROM 25 °C	61.3	mW/ °C																																							
OPERATING TEMP.	-40 TO +85	°C																																							
STORAGE TEMP.	-40 TO +85	°C																																							
<p style="text-align: center; font-size: small;">CONFIDENTIAL INFORMATION THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX OPTO/COMPONENTS, INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX OPTO/COMPONENTS, INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.</p>																																									
DATE: 3-19-97		DWN:	CHK'D:	APPD:																																					
SCALE: N/A																																									
<p>130mm x 25mm LED BACKLIGHT, 78 CHIPS ON BOARD, GREEN</p>																																									
PAGE 1 OF 1		DRAWING NUMBER SSB-COB13432GW		REV																																					

UNLESS OTHERWISE SPECIFIED TOLERANCE IS ±.25mm (±0.010")

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSB-COB13432GW](#)