

Features

- Halogen Free. "Green" Device (Note 1)
- AEC-Q101 Qualified
- High Surge Current Capability
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Available on Tape and Reel (see E1A std RS-481)
- Low Profile Package for Surface Mounting (Flat Handling Surface for Accurate Placement)
- Lead Free Finish/RoHS Compliant (Note2) ("P" Suffix Designates Compliant. See Ordering Information)

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance: 15°C/W Junction to Lead
- Thermal Resistance: 90°C/W Junction to Ambient (Note3)

Parameter	Symbol	Rating	Conditions
Steady State Power Dissipation	$P_{(AV)}$	5.0W	Note 4
Maximum Forward Voltage	V_F	1.2V	$I_F = 1.0mA$


Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

2. High Temperature Solder Exemption Applied, See EU Directive Annex 7a.

3. Ambient Temperature at 15°C = T_A at Mounting Plane. Derate Linearly Above 15°C to Zero Power at 150°C

4. Lead Temperature at 75°C = T_L at Mounting Plane. Derate Linearly Above 75°C to Zero Power at 150°C


Device Marking:



For Example: 339B for SMBJ5339B
369B for SMBJ5369B


5.0 Watt Surface Mount Silicon Zener Diodes 10V to 200V

SMB (DO-214AA) (LEAD FRAME)



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.079	0.103	2.00	2.62	
B	0.075	0.087	1.91	2.21	
C	0.002	0.008	0.05	0.20	
D	0.006	0.012	0.15	0.31	
E	0.030	0.060	0.76	1.52	
F	0.065	0.091	1.65	2.32	
G	0.200	0.220	5.08	5.59	
H	0.160	0.191	4.06	4.85	
J	0.130	0.155	3.30	3.94	

Suggested Solder Pad Layout



Electrical Characteristics @ 25°C Unless Otherwise Specified

MCC Part Number	Regulator Voltage	Test Current	Maximum Dynamic Impedance	Maximum Reverse Current	Test Voltage	Maximum Regulator Current	Maximum Dynamic Knee Impedance	Maximum Surge Current	Maximum Voltage Regulation
	V_Z	I_Z	Z_{ZT}	I_R	V_R	I_{ZM}	$Z_{ZK} @ 1.0mA$	I_{ZSM}	
	V	mA	Ω	μA	V	mA	Ω	A	V
SMBJ5347BHE3	10	125	2	5	7.6	475	125	8.6	0.22
SMBJ5348BHE3	11	125	2.5	5	8.4	430	125	8	0.25
SMBJ5349BHE3	12	100	2.5	2	9.1	395	125	7.5	0.25
SMBJ5350BHE3	13	100	2.5	1	9.9	365	100	7	0.25
SMBJ5351BHE3	14	100	2.5	1	10.6	340	75	6.7	0.25
SMBJ5352BHE3	15	75	2.5	1	11.5	315	75	6.3	0.25
SMBJ5353BHE3	16	75	2.5	1	12.2	295	75	6	0.3
SMBJ5354BHE3	17	70	2.5	0.5	12.9	280	75	5.8	0.35
SMBJ5355BHE3	18	65	2.5	0.5	13.7	264	75	5.5	0.4
SMBJ5356BHE3	19	65	3	0.5	14.4	250	75	5.3	0.4
SMBJ5357BHE3	20	65	3	0.5	15.2	237	75	5.1	0.4
SMBJ5358BHE3	22	50	3.5	0.5	16.7	216	75	4.7	0.45
SMBJ5359BHE3	24	50	3.5	0.5	18.2	198	100	4.4	0.55
SMBJ5360BHE3	25	50	4	0.5	19	190	110	4.3	0.55
SMBJ5361BHE3	27	50	5	0.5	20.6	176	120	4.1	0.6
SMBJ5362BHE3	28	50	6	0.5	21.2	170	130	3.9	0.6
SMBJ5363BHE3	30	40	8	0.5	22.8	158	140	3.7	0.6
SMBJ5364BHE3	33	40	10	0.5	25.1	144	150	3.5	0.6
SMBJ5365BHE3	36	30	11	0.5	27.4	132	160	3.3	0.65
SMBJ5366BHE3	39	30	14	0.5	29.7	122	170	3.1	0.65
SMBJ5367BHE3	43	30	20	0.5	32.7	110	190	2.8	0.7
SMBJ5368BHE3	47	25	25	0.5	35.8	100	210	2.7	0.8
SMBJ5369BHE3	51	25	27	0.5	38.8	93	230	2.5	0.9
SMBJ5370BHE3	56	20	35	0.5	42.6	86	280	2.3	1
SMBJ5371BHE3	60	20	40	0.5	45.5	79	350	2.2	1.2
SMBJ5372BHE3	62	20	42	0.5	47.1	76	400	2.1	1.35
SMBJ5373BHE3	68	20	44	0.5	51.7	70	500	2	1.5
SMBJ5374BHE3	75	20	45	0.5	56	63	620	1.9	1.6
SMBJ5375BHE3	82	15	65	0.5	62.2	58	720	1.8	1.8
SMBJ5376BHE3	87	15	75	0.5	66	54.5	760	1.7	2
SMBJ5377BHE3	91	15	75	0.5	69.2	52.5	760	1.6	2.2
SMBJ5378BHE3	100	12	90	0.5	76	47.5	800	1.5	2.3
SMBJ5379BHE3	110	12	125	0.5	83.6	43	1000	1.4	2.5
SMBJ5380BHE3	120	10	170	0.5	91.2	39.5	1150	1.3	2.5
SMBJ5381BHE3	130	10	190	0.5	98.8	36.6	1250	1.2	2.5
SMBJ5382BHE3	140	8.0	230	0.5	106	34	1500	1.2	2.5
SMBJ5383BHE3	150	8.0	330	0.5	114	31.6	1500	1.1	3
SMBJ5384BHE3	160	8.0	350	0.5	122	29.4	1650	1.1	3
SMBJ5385BHE3	170	8.0	380	0.5	129	28	1750	1.0	3
SMBJ5386BHE3	180	5.0	430	0.5	137	26.4	1750	1.0	4
SMBJ5387BHE3	190	5.0	450	0.5	144	25	1850	0.9	5
SMBJ5388BHE3	200	5.0	480	0.5	152	23.6	1850	0.9	5

Remarks:

1. Devices Listed Have a $\pm 5\%$ Tolerance on Nominal V_Z . Suffix C Denotes a $+2\%$
2. Nominal Zener Voltage (V_Z) is Tested With a 40 ± 10 Milliseconds Pulse Current at 25°C to Avoid Self-heat Affection.
3. The Zener Impedance (Z_{ZT} or Z_{ZK}) is Derived from The 60Hz AC Voltage, Which Results When an AC Current Having a rms value Equal to 10% of the DC Zener Current (I_{ZT} or I_{ZK}) Respectively.
4. The Maximum Reverse(Leakage) Current is Specified for Devices With $\pm 20\%$ and $\pm 10\%$ Voltage Tolerances on Nominal V_Z in Another Column.
5. The Maximum Zener Current(I_{ZM}) Shown is for $\pm 5\%$ Tolerance Devices. I_{ZM} for $\pm 10\%$ and $\pm 20\%$ Devices Can be Calculated Using the Formula:

$$I_{ZM} = \frac{P}{V_{ZM}}$$

Where " V_{ZM} " is V_Z at The High End of The Voltage Tolerance Specified and "P" is The Rated Power of The Device.

6. The Surge Current (I_{ZM}) is Specified As The Maximum Peak of a Nonrecurring Sine Wave of 8.3 Milliseconds Duration.
7. Voltage Regulatio (ΔV_Z) is The Difference Between The Voltage Measured at 10% and 50% (I_{ZM}).

Curve Characteristics

Fig. 1 - Power Derating Curve




Fig. 2 - Typical Zener Breakdown Characteristics





Fig. 3 - Typical Zener Breakdown Characteristics



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:3Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Commercial Components (MCC):

<u>SMBJ5347BHE3-TP</u>	<u>SMBJ5348BHE3-TP</u>	<u>SMBJ5349BHE3-TP</u>	<u>SMBJ5350BHE3-TP</u>	<u>SMBJ5351BHE3-TP</u>
<u>SMBJ5352BHE3-TP</u>	<u>SMBJ5353BHE3-TP</u>	<u>SMBJ5354BHE3-TP</u>	<u>SMBJ5355BHE3-TP</u>	<u>SMBJ5356BHE3-TP</u>
<u>SMBJ5357BHE3-TP</u>	<u>SMBJ5358BHE3-TP</u>	<u>SMBJ5359BHE3-TP</u>	<u>SMBJ5360BHE3-TP</u>	<u>SMBJ5361BHE3-TP</u>
<u>SMBJ5362BHE3-TP</u>	<u>SMBJ5363BHE3-TP</u>	<u>SMBJ5364BHE3-TP</u>	<u>SMBJ5365BHE3-TP</u>	<u>SMBJ5366BHE3-TP</u>
<u>SMBJ5367BHE3-TP</u>	<u>SMBJ5368BHE3-TP</u>	<u>SMBJ5369BHE3-TP</u>	<u>SMBJ5370BHE3-TP</u>	<u>SMBJ5371BHE3-TP</u>
<u>SMBJ5372BHE3-TP</u>	<u>SMBJ5373BHE3-TP</u>	<u>SMBJ5374BHE3-TP</u>	<u>SMBJ5375BHE3-TP</u>	<u>SMBJ5376BHE3-TP</u>
<u>SMBJ5377BHE3-TP</u>	<u>SMBJ5378BHE3-TP</u>	<u>SMBJ5379BHE3-TP</u>	<u>SMBJ5380BHE3-TP</u>	<u>SMBJ5381BHE3-TP</u>
<u>SMBJ5382BHE3-TP</u>	<u>SMBJ5383BHE3-TP</u>	<u>SMBJ5384BHE3-TP</u>	<u>SMBJ5385BHE3-TP</u>	<u>SMBJ5386BHE3-TP</u>
<u>SMBJ5387BHE3-TP</u>	<u>SMBJ5388BHE3-TP</u>			