


## LCM-X01602DXX/C


16 x 2

P/N PREFIX/SUFFIX TABLE		
LCM-X	DXX	DESCRIPTION
STANDARD	SR	STN, REFLECTIVE
	SF	STN, TRANSFLECTIVE(W/ BACKLIGHT)
HIGH TEMP.	TR	TN, REFLECTIVE
	TF	TN, TRANSFLECTIVE(W/ BACKLIGHT)

TYPE	DIM.	A	B
WITH BACKLIGHT	12.7	8.8	
NO BACKLIGHT	8.9	4.8	




## BLOCK DIAGRAM



## PIN CONFIGURATION

PIN NO.	1	2	3	4	5
SYMBOL	Vss	VDD	Vo	RS	R/W
PIN NO.	6	7~14	15	16	
SYMBOL	E	DB0~DB7	A	K	

## CHARACTER DETAIL



**ELECTRICAL CHARACTERISTICS (V<sub>DD</sub>=4.7V to 5.3V, T<sub>a</sub>=25°C)**

ITEM	SYMBOL	CONDITION	STANDARD VALUE			UNIT
			MIN.	TYP.	MAX.	
Supply Voltage for Logic	V <sub>DD</sub> - V <sub>SS</sub>	-	-	5.0	-	V
Supply Current for Logic	I <sub>DD</sub>	V <sub>DD</sub> = 5V	-	2.0	3.0	mA
Input Voltage	High	V <sub>IH</sub>	-	2.2	-	V <sub>DD</sub>
	Low	V <sub>IL</sub>	-	0	-	0.6
Output Voltage	High	V <sub>OH</sub>	-	2.4	-	V
	Low	V <sub>OL</sub>	-	-	0.4	V

**ABSOLUTE MAXIMUM RATINGS**

ITEM	SYMBOL	TEST CONDITION	STANDARD VALUE		UNIT
			MIN.	MAX.	
Supply Voltage for Logic	V <sub>DD</sub> - V <sub>SS</sub>	T <sub>a</sub> = 25°C	4.7	5.3	V
Supply Voltage for LCD Drive	V <sub>DD</sub> - V <sub>O</sub>	-	4.2 @ 50°C	4.8 @ 0°C	V
Input Voltage	V <sub>I</sub>	T <sub>a</sub> = 25°C	V <sub>SS</sub>	V <sub>DD</sub>	V
Operating Temperature	T <sub>opr</sub>	LCM-S	0	50	°C
		LCM-H	-20	70	°C
Storage Temperature	T <sub>stg</sub>	LCM-S	-20	70	°C
		LCM-H	-30	85	°C

**MECHANICAL SPECIFICATIONS**

PARAMETER	DIMENSIONS (mm)
Overall Size of Module	85.00 x 30.00 x 8.90
Overall Size with Led Backlight	85.00 x 30.00 x 12.70
Viewing Area	66.00 x 16.00
Character Size	2.96 x 5.56
Pixel Size	0.56 x 0.66

**FEATURES**

PART NUMBER	LCD MODE	BACKLIGHT
LCM-X01602DSR/C	STN REFLECTIVE	NONE
LCM-X01602DSF/C	STN TRANSFLECTIVE	LED
LCM-X01602DTR/C	TN REFLECTIVE	NONE
LCM-X01602DTF/C	TN TRANSFLECTIVE	LED

X = S (standard), or H (high)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[LCM-H01602DTR/C](#)