


# CGHV60075D5

75 W, 6.0 GHz, GaN HEMT Die

## Description

The CGHV60075D5 is a gallium nitride (GaN) High Electron Mobility Transistor (HEMT). GaN has superior properties compared to silicon or gallium arsenide, including higher breakdown voltage, higher saturated electron drift velocity, and higher thermal conductivity. GaN HEMTs offer greater power density and wider bandwidths compared to Si and GaAs transistors.



## Features

- 19 dB Typical Small Signal Gain at 4 GHz
- 17 dB Typical Small Signal Gain at 6 GHz
- 65% Typical Power Added Efficiency at 4 GHz
- 60% Typical Power Added Efficiency at 6 GHz
- 75 W Typical  $P_{SAT}$
- 50 V Operation
- High Breakdown Voltage
- Up to 6 GHz Operation

## Applications

- 2-Way Private Radio
- Broadband Amplifiers
- Cellular Infrastructure
- Test Instrumentation
- Class A, AB, Linear amplifiers suitable for OFDM, W-CDMA, EDGE, CDMA waveforms

## Packaging Information



- Bare die are shipped in Gel-Pak® containers
- Non-adhesive tacky membrane immobilizes die during shipment

 Large Signal Models Available for ADS and MWO



## Absolute Maximum Ratings (not simultaneous)

Parameter	Symbol	Rating	Units	Conditions
Drain-Source Voltage	$V_{DS}$	150	$V_{DC}$	25°C
Gate-to-Source Voltage	$V_{GS}$	-10, +2		
Storage Temperature	$T_{STG}$	-65, +150	°C	
Operating Junction Temperature	$T_J$	225		
Maximum Drain Current <sup>1</sup>	$I_{DMAX}$	6.3	A	25°C
Maximum Forward Gate Current	$I_{GMAX}$	10	mA	
Thermal Resistance, Junction to Case (packaged) <sup>2</sup>	$R_{\theta JC}$	2.67	°C/W	85°C, 41.6W Dissipation
Thermal Resistance, Junction to Case (die only)		1.66		
Mounting Temperature	$T_s$	320	°C	30 seconds

Notes:

<sup>1</sup> Current limit for long term, reliable operation

<sup>2</sup> Eutectic die attach using 80/20 AuSn mounted to a 10 mil thick Cu15Mo85 carrier

## Electrical Characteristics (Frequency = 6 GHz unless otherwise stated; $T_c = 25^\circ\text{C}$ )

Characteristics	Symbol	Min.	Typ.	Max.	Units	Conditions
<b>DC Characteristics</b>						
Gate Pinch-Off Voltage	$V_P$	-3.8	-3.0	-2.3	V	$V_{DS} = 10\text{ V}, I_D = 10\text{ mA}$
Drain Current <sup>1</sup>	$I_{DSS}$	8	10	—	A	$V_{DS} = 6\text{ V}, V_{GS} = 2.0\text{ V}$
Drain-Source Breakdown Voltage	$V_{BR}$	125	—	—	V	$V_{GS} = -8\text{ V}, I_D = 10\text{ mA}$
On Resistance	$R_{ON}$	—	0.28	—	$\Omega$	$V_{DS} = 0.1\text{ V}$
Gate Forward Voltage	$V_{G-ON}$	—	1.9	—	V	$I_{GS} = 10\text{ mA}$
<b>RF Characteristics</b>						
Small Signal Gain	$G_{SS}$	—	17	—	dB	$V_{DD} = 50\text{ V}, I_{DQ} = 125\text{ mA}$
Saturated Power Output <sup>2,3</sup>	$P_{SAT}$	—	75	—	W	
Drain Efficiency <sup>3</sup>	$\eta$	—	60	—	%	$V_{DD} = 50\text{ V}, I_{DQ} = 125\text{ mA}, P_{SAT} = 75\text{ W}$
Intermodulation Distortion	IM3	—	-30	—	dBc	$V_{DD} = 50\text{ V}, I_{DQ} = 125\text{ mA}, P_{OUT} = 75\text{ W PEP}$
Output Mismatch Stress	VSWR	—	—	10 : 1	$\Psi$	No damage at all phase angles, $V_{DD} = 50\text{ V}, I_{DQ} = 125\text{ mA}, P_{OUT} = 75\text{ W CW}$
<b>Dynamic Characteristics</b>						
Input Capacitance	$C_{GS}$	—	9.51	—	pF	$V_{DS} = 50\text{ V}, V_{GS} = -8\text{ V}, f = 1\text{ MHz}$
Output Capacitance	$C_{DS}$	—	3.6	—		
Feedback Capacitance	$C_{GD}$	—	0.26	—		


Notes:

<sup>1</sup> Scaled from PCM data

<sup>2</sup>  $P_{SAT}$  is defined as  $I_G = 1.0\text{ mA}$

<sup>3</sup> Drain Efficiency =  $P_{OUT} / P_{DC}$

## DIE Dimensions (units in microns)



Overall die size 3000 x 820 (+0/-50) microns, die thickness 100 microns.  
All Gate and Drain pads must be wire bonded for electrical connection.


## Assembly Notes:

- Recommended solder is AuSn (80/20) solder. Refer to the website for the Eutectic Die Bond Procedure application note.
- Vacuum collet is the preferred method of pick-up.
- The backside of the die is the Source (ground) contact.
- Die back side gold plating is 5 microns thick minimum.
- Thermosonic ball or wedge bonding are the preferred connection methods.
- Gold wire must be used for connections.
- Use the die label (XX-YY) for correct orientation.

## Electrostatic Discharge (ESD) Classifications

Parameter	Symbol	Class	Classification Level	Test Methodology
Human Body Model	HBM	TBD	ANSI/ESDA/JEDEC JS-001 Table 3	JEDEC JESD22 A114-D

## Typical Performance



**Figure 1.** CGHV60075D5  $G_{MAX}$  and K Factor vs Frequency at  $T_{CASE} = 25^{\circ}C$   
 $V_{DD} = 50V$ ,  $I_{DQ} = 125\text{ mA}$

## Typical Die S-Parameters

(Small Signal,  $V_{DS} = 50\text{ V}$ ,  $I_{DQ} = 125\text{ mA}$ , magnitude/angle)

Frequency	Mag S11	Ang S11	Mag S21	Ang S21	Mag S12	Ang S12	Mag S22	Ang S22
0.5	0.93309	-154.44	14.266	88.053	0.014402	-0.85181	0.35448	-119.95
0.6	0.93352	-158.34	11.838	83.444	0.01433	-5.2391	0.3779	-122.32
0.7	0.93452	-161.14	10.06	79.434	0.014195	-9.0268	0.40373	-124.1
0.8	0.93586	-163.24	8.7019	75.832	0.014019	-12.407	0.43075	-125.62
0.9	0.93743	-164.87	7.6297	72.531	0.013813	-15.485	0.45814	-127.01
1	0.93917	-166.17	6.761	69.468	0.013583	-18.326	0.48532	-128.36
1.1	0.94101	-167.24	6.0431	66.6	0.013336	-20.972	0.51193	-129.69
1.2	0.94292	-168.13	5.4398	63.9	0.013076	-23.449	0.5377	-131
1.3	0.94485	-168.89	4.926	61.348	0.012806	-25.779	0.56247	-132.31
1.4	0.9468	-169.55	4.4834	58.931	0.01253	-27.974	0.58611	-133.6
1.5	0.94872	-170.12	4.0987	56.635	0.012249	-30.047	0.60859	-134.86
1.6	0.95062	-170.64	3.7616	54.451	0.011966	-32.007	0.62986	-136.11
1.7	0.95247	-171.1	3.4641	52.373	0.011683	-33.861	0.64994	-137.32
1.8	0.95426	-171.51	3.2003	50.392	0.011401	-35.619	0.66885	-138.51
1.9	0.956	-171.89	2.9648	48.503	0.011122	-37.283	0.68662	-139.66
2	0.95767	-172.24	2.7539	46.699	0.010846	-38.863	0.70331	-140.77
2.1	0.95926	-172.56	2.5641	44.976	0.010574	-40.36	0.71895	-141.85
2.2	0.96079	-172.86	2.3927	43.33	0.010307	-41.781	0.73359	-142.89
2.3	0.96225	-173.14	2.2375	41.754	0.010045	-43.13	0.74731	-143.9
2.4	0.96364	-173.41	2.0963	40.247	0.0097893	-44.411	0.76014	-144.87
2.5	0.96496	-173.65	1.9677	38.802	0.0095396	-45.629	0.77216	-145.8
2.6	0.96621	-173.89	1.8502	37.416	0.0092961	-46.787	0.78341	-146.7
2.7	0.9674	-174.11	1.7425	36.087	0.0090588	-47.888	0.79393	-147.57
2.8	0.96853	-174.32	1.6437	34.811	0.0088279	-48.935	0.80379	-148.4
2.9	0.96959	-174.52	1.5528	33.584	0.0086033	-49.933	0.81303	-149.2
3	0.9706	-174.71	1.4689	32.404	0.0083851	-50.882	0.82169	-149.97
3.2	0.97246	-175.07	1.3198	30.177	0.0079668	-52.647	0.83741	-151.43
3.4	0.97412	-175.4	1.1918	28.105	0.0075724	-54.252	0.85128	-152.78
3.6	0.97561	-175.71	1.081	26.175	0.0072005	-55.712	0.86354	-154.03
3.8	0.97695	-175.99	0.98461	24.373	0.0068495	-57.041	0.87439	-155.19
4	0.97815	-176.26	0.90032	22.681	0.0065185	-58.254	0.88404	-156.27
4.2	0.97923	-176.5	0.82619	21.091	0.0062057	-59.361	0.89265	-157.28
4.4	0.9802	-176.74	0.76072	19.592	0.0059099	-60.372	0.90034	-158.21
4.6	0.98108	-176.96	0.70262	18.175	0.0056299	-61.295	0.90725	-159.09
4.8	0.98187	-177.17	0.65085	16.832	0.0053644	-62.137	0.91345	-159.91
5	0.98259	-177.36	0.60454	15.558	0.0051122	-62.903	0.91905	-160.68
5.2	0.98324	-177.55	0.56297	14.343	0.0048724	-63.603	0.92411	-161.41
5.4	0.98383	-177.73	0.52552	13.185	0.0046441	-64.237	0.9287	-162.09
5.6	0.98437	-177.91	0.49168	12.078	0.0044262	-64.81	0.93287	-162.73
5.8	0.98487	-178.07	0.46099	11.017	0.0042182	-65.327	0.93667	-163.34
6	0.98532	-178.23	0.4331	9.9987	0.0040191	-65.79	0.94015	-163.92

To download the s-parameters in s2p format, go to the CGHV60075D5 Product page.

Part Number System

CGHV60075D5




Table 1.


Parameter	Value	Units
Upper Frequency <sup>1</sup>	6.0	GHz
Power Output	75	W
Package	Bare Die	—

Note:  
<sup>1</sup> Alpha characters used in frequency code indicate a value greater than 9.9 GHz. See Table 2 for value.

Table 2.

Character Code	Code Value
A	0
B	1
C	2
D	3
E	4
F	5
G	6
H	7
J	8
K	9
Examples:	1A = 10.0 GHz 2H = 27.0 GHz

Product Ordering Information

Order Number	Description	Unit of Measure	Image
CGHV60075D5	Bare Die	Each	

## Notes & Disclaimer

---

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[CGHV60075D5-GP4](#) [CGHV60075D5](#)