










New!

MHS Series

Miniature Slide Switches

SPECIFICATIONS	FEATURES
Contact rating: 300 mA at 30 VDC Initial contact resistance: 20 milliohms max. Insulation resistance: 100 megohms min. at 500 VDC Dielectric strength: 500 VAC for 1 minute Electrical life: 10,000 cycles min. Operating temperature range: -20°C to +85°C Solder heat resistance: 260°C max. for 3 seconds Actuation force: 250 ±150 grams Solvent washing permissible	- Miniature compact size. - Wash-through open frame construction. - Positive spring loaded ball detent mechanism. - Epoxy sealed terminals.
	MATERIALS
	Contacts & terminals: Silver plated brass Housing: Tin plated steel Actuator: Polyacetal Base: Phenolic laminated sheet Terminal seal: Epoxy

MODEL NO. MHS122	1P2T   
MODEL NO. MHS123	1P2T w/center OFF   
MODEL NO. MHS133	1P3T   

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[MHS122](#)