

NK series

Subminiature slide switches

☐ The smallest changeover

UG1410A

☐ Flush and raised actuators

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : 0,5A 12V
- Minimum load : 1mA 10mV
- Initial contact resistance : 20 mΩ max.
- Insulation resistance : 10.000 MΩ min. at 500VDC
- Dielectric strength : 250 Vrms. 50 Hz min. between terminals
- 2.000 Vrms 50 Hz min. between adjacent poles of switches placed side by side
- Electrical life with nominal load : 2.000 cycles
- Capacitance : < 1,5 pF


MATERIALS

- Case : PA6/6, glass filled, UL94-V0
- Actuator : PA6/6, glass filled, UL94-V0
- Contacts : gold over nickel

GENERAL SPECIFICATIONS

- Wave solderable : flux sealed
- End stackable, 2,54 (.100) terminal to terminal pitch - 4 switches max., hole dia. 1 mm (.039)
- Travel : 1,6 mm (.062)
- Operating temperature : -40°C to +85°C
- Soldering temperature : 250°C for 5 sec. max.
- Moisture test : 21 days at 95 % RH (IEC 68-2-3)

EXAMPLES OF LAYOUT



Straight PC terminals



Flush actuator
NK236





Raised actuator
NK236H

I 1-3 II 1-2



ON - ON

ON - ON




Right angle terminals



Flush actuator
NK236W





Raised actuator
NK236WH

I 1-3 II 1-2



ON - ON

ON - ON



Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Packaging unit : 100 pieces.

The company reserves the right to change specifications without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[NK236WH](#) [NK236](#) [NK236W](#) [NK236H](#)