


## 1:2 Transformer 5 – 300 MHz

Rev. V3

### Features


- 1:2 impedance
- Surface mount
- Available on tape and reel
- 260° reflow compatible
- RoHS compliant and Pb free
- Excellent temperature stability
- Suitable for all CATV, Broadband and FTTX applications.



### Description

MACOM's MABA-011050 is a 1:2 transformer. This transformer is ideally suited for CATV Broadband applications.

### Functional Schematic



### Ordering Information

Part Number	Package
MABA-011050	Tape & Reel
MABA-011050-TB	Customer test board

### Pin Configuration

Pin No.	Function
1	Primary Dot (input)
2	Secondary Dot (output 1)
3	Centre tap (RF ground)
4	Secondary (output 2)
5	Primary (ground)

## 1:2 Transformer 5 – 300 MHz

Rev. V3

Electrical Specifications:  $T_A = 25^\circ\text{C}$ ,  $Z_0 = 75\ \Omega$ ,  $P_{in} = 0\text{dBm}$


Parameter	Conditions	Units	Min	Typ	Max
Frequency Range		MHz	5		300
Impedance		$\Omega$		75	
Impedance Ratio				1:2	
Insertion Loss 1 (Pin1 - Pin2)	5 - 150 MHz	dB	-	0.6	0.8
	150 - 300 MHz	dB	-	0.8	1.0
Insertion Loss 2 (Pin1 - Pin4)	5 - 300 MHz	dB	-	0.5	0.7
Amplitude Balance	5 - 150 MHz	dB	-	0.1	0.2
	150 - 300 MHz	dB	-	0.2	0.5
Phase Balance (Ref value $180^\circ$ )	5 - 150 MHz	$^\circ$	-	0.06	1.0
	150 - 300 MHz	$^\circ$	-	0.1	2.5
Input Return Loss (Pin1)	5 - 150 MHz	dB	18	19	-
	150 - 300 MHz	dB	16	18	-

## Recommended Maximum Ratings


Parameter	Units	Min	Max
Input Power	mW		250
DC Current	mA		600
Operating Temperature Range	$^\circ\text{C}$	-40	+125

Full temperature plots available on request

## Outline Drawing



## PCB Layout









1. Dimensions in mm.
2. Tolerance:  $\pm 0.2$  mm unless otherwise noted.
3. Model number and lot code are printed on the reel.
4. Lead plating: ENIG.

## Tape & Reel Information

Parameter	Units	Value
Qty per reel	-	900
Reel Size	mm	330
Tape Width	mm	16.00
Pitch	mm	12.00
Ao	mm	6.60
Bo	mm	7.40
Ko	mm	2.90
Orientation	-	F33
Reference Application Note ANI-019 for orientation		

## Typical Performance Curves



M/A-COM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with M/A-COM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[MABA-011050](#)