













M Series

Standard Size Slide Switches













SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SPECIFICATIONS	FEATURES
<p>Contact rating: 300 mA at 125 VAC or 30 VDC</p> <p>Initial contact resistance: 20 milliohms max.</p> <p>Insulation resistance: 100 megohms min. at 500 VDC</p> <p>Dielectric strength: 500 volts RMS at sea level</p> <p>Electrical life: 10,000 cycles min.</p> <p>Operating temperature range: -10°C to +60°C</p> <p>Solder heat resistance: 260°C max. for 3 seconds</p> <p>Solvent washing permissible</p>	<ul style="list-style-type: none"> Bifurcated wiping contact design. Epoxy sealed terminals. Wash-through open frame construction. Reinforcing mounting legs. Many actuator styles and lengths available on request.
MATERIALS	
<p>Contacts & terminals: Silver plated</p> <p>Housing: Tin plated steel</p> <p>Actuator: Thermoplastic</p> <p>Base: Phenolic laminated sheet</p>	<p>Terminal seal: Epoxy</p>

MODEL NO.			
M12R			
 <p>RIGHT ANGLE ACTUATOR</p>	<p>1P2T</p>  <p>SCHMATIC</p>	 <p>MECHANICAL OUTLINE</p>	 <p>P.C. BOARD LAYOUT</p>
MODEL NO.			
M13R			
 <p>RIGHT ANGLE ACTUATOR</p>	<p>1P3T</p>  <p>SCHMATIC</p>	 <p>MECHANICAL OUTLINE</p>	 <p>P.C. BOARD LAYOUT</p>
MODEL NO.			
M13AR			
 <p>RIGHT ANGLE ACTUATOR</p>	<p>1P3T</p>  <p>SCHMATIC</p>	 <p>MECHANICAL OUTLINE</p>	 <p>P.C. BOARD LAYOUT</p>

M Series

Standard Size Slide Switches

















<p>MODEL NO.</p> <p>M22</p>  <p style="text-align: center;">VERTICAL ACTUATOR</p>	<p style="text-align: center;">2P2T</p> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;">  <p>● = COMMON</p> </div> <div style="text-align: center;">  <p>MECHANICAL OUTLINE</p> </div> <div style="text-align: center;">  <p>P.C. BOARD LAYOUT</p> </div> </div>
<p>MODEL NO.</p> <p>M23</p>  <p style="text-align: center;">VERTICAL ACTUATOR</p>	<p style="text-align: center;">2P3T</p> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;">  <p>● = COMMON</p> </div> <div style="text-align: center;">  <p>MECHANICAL OUTLINE</p> </div> <div style="text-align: center;">  <p>P.C. BOARD LAYOUT</p> </div> </div>
<p>MODEL NO.</p> <p>M23R</p>  <p style="text-align: center;">RIGHT ANGLE ACTUATOR</p>	<p style="text-align: center;">2P3T</p> <div style="display: flex; justify-content: space-around;"> <div style="text-align: center;">  <p>● = COMMON</p> </div> <div style="text-align: center;">  <p>MECHANICAL OUTLINE</p> </div> <div style="text-align: center;">  <p>P.C. BOARD LAYOUT</p> </div> </div>

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

M Series













Standard Size Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO. M42		4P2T 			SCHMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. M42R		4P2T 			SCHMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. M42A		4P2T 			SCHMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. M43		4P3T 			SCHMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT

M Series

Standard Size Slide Switches

MODEL NO.	4P3T		
M43R			
 <p style="text-align: center;">RIGHT ANGLE ACTUATOR</p>	 <p style="text-align: center;">SCHEMATIC</p>	 <p style="text-align: center;">MECHANICAL OUTLINE</p>	 <p style="text-align: center;">P.C. BOARD LAYOUT</p>
MODEL NO.	6P2T		
M62R			
 <p style="text-align: center;">RIGHT ANGLE ACTUATOR</p>	 <p style="text-align: center;">SCHEMATIC</p>	 <p style="text-align: center;">MECHANICAL OUTLINE</p>	 <p style="text-align: center;">P.C. BOARD LAYOUT</p>
MODEL NO.	6P2T		
M62A			
 <p style="text-align: center;">VERTICAL ACTUATOR</p>	 <p style="text-align: center;">SCHEMATIC</p>	 <p style="text-align: center;">MECHANICAL OUTLINE</p>	 <p style="text-align: center;">P.C. BOARD LAYOUT</p>

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[M13AR](#) [M23](#) [M43R](#) [M12R](#) [M42](#) [M42A](#) [M42R](#) [M62A](#) [M62R](#) [M43G](#)