

NK series

Subminiature slide switches



DISTINCTIVE FEATURES

The smallest changeover

Flush and raised actuators

Straight PC and right angle terminals



ENVIRONMENTAL SPECIFICATIONS

- Operating temperature : -40 °C to +85 °C (-40 °F to +185 °F)
- Moisture test : 21 days at 95 % RH (IEC 68-2-3)



ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : 0.5 A 12 V
- Minimum load : 1 mA 10 mV
- Initial contact resistance : 20 mΩ max.
- Insulation resistance : 10,000 MΩ min. at 500 VDC
- Dielectric strength :
250 Vrms. 50 Hz min. between terminals
2,000 Vrms 50 Hz min. between adjacent poles of switches placed side by side
- Electrical life with nominal load : 2,000 cycles
- Capacitance : < 1.5 pF



GENERAL SPECIFICATIONS

- Soldering temperature : 250 °C (482 °F) for 5 sec. max.
- Wave solderable : flux sealed
- End stackable, 2.54 (.100) terminal to terminal pitch - 4 switches max., hole dia. 1 mm (.039)
- Travel : 1.6 mm (.062)



MATERIALS


- Case : PA6/6, glass filled, UL94-V0
- Actuator : PA6/6, glass filled, UL94-V0
- Contacts : gold over nickel

APEM products may be recycled at end-of-life for the re-claiming of valuable metal components.

The company reserves the right to change specifications without notice.



EXAMPLES OF LAYOUT




NK series

Subminiature slide switches

STRAIGHT PC TERMINALS




	I 1-3		II 1-2
Flush actuator	NK236	ON - ON	
Raised actuator	NK236H	ON - ON	



RIGHT ANGLE TERMINALS



	I 1-3		II 1-2
Flush actuator	NK236W	ON - ON	
Flush actuator	NK236WH	ON - ON	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[NK236X1105](#) [NK236HX1105](#)