



High Q Hyperabrupt Tuning Varactors

MA4ST550 Series

V 2.00

Features

- High Q
- Usable Capacitance Change of 7:1
- Low Reverse Leakage for Good Post Tuning Drift Characteristics
- Reproducible C-V Curves

Description

The MA4ST550 family of high Q Silicon Hyperabrupt Tuning Varactors is available in a series of low parasitic capacitance microwave packages or in chip form. The MA4ST550 series of diodes is available with junction capacitances of approximately 0.8 pF to 8.2 pF at -4 volts. These diodes have capacitance change ratios as high as 7:1.

Applications

The MA4ST550 series is appropriate for use in VCOs with frequencies within the range of approximately 1-14 GHz where a large capacitance change is required. These diodes are suited for VCOs in missile seekers, telecommunication systems and electronic warfare systems with critical post tuning drift specifications.

Environmental Performance

All tuning varactors in ceramic packages are capable of meeting the performance tests dictated by the methods and procedures of the latest revisions of MIL-S-19500, MIL-STD-202 and MIL-STD-750 which specify mechanical, electrical, thermal and other environmental tests common to semiconductor products.

Case Styles



30



31



134

Maximum Ratings

Reverse Voltage	Same as Breakdown Voltage
Operating Temperature	- 65°C to +150°C
Storage Temperature	- 65°C to +200°C
Temperature Coefficient	400 ppm/°C at -4 Volts

High Q Hyperabrupt Tuning Varactors

MA4ST550 Series

V 2.00

Specifications @ T_A = +25°C

Breakdown Voltage = 22 Volts Minimum @ 10 Microamps

Reverse Current = 50 nAmps Maximum @ 20 Volts and 25°C

Model Number	Case ¹ Style	Total Capacitance ^{2,3} @ - 4V (pF)		Total Capacitance ^{2,3} @ - 20V (pF)		Typical Q - 4 Volts 50 MHz
		Min.	Max.	Min.	Max.	
MA4ST551	30	0.72	0.88	0.30	0.38	850
MA4ST552	30	0.90	1.10	0.34	0.42	650
MA4ST553	30	1.08	1.32	0.38	0.48	600
MA4ST554	30	1.35	1.65	0.43	0.58	600
MA4ST555	30	1.62	1.98	0.51	0.68	550
MA4ST556	30	1.98	2.42	0.58	0.78	500
MA4ST557	30	2.43	2.97	0.68	0.88	500
MA4ST558	30	2.97	3.63	0.82	1.02	500
MA4ST559	30	3.51	4.29	0.93	1.18	450
MA4ST560	30	4.23	5.16	1.13	1.43	450
MA4ST561	30	5.04	6.16	1.33	1.63	450
MA4ST562	30	6.12	7.48	1.58	1.98	400
MA4ST563	30	7.38	9.02	1.88	2.38	400

Notes:

1. The standard case style is 30. Other packages and chips shown at the bottom of this page are available. When ordering, specify the desired case style by adding the case designation as a suffix to the model number. (i.e. MA4ST550-134 is a 15 X 15 mil chip diode. See appendix for complete dimensions.)

2. Capacitance is measured at 1 MHz.

3. The total capacitance values shown are for devices housed in case style 30. Other case styles will result in different values due to different case parasitics. Case parasitics (C_p and L_p) are given for available case styles along with the outline drawings in the appendix.

Case Styles



30



31



94



120



134



1056



1088

M/A-COM, Inc.

M/A-COM, Inc.

Specifications Subject to Change Without Notice.

4-19

4-18

North America: Tel. (800) 366-2266
Fax (800) 618-8883


Asia/Pacific: Tel. +81 (03) 3226-1671
Fax +81 (03) 3226-1451

Europe: Tel. +44 (1344) 889 595
Fax +44 (1344) 300 020

North America: Tel. (800) 366-2266
Fax (800) 618-8883

Asia/Pacific: Tel. +81 (03) 3226-1671
Fax +81 (03) 3226-1451

Europe: Tel. +44 (1344) 889 595
Fax +44 (1344) 300 020



DIM.	INCHES		MILLIMETERS	
	MIN.	MAX.	MIN.	MAX.
A	0.094	0.102	2.39	2.59
B	0.031	0.044	0.79	1.12
C	0.019	0.021	0.48	0.53
D	0.003	0.006	0.076	0.15
E	0.130	0.170	3.30	4.32

Notes:

$C_p = 0.15$ pF Typical

$L_s = 0.40$ nH Typical

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[MA4ST553-186](#)