

18000 series

Snap-action momentary pushbutton switches



DISTINCTIVE FEATURES

Panel and PC mount models

Snap-in panel mounting version

Tactile feedback



ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold plated brass contacts : 100 mA - 30 VDC
 - gold plated silver contacts : 1 A 30 VDC
- Initial contact resistance : 50 mΩ max.
- Insulation resistance : 1,000 MΩ min.
- Dielectric strength : 1,000 Vrms 50 Hz min.
- Electrical life : 60,000 cycles at full load



GENERAL SPECIFICATIONS

- Total travel : 0.5 mm (.019)
- Torque : 1.25 Nm (.922 Ft.lb) max. applied to nut
- Operating temperature : -30 °C to +65 °C (-22 °F to +149 °F)
- Soldering : 300 °C (572 °F), 3 sec. max.



MATERIALS

- Case : PBT
- Actuator : polyamide, glass filled
- Bushing : brass, nickel plated
- Housing : stainless steel
- Bracket : tin plated steel
- Contacts
 - AD : silver, gold plated
 - CD : brass, gold plated
- Terminal seal : epoxy

APEM products may be recycled at end-of-life for the re-claiming of valuable metal components.

The company reserves the right to change specifications without notice.





18000 series

Snap-action momentary pushbutton switches




TERMINALS




ELECTRICAL FUNCTION

→ KEYWAY



Plain bushing




Threaded bushing




PANEL CUT-OUT


18500 - 18200




18700 - 18900



18800



With bezel U1200




With bezel U1210 for LED

18000 series

Snap-action momentary pushbutton switches



BUILD YOUR PART NUMBER



ABOUT THIS SERIES

On the following pages, you will find successively basic part numbers of switches and options in the same order as in above chart.

- Notice** : please note that not all combinations of above numbers are available. Refer to following pages for further information.
- Sealing boots** are available to protect the switches against dust and water. See "Sealing Boots" section on website.
- Mounting accessories** : standard hardware supplied with all models with Ø 6,35 (1/4) threaded bushing : 2 hex nuts 8 mm (.314) across flats, 1 locking ring and 1 lockwasher. Standard and special hardware is presented in the "Hardware" section of website.

18000 series

Snap-action momentary pushbutton switches

THREADED BUSHING

SOLDER LUG TERMINALS : 18500



		
Single pole	1-3	1-2
18535	ON	MOM
Double pole		
18545	ON	MOM



		
Single pole	1-3	1-2
18735	ON	MOM
Double pole		
18745	ON	MOM




		
Single pole	1-3	1-2
18235	ON	MOM
Double pole		
18245	ON	MOM




	 1-3	 1-2
Single pole	ON	MOM
18935	ON	MOM
Double pole	ON	MOM
18945	ON	MOM

→ KEYWAY


Shown with standard plunger




→ KEYWAY



→ KEYWAY





18000 series

Snap-action momentary pushbutton switches

SNAP-IN MOUNTING

SOLDER LUG TERMINALS : 18800



Single pole

18835

1-3
ON

1-2
MOM

Double pole

18845

ON

MOM

Available with straight PC terminals : see X662 under "Special options"

STRAIGHT PC TERMINALS

BRACKET MOUNTING - SINGLE POLE : 18230Y



18235Y

ON

MOM

STRAIGHT PC TERMINALS

BRACKET MOUNTING - DOUBLE POLE : 18240Y



18245Y

ON

MOM

RIGHT ANGLE TERMINALS

HORIZONTAL : 18200W



Single pole

18235W

ON

MOM


Double pole

18245W

ON

MOM

Shown with cap U910 + U1200



18000 series

Snap-action momentary pushbutton switches

PLAIN BUSHING - RIGHT ANGLE TERMINALS VERTICAL : 18200WW



Single pole

18235WW

1-3

ON

1-2


MOM

Double pole

18245WW

ON

MOM



CONTACT MATERIALS

BASIC P/N


AD Silver, gold plated
CD Brass, gold plated

PLUNGERS


BASIC P/N

Dash compulsory before plunger code.


Blank Ø 4 (.157) - long
-6 Ø 3.1 (.122)
-3 Ø 4 (.157) - short
-5 Ø 3.1 (.122)



Blank







-6



-3

-5




SPECIAL OPTIONS


BASIC P/N

X371 Plain bushing Ø 6.25 mm (.246) (instead of standard threaded bushing).

X372 Shorter threaded bushing Ø 6.35 (1/4).
Height 7 mm (.274).



X371




X372

Snap-action momentary pushbutton switches


SPECIAL OPTIONS (CONTINUED)

BASIC P/N

- | | |
|------|---|
| X386 | Threaded bushing Ø 6.35 mm (1/4) to replace plain bushing on models W - WW and Y. |
| X438 | Plain bushing Ø 6.25 mm (.246). Height 7,2 mm (.283) - without shoulder. |
| X624 | Straight PC terminals - bracket mounting - with shorter bushing and plunger |
| X662 | Snap-in mounting - straight PC terminals |



X386



X438

OPTION X624 - SINGLE POLE




18235Y -2X624



ON



MOM



OPTION X624 - DOUBLE POLE




18245Y -2X624




ON



MOM




OPTION X662



18000 series


Snap-action momentary pushbutton switches




For cap colors, replace last "0" by number :

1	Blue	5	Yellow
1/4	Dark blue	6	Red
2	Black	7	Ivory
3	Green	7/1	White
4	Grey	9	Orange


CAPS FOR Ø 4 (.157) PLUNGERS (-13, -3)



CAPS FOR Ø 3.1 (.122) PLUNGERS (-5, -6)



CAPS FOR Ø 3.1 (.122) PLUNGERS (-5, -6)



18000 series

Snap-action momentary pushbutton switches

BEZELS




For cap colors, replace last "0" by number :


1	Blue	5	Yellow
1/4	Dark blue	6	Red
2	Black	7	Ivory
3	Green	7/1	White
4	Grey	9	Orange

STANDARD PANEL MOUNTING

Panel thickness with bezel : 1 mm (.039) to 2.5 mm (.098)




18800 + U910 + U1200




18800 + U910 + U1210

FOR BRACKET MOUNTING MODELS (18200Y & 18200YX624)




U3200

FOR SNAP-IN MODELS (18800 - 18800X662)



U1200



U1210
For LED Ø 5 - not supplied


DRESS NUTS

Order separately. For models with threaded bushing (18500 - 18700 - 18200 - 18900)
Chrome plated.


U1636 For caps U1140 and U2510

U840 For cap U480 and U2900


U825 For caps U630 and U3400



U1636



U840



U825

18000 series

Snap-action momentary pushbutton switches •
high currents



DISTINCTIVE FEATURES

Tactile feedback
High currents



ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : 7 A 30 VDC
- Initial contact resistance : 20 mΩ max. at 0.1 A 3 VDC
- Insulation resistance : 200,000 MΩ min. between terminals and frame
- Dielectric strength : 1,500 Vrms 50 Hz min.
- Electrical life : 60,000 cycles at full load



GENERAL SPECIFICATIONS

- Total travel : 0.9 mm (.035) approx.
- Operating temperature : -30 °C to +65 °C (-22 °F to +149 °F)



MATERIALS


- Case : diallylphthalate (DAP)
- Actuator : glass filled polyester
- Bushing : brass, nickel plated
- Housing : stainless steel
- Contacts : silver
- Terminal seal : epoxy

APEM products may be recycled at end-of-life for the re-claiming of valuable metal components.




ELECTRICAL FUNCTION

→ KEYWAY



PANEL CUT-OUT



18000 series

Snap-action momentary pushbutton switches •
high currents

THREADED BUSHING - SINGLE POLE



18635A




ON



MOM

Also available in double pole configuration.

→ KEYWAY



CAPS

BASIC P/N

+ U...

ROUND

U2400 Ø 5 (.196)
U2510 Ø 8 (.314)
U2130 Ø 9,4 (.370)
U2900 Ø 10 (.393)
U3400 Ø 15 (.590)

SQUARE

U910 Height 4 (.157)
U2340 Height 6 (.236)

For cap dimensions, see "Caps for Ø 3,1 (.122) plungers" on the preceding pages.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[18945AD](#) [18935AD](#) [18245YAD](#) [18535AD6](#) [18735AD5X372](#) [18835CD](#) [18235WAD5](#) [18245WCD5](#) [18845CD](#)