




**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Sensitivity Range	-44 ± 3 dB $R_L = 2.2$ k Ω $V_{CC} = 2.0$ V (1 kHz 0 dB = 1 μ Pa)
Impedance	Max. 2.2k Ω 1 kHz $R_L = 2.2$ k Ω)
Frequency	20 - 16000 Hz
Current Consumption	Max. 1.5 mA
Operating Voltage Range	1 - 10 V
Max SPL (dB)	120 dB
S/N Ratio	More than 58 dB
Sensitivity Reduction	2.0 - 1.5 V Variation less than 3 dB
Storage Condition	-20 ~ +60°C; R.H. < 45% ~ 75%
Operating Condition	-10 ~ +45°C; R.H. < 85%
Weight (g)	0.5
Options	For other options contact factory

Dimensions: (units: mm)**Filter****ROHS Compliant****Schematic Diagram****Packaging:** Bulk pack in quantities of 100pcs.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PMOF-6050S-44UQ](#)