



Features :

- 1000VDC I/O isolation
- Internal SMD technology
- Protection: Short circuit
- Cooling by free air convection
- Non-conductive plastic case
- SMD package styles
- 100% full load burn-in test
- Low cost / High reliability
- Approved: UL / CUL
- 1 year warranty


SPECIFICATION



ORDER NO.		SBT01L-05	SBT01M-05	SBT01L-09	SBT01M-09	SBT01L-12	SBT01M-12	SBT01L-15	SBT01M-15
OUTPUT	DC OUTPUT VOLTAGE	5V		9V		12V		15V	
	OUTPUT CURRENT RANGE	0 ~ 200mA		0 ~ 111mA		0 ~ 84mA		0 ~ 67mA	
	EFFICIENCY	70%	72%	74%	75%	74%	75%	75%	75%
	RATED POWER	1W							
	RIPPLE & NOISE (max.) Note.2	100mVp-p							
	LINE REGULATION Note.3	±1.2% for 1% input variation							
	LOAD REGULATION Note.4	±8.0%							
	VOLTAGE TOLERANCE	±8.0%							
	SWITCHING FREQUENCY(Typ.)	100KHz							
INPUT	VOLTAGE RANGE	4.5 ~ 5.5V	10.8 ~ 13.2V	4.5 ~ 5.5V	10.8 ~ 13.2V	4.5 ~ 5.5V	10.8 ~ 13.2V	4.5 ~ 5.5V	10.8 ~ 13.2V
	NORMAL VOLTAGE	5V	12V	5V	12V	5V	12V	5V	12V
	INPUT CURRENT	Full load	292mA	120mA	292mA	120mA	292mA	120mA	292mA
		No load	29mA	15mA	29mA	15mA	29mA	15mA	29mA
PROTECTION	PROTECTION	Fuse recommended							
	OVERLOAD	Momentary							
	SHORT CIRCUIT	Protection type : Broken							
		Momentary							
ENVIRONMENT	WORKING TEMP.	-40 ~ +85°C (Refer to output load derating curve)							
	WORKING HUMIDITY	20% ~ 90% RH non-condensing							
	STORAGE TEMP., HUMIDITY	-40 ~ +105°C, 10 ~ 95% RH							
	TEMP. COEFFICIENT	±0.03% / °C (0 ~ 50°C)							
	VIBRATION	10 ~ 500Hz, 2G 10min./1 cycle, period for 60min. each along X, Y, Z axes							
SAFETY & EMC	SAFETY STANDARDS	UL60950-1, CSA C22.2							
	WITHSTAND VOLTAGE	I/P-O/P: 1KVDC							
	ISOLATION RESISTANCE	I/P-O/P: 100M Ohms / 500VDC / 25°C / 70% RH							
OTHERS	MTBF	500khrs min. MIL-HDBK-217F(25°C)							
	DIMENSION	12.7*7.5*6.0mm or 0.50"*0.30"*0.24" inch (L*W*H)							
	WEIGHT	1.3g							

Mechanical Specification


Unit: mm (inch)



Pin Configuration

Pin No.	Output
1	-Vin
2	+Vin
3	NC
4	-Vout
5	+Vout
6	NC
7	NC
8	NC

Derating Curve



NOTE

1. All parameters are specified at normal input, rated load, 25°C 70% RH ambient.
2. Ripple & noise are measured at 20MHz by using a 12" twisted pair terminated with a 0.1uF & 47uF capacitor.
3. Line regulation is measured from low line to high line at rated load.
4. Load regulation is measured from 20% to 100% rated load.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

MEAN WELL:

[SBT01L-09](#) [SBT01L-12](#) [SBT01L-15](#) [SBT01M-05](#)