


N-Channel MOSFET

Power MOS 8™ is a high speed, high voltage N-channel switch-mode power MOSFET. A proprietary planar stripe design yields excellent reliability and manufacturability. Low switching loss is achieved with low input capacitance and ultra low C_{rss} "Miller" capacitance. The intrinsic gate resistance and capacitance of the poly-silicon gate structure help control slew rates during switching, resulting in low EMI and reliable paralleling, even when switching at very high frequency. Reliability in flyback, boost, forward, and other circuits is enhanced by the high avalanche energy capability.


APT14M100B

APT14M100S

Single die MOSFET



FEATURES

- Fast switching with low EMI/RFI
- Low $R_{DS(on)}$
- Ultra low C_{rss} for improved noise immunity
- Low gate charge
- Avalanche energy rated
- RoHS compliant 

TYPICAL APPLICATIONS

- PFC and other boost converter
- Buck converter
- Two switch forward (asymmetrical bridge)
- Single switch forward
- Flyback
- Inverters

Absolute Maximum Ratings

Symbol	Parameter	Ratings	Unit
I_D	Continuous Drain Current @ $T_C = 25^\circ\text{C}$	14	A
	Continuous Drain Current @ $T_C = 100^\circ\text{C}$	9	
I_{DM}	Pulsed Drain Current ^①	55	
V_{GS}	Gate-Source Voltage	±30	V
E_{AS}	Single Pulse Avalanche Energy ^②	875	mJ
I_{AR}	Avalanche Current, Repetitive or Non-Repetitive	7	A

Thermal and Mechanical Characteristics

Symbol	Characteristic	Min	Typ	Max	Unit
P_D	Total Power Dissipation @ $T_C = 25^\circ\text{C}$			500	W
$R_{\theta JC}$	Junction to Case Thermal Resistance			0.25	$^\circ\text{C/W}$
$R_{\theta CS}$	Case to Sink Thermal Resistance, Flat, Greased Surface		0.11		
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55		150	$^\circ\text{C}$
T_L	Soldering Temperature for 10 Seconds (1.6mm from case)			300	
W_T	Package Weight		0.22		oz
			5.9		g
Torque	Mounting Torque (TO-247 Package), 6-32 or M3 screw			10	in·lbf
				1.1	N·m

Static Characteristics
T_J = 25°C unless otherwise specified
APT14M100B_S

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
$V_{BR(DSS)}$	Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu A$	1000			V
$\Delta V_{BR(DSS)}/\Delta T_J$	Breakdown Voltage Temperature Coefficient	Reference to 25°C, $I_D = 250\mu A$		1.15		V/°C
$R_{DS(on)}$	Drain-Source On Resistance ^③	$V_{GS} = 10V, I_D = 7A$		0.71	0.88	Ω
$V_{GS(th)}$	Gate-Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 1mA$	3	4	5	V
$\Delta V_{GS(th)}/\Delta T_J$	Threshold Voltage Temperature Coefficient			-10		mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 1000V, T_J = 25^\circ C$ $V_{GS} = 0V, T_J = 125^\circ C$			100 500	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS} = \pm 30V$			±100	nA

Dynamic Characteristics
T_J = 25°C unless otherwise specified

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
g_{fs}	Forward Transconductance	$V_{DS} = 50V, I_D = 7A$		16		S
C_{iss}	Input Capacitance	$V_{GS} = 0V, V_{DS} = 25V$ $f = 1MHz$		3965		pF
C_{rss}	Reverse Transfer Capacitance			55		
C_{oss}	Output Capacitance			335		
$C_{o(cr)}^{④}$	Effective Output Capacitance, Charge Related	$V_{GS} = 0V, V_{DS} = 0V \text{ to } 667V$		135		
$C_{o(er)}^{⑤}$	Effective Output Capacitance, Energy Related			70		
Q_g	Total Gate Charge	$V_{GS} = 0 \text{ to } 10V, I_D = 7A,$ $V_{DS} = 500V$		120		nC
Q_{gs}	Gate-Source Charge			21		
Q_{gd}	Gate-Drain Charge			60		
$t_{d(on)}$	Turn-On Delay Time	Resistive Switching $V_{DD} = 667V, I_D = 7A$ $R_G = 4.7\Omega^{⑥}, V_{GG} = 15V$		28		ns
t_r	Current Rise Time			29		
$t_{d(off)}$	Turn-Off Delay Time			95		
t_f	Current Fall Time			26		

Source-Drain Diode Characteristics

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
I_S	Continuous Source Current (Body Diode)	MOSFET symbol showing the integral reverse p-n junction diode (body diode)			14	A
I_{SM}	Pulsed Source Current (Body Diode) ^①				56	
V_{SD}	Diode Forward Voltage	$I_{SD} = 7A, T_J = 25^\circ C, V_{GS} = 0V$			1	V
t_{rr}	Reverse Recovery Time	$I_{SD} = 7A, V_{DD} = 100V^{②}$ $di_{SD}/dt = 100A/\mu s, T_J = 25^\circ C$		1065		ns
Q_{rr}	Reverse Recovery Charge			22		μC
dv/dt	Peak Recovery dv/dt	$I_{SD} \leq 7A, di/dt \leq 1000A/\mu s, V_{DD} = 667V,$ $T_J = 125^\circ C$			10	V/ns

① Repetitive Rating: Pulse width and case temperature limited by maximum junction temperature.

② Starting at $T_J = 25^\circ C, L = 35.71mH, R_G = 4.7\Omega, I_{AS} = 7A$.

③ Pulse test: Pulse Width < 380μs, duty cycle < 2%.

④ $C_{o(cr)}$ is defined as a fixed capacitance with the same stored charge as C_{OSS} with $V_{DS} = 67\%$ of $V_{(BR)DSS}$.

⑤ $C_{o(er)}$ is defined as a fixed capacitance with the same stored energy as C_{OSS} with $V_{DS} = 67\%$ of $V_{(BR)DSS}$. To calculate $C_{o(er)}$ for any value of V_{DS} less than $V_{(BR)DSS}$, use this equation: $C_{o(er)} = -1.15E-7/V_{DS}^2 + 2.03E-8/V_{DS} + 3.93E-11$.

⑥ R_G is external gate resistance, not including internal gate resistance or gate driver impedance. (MIC4452)

Microsemi reserves the right to change, without notice, the specifications and information contained herein.




Figure 1, Output Characteristics




Figure 2, Output Characteristics



Figure 3, $R_{DS(ON)}$ vs Junction Temperature

Figure 4, Transfer Characteristics




Figure 5, Gain vs Drain Current




Figure 6, Capacitance vs Drain-to-Source Voltage




Figure 7, Gate Charge vs Gate-to-Source Voltage




Figure 8, Reverse Drain Current vs Source-to-Drain Voltage




Figure 9, Forward Safe Operating Area




Figure 10, Maximum Forward Safe Operating Area





Figure 11. Maximum Effective Transient Thermal Impedance Junction-to-Case vs Pulse Duration

TO-247 (B) Package Outline


Ⓔ1 SAC: Tin, Silver, Copper



Dimensions in Millimeters (Inches)

D³PAK Package Outline

Ⓔ3 100% Sn Plated



Dimensions in Millimeters (Inches)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[APT14M100S](#)