

MOSFET Driver Hybrid

The DRF1211 hybrid includes a high power gate driver and the power MOSFET. It was designed to provide the system designer increased flexibility and lowered cost over a non-integrated solution.

FEATURES

- Switching Frequency: DC TO 30MHz
- Low Pulse Width Distortion
- Single Power Supply
- 1V CMOS Schmitt Trigger Input 1V
 Hysteresis
- Inverting Non-Inverting Select
- RoHS Compliant

Driver Absolute Maximum Ratings

- Switching Speed 3-4ns
- B_{Vds} = 1Kv
- I_{ds} = 26A avg.
- R_{DS(on)}≤ .55 Ohm
- P_D = 1000W



TYPICAL APPLICATIONS

- Class C, D and E RF Generators
- Switch Mode Power Amplifiers
- Pulse Generators
- Ultrasound Transducer Drivers
- Acoustic Optical Modulators

	- · · · · · · · · · · · · · · · · · · ·				
Symbol	Parameter	Min	Тур	Мах	Unit
V _{dd}	Supply Voltage			15	V
IN	Input Single Voltages			-5.0 to 15.3	v
I _{о РК}	Output Current Peak			15	А
T	Operating Temperature			150	°C

Driver Specifications

Symbol	Parameter	Min	Тур	Max	Unit
V _{dd}	Supply Voltage	8		15	N/
IN	Input Voltage	-5.0		V _{dd} +0.3	V
IN _(R)	Input Voltage Rising Edge		2.5		20
IN _(F)	Input Voltage Falling Edge		2.5		ns
I _{DDQ}	Quiescent Current		15	25	mA
Ι _ο	Output Current		15		А
C _{oss}	Output Capacitance		2500		
C _{iss}	Input Capacitance		35		р⊢
R _{IN}	Input Parallel Resistance		1		MΩ
V _{T(ON)}	V threshhold On, V _{dd} = 12V, Vin = 0 to 5V Ramp	2.2		3.2	V
V _{T(OFF)}	V threshhold On, V _{dd} = 12V, Vin = 0 to 5V Ramp	1.0		1.9	v
t,	Rise Time 10% to 90%, V_{dd} = 12V, Vin = 0 to 5V, R_L = 1.0 Ω , C_L = 2nF	1.5	2.5	3.0	
t _r	Fall Time 90% to 10%, V_{dd} = 12V, Vin = 0 to 5V, R_L = 1.0 Ω , C_L = 2nF	1.5	2.5	3.0	
T _{D(ON)}	On Delay Time, 50% to 50%, V_{dd} = 12V, Vin = 0 to 5V, R_{L} = 1.0 Ω , C_{L} = 2nF		18		115
T _{D(OFF)}	Off Delay Time, 50% to 50%, V_{dd} = 12V, Vin = 0 to 5V, R_{L} = 1.0 Ω , C_{L} = 2nF		18		

Microsemi Website - http://www.microsemi.com



DRF1211

1000V, 26A, 30MHz

Driver Output Characteristics

Symbol	Parameter	Min	Тур	Max	Unit
C _{out}	Output Capacitance		2500		pF
R _{out}	Output Resistance		0.5		Ω
L _{out}	Output Inductance	2	3	4	nH
F _{MAX}	Operating Frequency CL = $3nF + 50\Omega$			60	MHz

Driver Thermal Characteristics

Symbol	Parameter	Min	Тур	Max	Unit
R _{θJC}	Thermal Resistance Junction to Case		1.5		°C/W
T _j , T _{STG}	Operating and Storage Temperature		-55 to 150		°C
P _{DC}	Maximum Power Dissipation @ T _c = 25°C		80		W

MOSFET Absolute Maximum Ratings

Symbol	Parameter		Тур	Max	Unit
BV _{DSS}	Drain Source Voltage				V
I _D	Continuous Drain Current $T_c = 25^{\circ}C \otimes I_p = 13A$			26	А
R _{DS(on)}	Drain-Source On State Resistance			0.7	Ω
T _{jmax}	Operating Temperature			175	°C

MOSFET Dynamic Characteristics

Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
C _{iss}	Input Capacitance	$V_{qs} = 0$		4000		
C _{oss}	Output Capacitance	V _{DS} = 50V		460		pF
C _{rss}	Reverse Transfer Capacitance	f = 1 MHz		90		

MOSFET Thermal Characteristics

Symbol	Parameter		Тур	Max	Unit
R _{θJC}	Thermal Resistance Junction to Case (per MOSFET)		0.16	0.17	°C ///
R _{θJHS}	Thermal Resistance Junction to Heat Sink			0.22	C/W
T _{JSTG}	Storage Temperature			-55 to 150	°C
P _{DHS}	Maximum Power Dissipation @ T _{SINK} = 25°C			680	10/
P _{DC}	Total Power Dissipation @ $T_c = 25^{\circ}C$		1000		VV

Microsemi reserves the right to change, without notice, the specifications and information contained herein.



Figure 1, DRF1211 Simplified Circuit Diagram

The Simplified DRF1211 Circuit Diagram is illustrated above. By including the driver high speed by-pass capacitor (C1), the contribution to the internal parasitic loop inductance of the driver output is greatly reduced. This, coupled with the tight geometry of the hybrid, allows optimal gate drive to the MOSFET. This low parasitic approach, coupled with the Schmitt trigger input (IN), Kelvin signal ground (SG) and the Anti-Ring Function, provide improved stability and control in Kilowatt to Multi-Kilowatt, high Frequency applications. IN pin is referenced to the Kelvin ground (SG.) The signal is then applied to the intermediate drivers and level shifters; this section contains proprietary circuitry designed specifically for the ring abatement. The power drivers provide high current to the gate of the MOSFETS.











RECTANGULAR PULSE DURATION (SECONDS) Figure 3b, Maximum Effective Transient Thermal Impedance, Junction-To-Case vs Pulse Duration



Figure 4, DRF1211 Test Circuit

The Test Circuit illustrated above was used to evaluate the DRF1211 (available as an evaluation Board DRF12XX / EVALSW.) The input control signal is applied to the DRF1211 via IN(4) and SG(5) pins using RG188. This provides excellent noise immunity and control of the signal ground currents.

The +V_{DD} inputs (2,6) are by-passed (C1, C2, C4-C9), this is in addition to the internal by-passing mentioned previously. The capacitors used for this function must be capable of supporting the RMS currents and frequency of the gate load. R_L set for I_{DM} at V_{DS} max this load is used to evaluate the output performance of the DRF1211.

Pin Assignments		
Pin 1	GND	
Pin 2	+Vdd	
Pin 3	GND	
Pin 4	IN	
Pin 5	SG	
Pin 6	+Vdd	
Pin 7	GND	
Pin 8	Source	
Pin 9	Drain	
Pin 10	Source	



All dimensions are ± .005



HAZARDOUS MATERIAL WARNING

The ceramic portion of the device between leads and mounting flange is beryllium oxide. Beryllium oxide dust is highly toxic when inhaled. Care must be taken during handling and mounting to avoid damage to this area. These devices must never be thrown away with general industrial or domestic waste. BeO substrate weight: 1.973g. Percentage of total module weight which is BeO: 31%.



a **MICROCHIP** company

Microsemi Headquarters One Enterprise, Aliso Viejo,

One Enterprise, Also Vielo, CA 92556 USA (200) 713-4113 Outside the USA: +1 (949) 380-6100 Sales: +1 (949) 380-6136 Fax: +1 (949) 380-6136 Email: sales.support@microsemi.com www.microsemi.com

© 2020 Microsemi. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners. Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi ones on grant, explicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.

Microsemi, a wholly owned subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions, security technologies and scalable anti-tamper products; thermet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, California, and has approximately 4,800 employees globally. Learn more at www. microsemi.com.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Microchip: DRF1211