

Helping Customers Innovate, Improve & Grow



OX-171

The OX-171 is a high stability ovenized crystal oscillator in a 28 x 38 mm package, capable of aging rates of 0.06 ppb/day and temperature stabilities of 1ppb over an industrial temperature range. Driven by an SC-cut crystal, the oscillator provides excellent phase noise and Allan Deviation. The OX-171 is a member of the OX-17 series oscillators. Other oscillators in the series include the OX-170 standard oscillator, OX-172 optimized for 1588 solutions, and the OX-174 and OX-175 low phase noise oscillators. The Vectron design team will also help develop custom solutions where performance optimization is required for specific applications. Please contact the factory for customization options.

Features

- Reflow Process Compatible
- SC-Cut resonator
- Temperature stability to 0.4 ppb
- Aging rate options to 0.06 ppb/day
- Frequency Range 5 to 20 MHz
- Standard Frequencies: 5, 10, 12.8, 20 MHz

Applications

- Holdover reference
- Test equipment
- Synthesizers
- Military communication equipment
- Digital Switching

Performance Specifications


Frequency Stabilities ¹					
(Stabilities listed for 10 MHz, for stabilities above 10 MHz values may degrade, please contact factory)					
Parameter	Min	Typical	Max	Units	Condition
vs. operating temperature range (referenced to +25°C)	-0.4 -0.6 -0.8		+0.4 +0.6 +0.8	ppb	0 to +70°C -20 to +70°C -40 to +85°C
For better stability refer to the MX-060 or MX-041 datasheets					
Initial tolerance	-25		+25	ppb	at time of shipment, nominal EFC
vs. supply voltage change	-0.5		+0.5	ppb	$V_s \pm 5\%$
vs. load change	-0.2		+0.2	ppb	Load $\pm 5\%$
vs. aging / day	-1		+1	ppb	after 24 hours operation
vs. aging / day	-0.1		+0.1	ppb	after 72 hours operation
vs. aging/day	-0.06		+0.06	ppb	after 7 days operation
vs. aging / year	-15		+15	ppb	after 72 hours operation
vs. aging / year (following year)	-10		+10	ppb	
vs. aging/ 10 years	-75		+75	ppb	
retrace ²	-2		+2	ppb	
Warm-up time			5	minutes	to ± 5 ppb of final frequency (1 hour reading) @ +25°C

Performance Specifications

Supply Voltage (Vs)					
Parameter	Min	Typical	Max	Units	Condition
Supply Voltage (Vs)	3.135	3.3	3.465	VDC	Ordering Code E
	4.75	5.0	5.25	VDC	Ordering Code D
	11.4	12.0	12.6	VDC	Ordering code B , temp stability T and J only
Power Consumption			4	Watts	during warm-up, all temperatures
			1.5	Watts	steady state @ +25°C
		3.3		Watts	steady state @ -40°C
		0.5		Watts	steady state @ +85°C
RF Output					
start time		1	2	s	time required to achieve 90% of amplitude
Signal [standard]	HCMOS				
Load		15		pF	
Signal Level (Vol)			0.4	VDC	with Vs=3.3V and 15pF Load
			0.5	VDC	with Vs=5.0V & 12V and 15pF Load
Signal Level (Voh)	2.4			VDC	with Vs=3.3V and 15pF Load
	3.5				with Vs=5.0V & 12V and 15pF Load
Duty Cycle	45		55	%	@ (Voh-Vol)/2
Signal	Sine Wave				
Load		50		Ω	
Output Power @3,3V	2	5	8	dBm	
Output Power @ 5.0V,12 V	5	8	11	dBm	
Harmonics			-40	dBc	
Subharmonics			-40	dBc	frequencies >= 10 MHz
Frequency Tuning (EFC)					
Tuning Range	±125		±250	ppb	(fixed frequency option available)
Linearity		10		%	
Tuning Slope	Positive				
Input Impedance		100		kOhm	
Bandwidth Modulation	150			Hz	
Control Voltage Range	0.0	1.4	2.8	VDC	with Vs=3.3V
	0.0	2.0	4.0	VDC	with Vs=5.0V
	0.0	2.5	5	VDC	with Vs=12.0V
Reference Voltage Output (Vref)					
<p>The OX-171 can be configured with a reference voltage, but requires the use of a six pin package. This configuration requires a custom part number, and may degradethe stability of the part. Please contact the factory for ordering information.</p>					
Reference Voltage	2.75	2.8	2.85	VDC	with Vs = 3.3 VDC
	3.92	4.0	4.08	VDC	with Vs = 5.0 VDC
	4.9	5	5.1	VDC	with Vs =12 VDC


Additional Parameters								
Parameter	Min	Typical	Max	Units	Condition			
Phase Noise ³			-95 -125 -140 -145 -145	dBc/Hz dBc/Hz dBc/Hz dBc/Hz dBc/Hz	1 Hz 10 Hz 100 Hz 1 kHz 10 kHz	@ 10MHz		
For lower phase please review the OX-174 datasheet.								
Allan deviation			5 8 1 5	E-12 E-12 E-11 E-11	1 s tau 10 s tau 100 s tau 1000 s tau	@ 10MHz		
For oscillators with low ADEV requirements please review the OX-174 datasheet. For oscillators with TDEV and MTIE requirements please review the OX-172 datasheet								
g-sensitivity				1	ppb/g			
g-sensitivity of 0.5 ppb/g available in this package size. Please contact factory for ordering information. For g sensitivity <0.1 ppb/g please review the OX-043 series.								
Weight			25	g				
Absolute Maximum Ratings								
Supply Voltage (Vs)			6.5	V	with Vs=3.3 & 5.0 VDC			
			15.0	V	with Vs= 12 VDC			
Output Load			50	pF				
Operable Temperature Range	-55		+95	°C	operable temperature range implies the device will continue to operate with no long-term damage to unit however it will not be specification compliant outside the operating temperature range			
Environmental and Product Classification								
Shock (Endurance)	MIL-STD-202, Method 213, Condition J, 30g 11 ms							
Sine Vibration (Endurance)	MIL-STD-202, Method 201 and 204, Condition A, except 5g to 500 Hz, 1 sweep each axis							
Random Vibration (Endurance)	MIL-STD-202, Method 214, Condition I-D							
Humidity	MIL-STD-202, Method 103, Condition B, 100% rh							
Seal	MIL-STD-202, Method 112, Condition D, hermetic, washable							
Altitude	MIL-STD-202, Method 105, sea level to space							
Resistance to Soldering Heat	MIL-STD-202, Method 210, Condition A,B,C							
Terminal Strength	MIL-STD-202, Method 211, Condition C (5 bends at 45°, 2 lbs)							
Moisture Sensitive Level	1							
RoHS	compliant with exemption 7c-i							
Storage Temperature Range	-55		+125	°C				

OX-171 Frequency vs. Temperature




Frequency vs Temperature Plot -
Blue line - measured data-
Red line - curve fit data.

OX-171 Aging



Outline Drawing / Enclosure




Through hole Package configuration A

	Height "H"	Pin Length "L"
0	14	4.5 mm min
4	12.7	4.5 mm min

Pin Connections

1	Electronic Frequency Control Input (EFC) No connect for fixed frequency oscillators
2	No Connect
3	Supply Voltage Input (VS)
4	RF Output
5	Ground (Case)

Dimensions in mm



SMD Package configuration 1

	Height "H"
1	17
5	15.7

Pin Connections

2,4,5,6,7, 11,12,13	No Connect
1	Electronic Frequency Control Input (EFC) No Connect for Fixed frequency Oscillators
3	Supply Voltage Input (Vs)
8	RF Output
9,10	Ground (Case)

Ordering Information⁴

OX - 171 0 - D A E - 109 1 - 10M0000000

Product Family
OX: OCXO

Model
171

Height and Package

0: 14 mm, package A - THT
4: 12.7 mm, package A - THT
1: 17 mm, package B - SMD
5: 15.7 mm, package B - SMD

Supply Voltage

B: 12V
D: 5V
E: 3.3V
RF Output Code
A: HCMOS
E: Sinewave

Frequency
5M00000000
10M00000000
12M80000000
20M00000000
(others available on request)

Frequency Control
0: Fixed frequency
1: ±150 to ±250 ppb
Stability Code
400: ± 0.4 ppb
600: ± 0.6 ppb
800: ± 0.8 ppb
109: ± 1.0 ppb
159: ± 1.5 ppb
209: ± 2.0 ppb

Stability code - Temperature and Frequency Options

Frequency	0 to +70 °C	-20 to +70 °C	-40 to +85°C
5 to 10 MHz	400	600	800
> 10 MHz	109	159	209

Additional Ordering Options

Additional ordering options available include custom heights, custom aging rates, custom temperature ranges, custom temperature stabilities, custom phase noise requirements, improved g-sensitivity, and oscillators with voltage reference output on pin 2. These modifications require a custom dash number - please contact the factory for additional information.

Design Tools

Vectorn stocks the following items for small orders and prototype development:

OX-1710-DEE-8001-10M00000000

Vectorn stocks the following evaluation board for this product:

OCXO Evaluation Board

Application Notes:

None

Notes:

1. Unless otherwise stated, all values are valid after warm-up time and refer to typical conditions for supply voltage, frequency control voltage, load, and temperature (25°C).
2. Retrace defined as f1-fo where fo is the reading after the unit has been on power for 24 hours, and f1 is the frequency after 24 hours off followed by 60 minutes on.
3. Phase noise degrades with increasing output frequency.
4. Not all options and codes available at all frequencies.

Contact Information

USA:

100 Watts Street
Mt Holly Springs, PA 17065
Tel: 1.717.486.3411
Fax: 1.717.486.5920

Europe:

Landstrasse
74924 Neckarbischofsheim
Germany
Tel: +49 (0) 7268.801.0
Fax: +49 (0) 7268.801.281



Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATION OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING, BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly, or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip and Vectorn names and logos are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[OX-1715-DAE-2090-20M0000000](#) [OX-1710-DEE-8001-10M0000000](#)