


60 Amp Schottky Rectifier

SBR6035PF — SBR6045PF



Dim.	Millimeter					Notes
	Inches	Minimum	Maximum	Minimum	Maximum	
A	.590	.630	15.0	16.0	Dia.	
B	.499	.510	12.6	13.0	Dia.	
C	—	.600	—	15.2		
D	.350	.370	8.90	9.40		
E	.090	.130	2.28	3.30		
F	.097	.103	2.46	2.62	Dia.	
G	.030	.035	.762	.900		
H	.500	.510	12.7	13.0	Dia.	

Microsemi Catalog Number	Working Reverse Voltage	Peak Reverse Voltage	Repetitive Peak Reverse Voltage
SBR6035PF*	35V	35V	35V
SBR6040PF*	40V	40V	40V
SBR6045PF*	45V	45V	45V

*Add the Suffix R for Reverse Polarity

- Schottky Barrier Rectifier
- Guard Ring Protected
- 150°C Junction Temperature
- V_{RRM} – 35 to 45 Volts
- Reverse Energy Tested

Electrical Characteristics

Average forward current	I _{F(AV)} 60 Amps	T _C = 89°C, Square wave, R _{θJC} = 1.0°C/W
Maximum surge current	I _{FSM} 800 Amps	8.3 ms, half sine, T _J = 150°C
Max repetitive peak reverse current	I _{R(OV)} 2 Amps	f = 1 KHz, 25°C, 1 μsec Square wave
Max peak forward voltage	V _{FM} .58 Volts	I _{FM} = 60A: T _J = 150°C*
Max peak forward voltage	V _{FM} .60 Volts	I _{FM} = 60A: T _J = 25°C*
Max peak reverse current	I _{RM} 600 mA	V _{RRM} , T _J = 125°C*
Max peak reverse current	I _{RM} 2 mA	V _{RRM} , T _J = 25°C
Maximum junction capacitance	C _J 2700 pF	V _R = 5.0V, T _J = 25°C

*Pulse test: Pulse width 300 μsec, Duty cycle 2%

Thermal and Mechanical Characteristics

Storage temp range	T _{STG}	-55°C to 175°C
Operating junction temp range	T _J	-55°C to 150°C
Max thermal resistance	R _{θJC}	1.0°C/W Junction to case
Weight		.32 ounces (9.2 grams) typical

LAWRENCE
Microsemi

6 Lake Street
Lawrence, MA 01841
PH: (978) 620-2600
FAX: (978) 689-0803
www.microsemi.com

05-30-07 Rev. 2

SBR6035PF — SBR6045PF

Figure 1
Typical Forward Characteristics




Figure 2
Typical Reverse Characteristics




Figure 3
Typical Junction Capacitance






Figure 4
Forward Current Derating



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[SBR6035PF](#)