

**Micro Commercial Components** 

ROHS

Micro Commercial Components 20736 Marilla Street Chatsworth

CA 91311

Phone: (818) 701-4933 Fax: (818) 701-4939

# SK82L THRU SK810L

8.0 Amp

**Schottky Rectifier** 

20 to 100 Volts

### **Features**

- High Current Capability
- Low Forward Voltage
- For Surface Mount Application
- Lead Free Finish/Rohs Compliant (Note1) ("P"Suffix designates Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Halogen free available upon request by adding suffix "-HF"

### **Maximum Ratings**

- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Typical Thermal Resistance: 18°C/W Junction to Lead


MCC Catalog Number	Device Marking	Maximum Reccurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
SK82L	SK82	20V	14V	20V
SK83L	SK83	30V	21V	30V
SK835L	SK835	35V	24.5V	35V
SK84L	SK84	40V	28V	40V
SK845L	SK845	45V	31.5V	45V
SK86L	SK86	60V	42V	60V
SK88L	SK88	80V	56V	80V
SK810L	SK810	100V	70V	100V

### Electrical Characteristics @ 25°C Unless Otherwise Specified


Average Forward Current	I <sub>F(AV)</sub>	8.0A	T <sub>J</sub> =95°C
Peak Forward Surge Current	I <sub>FSM</sub>	200A	8.3ms half sine
Maximum Instantaneous Forward Voltage SK82L-86L SK88L-810L	V <sub>F</sub>	.65V .80V	I <sub>FM</sub> =8.0A T <sub>A</sub> =25°C
Maximum DC Reverse Current At Rated DC Blocking Voltage	I <sub>R</sub>	1mA 20mA	T <sub>J</sub> =25°C T <sub>J</sub> =100°C
Typical Junction Capacitance	CJ	400pF	Measured at 1.0MHz, V <sub>R</sub> =4.0V

Note: 1. High Temperature Solder Exemptions Applied, see EU Directive Annex 7.

# DO-214AB (SMC) (LEAD FRAME)



DIMENSIONS							
	INCHES		ММ				
DIM	MIN	MAX	MIN	MAX	NOTE		
Α	.260	.280	6.60	7.11			
В	.220	.245	5.59	6.22			
С	.006	.012	0.15	0.31			
О	.030	.060	0.76	1.52			
П	.305	.320	7.75	8.13			
F	.079	.103	2.00	2.62			
G	.108	.128	2.75	3.25			
Н	.002	.008	0.050	0.203			





### SK82L thru SK810L

Figure 1 Typical Forward Characteristics





Figure 2 Forward Derating Curve 12 10 8.0 6.0 Amps 4.0 2.0 Single Phase, Half Wave 60Hz Resistive or Inductiv 0 <mark></mark> 120 140 160 180

> Average Forward Rectified Current - Amperes versus Junction Temperature -°C

Instantaneous Forward Current - Amperes versus Instantaneous Forward Voltage - Volts



Junction Capacitance - pF versus Reverse Voltage - Volts



60 80 100

40

## SK82L thru SK810L

**Micro Commercial Components** 

8 10 20

Cycles

Figure 4 Figure 5 Typical Reverse Characteristics Peak Forward Surge Current 600 6 500 4 400 2 300 10d°C Amps 200 1 .6 100 mAmps .1 Peak Forward Surge Current - Amperes versus Number Of Cycles At 60Hz - Cycles .04 .02 .01 .006 .004 SK82L-845L SK85L-810L .002 .001 40 60 80 100 120 140 Volts

Instantaneous Reverse Leakage Current - MicroAmperes versus Percent Of Rated Peak Reverse Voltage - Volts



#### **Micro Commercial Components**

#### **Ordering Information:**

Device	Packing		
Part Number-TP	Tape&Reel: 3Kpcs/Reel		

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

#### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Commercial Components (MCC):

SK810L-TP SK86L-TP SK88L-TP SK845L-TP SK84L-TP