

Features

- For surface mounted applications
- Low-profile package
- Ideal for automated placement
- Available in Unidirectional and Bi-directional
- 600 W peak pulse power capability with a 10/1000 μ s waveform
- Low incremental surge resistance, excellent clamping capability
- Very fast response time
- High temperature soldering guaranteed: 260 °C/10 s at terminals
- Meets MSL level 1
- Component in accordance to RoHS

Mechanical Data

- Polarity: Color Band Denotes Positive end(cathode) Except Bi-directional Types
- Maximum Soldering Temperature: 260°C for 10 Seconds
- Terminals: Solderable Per MIL-STD-750, Method 2026

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +150°C
- Storage Temperature Range: -55°C to +150°C
- Thermal Resistance :20°C/W Junction to Lead
- Thermal Resistance :15°C/W Junction to Case
- Thermal Resistance :100°C/W Junction to Ambient


Electrical Characteristics @ 25°C Unless Otherwise Specified

Peak Pulse Power Surge Current on 10/1000 μ s Waveform	I_{PP}	See the Table	Note 3
Peak Pulse Power Dissipation	P_{PP}	600W	Note 3,4,5
Steady State Power Dissipation	$P_{M(AV)}$	5.0W	Note 6
Peak Forward Surge Current	I_{FSM}	100A	8.3 ms Single Half Sine-Wave Unidirectional Only


NOTES:

1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. High Temperature Solder Exemption Applied, see EU Directive Annex 7a.
3. Non-repetitive current pulse, per Fig.3 and derated above $T_A=25^\circ\text{C}$ per Fig.4
4. Mounted on 5.0mm² copper pads to each terminal.
5. Peak pulse current waveform is 10/1000 μ s, with maximum duty Cycle of 0.01%.
6. Power dissipation, on infinite heat sink at $T_L=75^\circ\text{C}$

Pin Configuration:




600 Watt TVS 5.0 to 220 Volts



DIM	DIMENSIONS				NOTE
	INCHES		MM		
	MIN	MAX	MIN	MAX	
A	0.134	0.150	3.40	3.80	
B	0.075	0.083	1.90	2.10	
C	0.163	0.175	4.15	4.45	
D	0.201	0.220	5.10	5.60	
E	0.041	0.061	1.05	1.55	
F	0.028	0.053	0.70	1.35	
G	0.006	0.010	0.15	0.25	

Suggested Solder Pad Layout



Electrical Characteristics @ 25°C Unless Otherwise Specified

MCC PART NUMBER		REVERSE STAND-OFF VOLTAGE V_{WM}	BREAKDOWN VOLTAGE $V_{(BR)} @ I_T$ (VOLTS)			MAXIMUM CLAMPING VOLTAGE @ I_{PP}	PEAK PULSE CURRENT $I_{PP}^{(5)}$	MAXIMUM REVERSE LEAKAGE @ V_{WM} $I_D^{(6)}$	MARKING CODE	
UNI-POLAR	BI-POLAR	(VOLTS)	MIN	MAX	$I_T^{(4)}$ (mA)	(VOLTS)	(AMPS)	(μ A)	UNI	BI
SMBF5.0A	SMBF5.0CA(4)	5	6.4	7.07	10	9.2	65.22	800	5V0A	5V0CA
SMBF6.0A	SMBF6.0CA	6	6.67	7.37	10	10.3	58.25	800	6V0A	6V0CA
SMBF6.5A	SMBF6.5CA	6.5	7.22	7.98	10	11.2	53.57	500	6V5A	6V5CA
SMBF7.0A	SMBF7.0CA	7	7.78	8.6	10	12	50	200	7V0A	7V0CA
SMBF7.5A	SMBF7.5CA	7.5	8.33	9.21	1	12.9	46.51	100	7V5A	7V5CA
SMBF8.0A	SMBF8.0CA	8	8.89	9.83	1	13.6	44.12	50	8V0A	8V0CA
SMBF8.5A	SMBF8.5CA	8.5	9.44	10.4	1	14.4	41.67	10	8V5A	8V5CA
SMBF9.0A	SMBF9.0CA	9	10	11.1	1	15.4	38.96	5	9V0A	9V0CA
SMBF10A	SMBF10CA	10	11.1	12.3	1	17	35.29	5	10A	10CA
SMBF11A	SMBF11CA	11	12.2	13.5	1	18.2	32.97	5	11A	11CA
SMBF12A	SMBF12CA	12	13.3	14.7	1	19.9	30.15	5	12A	12CA
SMBF13A	SMBF13CA	13	14.4	15.9	1	21.5	27.91	1	13A	13CA
SMBF14A	SMBF14CA	14	15.6	17.2	1	23.2	25.86	1	14A	14CA
SMBF15A	SMBF15CA	15	16.7	18.5	1	24.4	24.59	1	15A	15CA
SMBF16A	SMBF16CA	16	17.8	19.7	1	26	23.08	1	16A	16CA
SMBF17A	SMBF17CA	17	18.9	20.9	1	27.6	21.74	1	17A	17CA
SMBF18A	SMBF18CA	18	20	22.1	1	29.2	20.55	1	18A	18CA
SMBF19A	SMBF19CA	19	21.1	23.3	1	30.8	19.49	1	19A	19CA
SMBF20A	SMBF20CA	20	22.2	24.5	1	32.4	18.52	1	20A	20CA
SMBF22A	SMBF22CA	22	24.4	26.9	1	35.5	16.9	1	22A	22CA
SMBF24A	SMBF24CA	24	26.7	29.5	1	38.9	15.42	1	24A	24CA
SMBF26A	SMBF26CA	26	28.9	31.9	1	42.1	14.25	1	26A	26CA
SMBF28A	SMBF28CA	28	31.1	34.4	1	45.4	13.22	1	28A	28CA
SMBF30A	SMBF30CA	30	33.3	36.8	1	48.4	12.4	1	30A	30CA
SMBF33A	SMBF33CA	33	36.7	40.6	1	53.3	11.26	1	33A	33CA
SMBF36A	SMBF36CA	36	40	44.2	1	58.1	10.33	1	36A	36CA
SMBF40A	SMBF40CA	40	44.4	49.1	1	64.5	9.3	1	40A	40CA
SMBF43A	SMBF43CA	43	47.8	52.8	1	69.4	8.65	1	43A	43CA
SMBF45A	SMBF45CA	45	50	55.3	1	72.7	8.25	1	45A	45CA
SMBF48A	SMBF48CA	48	53.3	58.9	1	77.4	7.75	1	48A	48CA
SMBF51A	SMBF51CA	51	56.7	62.7	1	82.4	7.28	1	51A	51CA
SMBF54A	SMBF54CA	54	60	66.3	1	87.1	6.89	1	54A	54CA
SMBF58A	SMBF58CA	58	64.4	71.2	1	93.6	6.41	1	58A	58CA
SMBF60A	SMBF60CA	60	66.7	73.7	1	96.8	6.2	1	60A	60CA
SMBF64A	SMBF64CA	64	71.1	78.6	1	103	5.83	1	64A	64CA
SMBF70A	SMBF70CA	70	77.8	86	1	113	5.31	1	70A	70CA
SMBF75A	SMBF75CA	75	83.3	92.1	1	121	4.96	1	75A	75CA
SMBF78A	SMBF78CA	78	86.7	95.8	1	126	4.76	1	78A	78CA
SMBF80A	SMBF80CA	80	88.8	97.6	1	129.6	4.63	1	80A	80CA
SMBF85A	SMBF85CA	85	94.4	104	1	137	4.38	1	85A	85CA
SMBF90A	SMBF90CA	90	100	111	1	146	4.11	1	90A	90CA
SMBF100A	SMBF100CA	100	111	123	1	162	3.7	1	100A	100CA
SMBF110A	SMBF110CA	110	122	135	1	177	3.39	1	110A	110CA
SMBF120A	SMBF120CA	120	133	147	1	193	3.11	1	120A	120CA
SMBF130A	SMBF130CA	130	144	159	1	209	2.87	1	130A	130CA
SMBF140A	SMBF140CA	140	155	171	1	226.8	2.65	1	140A	140CA
SMBF150A	SMBF150CA	150	167	185	1	243	2.47	1	150A	150CA
SMBF160A	SMBF160CA	160	178	197	1	259	2.32	1	160A	160CA
SMBF170A	SMBF170CA	170	189	209	1	275	2.18	1	170A	170CA

Electrical Characteristics @ 25°C Unless Otherwise Specified

MCC PART NUMBER		REVERSE STAND-OFF VOLTAGE V_{WM}	BREAKDOWN VOLTAGE $V_{(BR)} @ I_T$ (VOLTS)			MAXIMUM CLAMPING VOLTAGE @ I_{PP}	PEAK PULSE CURRENT $I_{PP}^{(5)}$	MAXIMUM REVERSE LEAKAGE @ V_{WM} $I_D^{(6)}$	MARKING CODE	
UNI-POLAR	BI-POLAR	(VOLTS)	MIN	MAX	$I_T^{(4)}$ (mA)	(VOLTS)	(AMPS)	(μ A)	UNI	BI
SMBF180A	SMBF180CA	180	200	220	1	291.6	2.06	1	180A	180CA
SMBF190A	SMBF190CA	190	211	232	1	307.8	1.95	1	190A	190CA
SMBF200A	SMBF200CA	200	224	247	1	324	1.85	1	200A	200CA
SMBF220A	SMBF220CA	220	246	272	1	356	1.69	1	220A	220CA

- (4) Pulse test $p \leq 50$ ms.
- (5) Surge current waveform per Fig. 3
- (6) For bi-directional types having V_{RWM} of 10 V and less, the I_R limit is doubled.
- (7) For the bi-directional SMBJ5.0CA, the maximum V_{BR} is 7.25 V.

Curve Characteristics

Fig. 1 - Peak Pulse Power Rating Curve




Fig. 2 - Typical Transient Thermal Impedance




Fig. 3 - Pulse Waveform




Fig. 4 - Pulse Derating Curve




Fig. 5 - Maximum Non-Repetitive Peak Forward Surge Current





Fig. 6 - Steady State Power Dissipation



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:5Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Commercial Components (MCC):

[SMBF100A-TP](#) [SMBF100CA-TP](#) [SMBF10A-TP](#) [SMBF10CA-TP](#) [SMBF110A-TP](#) [SMBF110CA-TP](#) [SMBF11A-TP](#)
[SMBF11CA-TP](#) [SMBF120A-TP](#) [SMBF120CA-TP](#) [SMBF12A-TP](#) [SMBF12CA-TP](#) [SMBF130A-TP](#) [SMBF130CA-TP](#)
[SMBF13A-TP](#) [SMBF13CA-TP](#) [SMBF140A-TP](#) [SMBF140CA-TP](#) [SMBF14A-TP](#) [SMBF14CA-TP](#) [SMBF150A-TP](#)
[SMBF150CA-TP](#) [SMBF15A-TP](#) [SMBF15CA-TP](#) [SMBF160A-TP](#) [SMBF160CA-TP](#) [SMBF16A-TP](#) [SMBF16CA-TP](#)
[SMBF170A-TP](#) [SMBF170CA-TP](#) [SMBF17A-TP](#) [SMBF17CA-TP](#) [SMBF180A-TP](#) [SMBF180CA-TP](#) [SMBF18A-TP](#)
[SMBF18CA-TP](#) [SMBF190A-TP](#) [SMBF190CA-TP](#) [SMBF19A-TP](#) [SMBF19CA-TP](#) [SMBF200A-TP](#) [SMBF200CA-TP](#)
[SMBF20A-TP](#) [SMBF20CA-TP](#) [SMBF220A-TP](#) [SMBF220CA-TP](#) [SMBF22A-TP](#) [SMBF22CA-TP](#) [SMBF24A-TP](#)
[SMBF24CA-TP](#) [SMBF26A-TP](#) [SMBF26CA-TP](#) [SMBF28A-TP](#) [SMBF28CA-TP](#) [SMBF30A-TP](#) [SMBF30CA-TP](#)
[SMBF33A-TP](#) [SMBF33CA-TP](#) [SMBF36A-TP](#) [SMBF36CA-TP](#) [SMBF40A-TP](#) [SMBF40CA-TP](#) [SMBF43A-TP](#)
[SMBF43CA-TP](#) [SMBF45A-TP](#) [SMBF45CA-TP](#) [SMBF48A-TP](#) [SMBF48CA-TP](#) [SMBF5.0A-TP](#) [SMBF5.0CA-TP](#)
[SMBF51A-TP](#) [SMBF51CA-TP](#) [SMBF54A-TP](#) [SMBF54CA-TP](#) [SMBF58A-TP](#) [SMBF58CA-TP](#) [SMBF6.0A-TP](#)
[SMBF6.0CA-TP](#) [SMBF6.5A-TP](#) [SMBF6.5CA-TP](#) [SMBF60A-TP](#) [SMBF60CA-TP](#) [SMBF64A-TP](#) [SMBF64CA-TP](#)
[SMBF7.0A-TP](#) [SMBF7.0CA-TP](#) [SMBF7.5A-TP](#) [SMBF7.5CA-TP](#) [SMBF70A-TP](#) [SMBF70CA-TP](#) [SMBF75A-TP](#)
[SMBF75CA-TP](#) [SMBF78A-TP](#) [SMBF78CA-TP](#) [SMBF8.0A-TP](#) [SMBF8.0CA-TP](#) [SMBF8.5A-TP](#) [SMBF8.5CA-TP](#)
[SMBF80A-TP](#) [SMBF80CA-TP](#)