


Helping Customers Innovate, Improve & Grow



VX-501-0276-245M76

Nominal frequency (f0)
245.76 MHz

Performance Specifications

Frequency stabilities					
Parameter	Min	Typical	Max	Units	Condition
vs. operating temp. range (df/f@25°C)	-40		+40	ppm	-40...85°C
initial tolerance (df/f0)	-20		+20	ppm	@Vc = 1.65 V; 25 °C
vs. supply voltage change (df/f)	-1.5		+1.5	ppm	static; 3.3 V ±5 %
vs. load change (df/f)	-0.5		+0.5	ppm	static; Load +10 % -10 %
vs. aging / 10 years (df/f)	-10		+10	ppm	@ 40 °C
Additional information	APR >±10ppm incl.: 10 years aging, temp. stab. -40 ...+85°C, load and supply changes				

Frequency Tuning					
Parameter	Min	Typical	Max	Units	Condition
Absolute pulling range (APR) (df/f0)	10			ppm	ext. tuning voltage@0 to 3.3V
slope (pos./neg.)	positiv				

RF output					
Parameter	Min	Typical	Max	Units	Condition
Signal	LVPECL				
Load	45	50	55	Ohm	
Rise Time			1	ns	@20 to 80 %Vout
Fall Time			1	ns	@80 to 20 %Vout
Duty cycle	45		55	%	@50 %
V Low	1.36		1.68	V	
V High	2.16		2.42	V	

RF output					
Parameter	Min	Typical	Max	Units	Condition
Enable	Enable Function Pin2		Output Pin4		Output Pin5
	high		no data		no data
	open		data		compl. data
	low		data		compl. data

Supply voltage					
Parameter	Min	Typical	Max	Units	Condition
Supply voltage (Vs)	3.14	3.3	3.47	V	
Current consumption steady state			90	mA	@ Vsnom & 25 °C

Additional Parameters					
Parameter	Min	Typical	Max	Units	Condition
Phase Noise		-61		dBc/Hz	@10Hz
		-92		dBc/Hz	@100Hz
		-118		dBc/Hz	@1kHz
		-146		dBc/Hz	@10kHz
		-157		dBc/Hz	@100kHz
		-160		dBc/Hz	@1MHz
		-162		dBc/Hz	@10MHz
Jitter			0.05	psec (RMS)	@ 10kHz to 20MHz
Processing & Packing	handling&processing note				

Additional Environmental Conditions	
Parameter	Description
RoHS compliance	100% RoHS 6 compliant
Washable	non-washable device
Altitude (Low Pressure)	MIL-STD-810G Meth.500.5, Procedure II - 4h, 60000ft at -40°C operating
ESD HBM	JESD22-A114F Class 1B - 10x1000V
Phase Noise under Vibration	acc. Spec - @100Hz; 1KHz; 10kHz
Free fall	IEC60068-2-31 Method Ec - acc.Spec
Mechanical Shock	MIL-STD-202 Meth 213B Cond. E - 1000g 0,5ms 6 shocks in each direction
Vibration, Sine	MIL-STD-883 Meth 2007 Cond A - 20g 20-2000Hz 4x in each 3 axis 4min sweep time
Vibration, Sine (operating)	MIL-STD-202G Meth 201A - 10Hz-55Hz-10Hz 4x in 1 minute 2hrs@0,06inch(peak-peak)/axis in 3 orthogonal/continuous
Vibration, Sine(endurance level),	MIL-STD-202G Meth 201A - 10Hz-55Hz-10Hz in 1 minute 2hrs@0,06inch/axis(0,06inch oscillator displacement)
Abnormal use	IEC600068-2-2 - +260°C 24h
Dishwasher test	acc. Spec - 100 Zyklen 70...75°C
Moisture Sen. Level	JESD22-A113-B - only if > MSL 1
Solderability	J-STD-002C Cond. A, Trough hole device; Cond.B, SMD (correspond to MIL-STD-883 Meth 2003) - 255°C (diving Time 5 ±0,5sec.) Dip&Look with 8h damp pre-treatment: solder wetting >95%
Low temperature storage cum operation	MIL-STD-810D Meth.502.2 - Storage: -55°C 4h; Operational:-40°C 1h
High temp operating life(HTOL)	MIL-STD-202 Meth108A Cond C - 1000h @ 105°C power on
High temperature storage cum operation	MIL-STD-810D Meth.501.2 - 7 cycles / 35°C to 85°C


Additional Environmental Conditions

Parameter	Description
Humidity Bias (non operating)	MIL-STD-202G Meth 103B Cond.A - 40°C/95% RH 240h/drying period:1 to 2 hrs at room conditions
Low temp operating life(LTOL)	IEC 60068-2-1 Cond. Ae - 1000h @ -40°C power on
Reflow Simulation Test	J-STD-020D - Total 3x Lead free profile (for SMD)
Steady-state High temperature (operating)	acc.Spec - +85°C 168h
Steady-state Low temperature (operating)	acc.Spec - -40°C 96h/ON-OFF cycles;30 min ON&test-15min OFF/128 cycles ON-OFF
Temperature Cycling	JESD22-A104-D Cond.G - 1000cycles -40/+125°C; cycle time 30 min.

Absolute Maximum Ratings

Parameter	Min	Typical	Max	Units	Condition
Operable temperature range	-40		+85	°C	
Storage temperature range	-40		+95	°C	

Enclosure



all units in mm

Enclosure Info	
Parameter	Description
Type	G218C
Height	2.8 mm
Pin Connections	1: Vc (control voltage) 2: Enable 3: GND(Case) 4: RF-Output 5: RF-Output compl. 6: Vs (supply voltage)
Marking	VX-501-0276 245M760 * VI AYYWW * pin-1 marking
Package cover material	Metal
Package base material	FR4

Solder profile


Recommended reflow solder profile according IPC/JEDEC J-STD-020 (latest revision)

Additional Information:

This SMD oscillator has been designed for pick and place reflow soldering

SMD oscillators must be on the top side of the PCB during the reflow process.

Standard shipping method



Maßangaben in mm:

A, B und K Maße von Bauelement abhängig

Fertigungstoleranzen entsprechen der DIN IEC 286-3

Dimension in mm:

A, B und K are dependent upon component dimensions

production tolerance complying DIN IEC 286-3

All dimensions in millimeters unless otherwise stated

Reel Info						
Tape width W [mm]	Quantity per meter	Quantity per reel	P [mm]	A [mm]	B [mm]	K [mm]
24	83.3	1700	12	9.8	15	3.2

Notes: Unless otherwise stated all values are valid after warm-up time and refer to typical conditions for supply voltage, frequency control voltage, load, temperature (25°C).
Preliminary version: Subject to technical modification.

For Additional Information, Please Contact

USA:

Vectron International
267 Lowell Road, Suite 102
Hudson, NH 03051
Tel: 1.888.328.7661
Fax: 1.888.329.8328

Europe:

Vectron International
Landstrasse, D-74924
Neckarbischofsheim, Germany
Tel: +49 (0) 7268.801.100
Fax: +49 (0) 7268.801.282

Asia:

Vectron International
68 Yin Cheng Road(C), 22nd Floor
One LuJiaZui
Pudong, Shanghai 200120, China
Tel: +86 21 6194 6886
Fax: +86 21 6194 6699

Disclaimer

Vectron International reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Microchip:](#)

[VX-501-0276-245M76](#)