

MG 130 Kit Nozzle

Product no.: U-130-1055-ESDN



Benefits

- › Filter alarm and 3-step speed control
- › 100 - 240V power supply
- › Includes MG130 fume extraction unit 100 - 240 V / 50/60 HZ, H13 compact particle filter with wide band gas filter, pre-filter F7
- › Also includes 2 0F10 extraction arms and 1 ALFA nozzlesThe fume extraction unit MG 130 Kit Nozzle is easy to install and operate. It will be supplied complete with 2 pcs. flexible extraction arms 1 meter and 2 pcs. metal sloped nozzle 130 mm. The extraction arms fixed direct on the unit who will place close to the workbench.
- › Arms attach directly to unit - no mounting hardware needed
- › Applications: Hand soldering, heavy duty and general soldering, gluing, cleaning, filling, fine dust, MEK, cleanroom
- › Variable speed and alarm function for filter change
- › Maximum extraction rate 140 m3/h



Technical Data

Dimensions L x W x H (mm)	460 x 210 x 500
Dimensions L x W x H (inches)	18, 11 x 8, 26 x 19, 68
Weight (approx.) in kg	11
Voltage	110 - 240 V, 50/60 Hz
Power	100 W
Noise level (distance 1 m) dB(A)	< 52
Max. vacuum	---
Capacity m³/h	140
Pre-filter	---
Compact filter	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-2 workstations
RS232 interface (remote control)	---
USB port	---
WX-compatible	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[U-130-1055-ESDN](#)