

Q14 series

Ø14 mm panel mount LED indicators



DISTINCTIVE FEATURES

10 mm colored diffused epoxy lens or 10 mm water clear super bright LEDs

Prominent and flush bezel styles

(2.8 x 0.8) solder lug/faston terminals, pins or (200 mm long) wire terminations

Custom engraving available

Available in RGB



ENVIRONMENTAL SPECIFICATIONS

- IP67 sealing option (EN60529)
- Operating & Storage Temperature Range:
Rear plastic body: -30 °C to +65° C (-22 °F to +149 °F)
Rear epoxy body: -40 °C to +85° C (-40 °F to +185 °F)



GENERAL SPECIFICATIONS

- Max Reverse Voltage: 5 V
- Viewing Angle: 30–100° (dependant on model)
- Life Expectancy: 100,000 hours
- Torque: 75 cNm
- Maximum panel thickness 11 mm




MATERIALS

- Plated brass bezel finished in bright chrome, black or satin grey and moulded polycarbonate rear body



MOUNTING



The company reserves the right to change specifications without notice.

All LED characteristics are dependent upon environmental conditions. Therefore published data should be considered nominal and subject to variations.



Q14 series

Ø14 mm panel mount LED indicators

ELECTRICAL SPECIFICATIONS

STANDARD LED INTENSITY

LED COMPONENT SPECIFICATIONS			
	Prominent and Recessed	Flush	Forward Voltage
HE Red	80 mcd	10 mcd	2.0 V
Green	60 mcd	5 mcd	2.2 V
Yellow	50 mcd	4 mcd	2.1 V
Blue	540 mcd	100 mcd	3.3 V
White	1000 mcd	150 mcd	3.3 V
Orange	80 mcd	200 mcd	2.2 V
Bi-color (Typical) (Red/Green)	15/15 mcd	14/10 mcd	2.0V/2.2 V
Tri-color (Typical) (Red/Green/Yellow)	60/50/50mcd	15/10/30 mcd	2.0 V/2.2 V/2.1 V

Bi-color - The color is changed by reversing the polarity of the supply voltage.
Tri-color - The indicator has red and green LEDs, when both connected yellow is produced.

SUPER BRIGHT LED INTENSITY

LED COMPONENT SPECIFICATIONS			
	Prominent and Recessed	Flush	Forward Voltage
HE Red	17,000 mcd	2,000 mcd	2.2 V
Green	11,000 mcd	680 mcd	3.3 V
Yellow	4,000 mcd	350 mcd	2.0 V
Blue	2,500mcd	250 mcd	3.3 V
White	4,400 mcd	250 mcd	3.3 V
Orange	2,800 mcd	300 mcd	2.2 V

HYPER BRIGHT LED INTENSITY

LED COMPONENT SPECIFICATIONS			
	Prominent and Recessed	Flush	Forward Voltage
HE Red	2,800 mcd	800 mcd	2.1 V
Green	2,200 mcd	250 mcd	3.2 V
Yellow	1,300 mcd	250 mcd	2.0 V
Orange	850 mcd	200 mcd	2.1 V

RGB LED INTENSITY

ITEM	SYMBOL	CONDITION	TYP.
DC Forward Voltage	V _F (R)	IF=20 mA	2.1
	V _F (B/G)	IF=20 mA	3.1
Luminous Intensity	I _v (Red)		220 mdc
	I _v (Green)		500 mdc
	I _v (Blue)		100 mdc

Voltage	Operating Voltage	Operating Current
	(Min to Max)	(Typical All Types)
02 (No Resistor)	1.8 to 3.3 VDC	20 mA max
6 VDC	5.4 to 6.6 VDC	20 mA
12 VDC	10.8 to 13.2 VDC	20 mA
24 VDC	21.6 to 26.4 VDC	20 mA
28 VDC	25.2 to 30.8 VDC	20 mA
110 VAC	99 to 121 VAC	6 mA
220 VAC	207 to 235 VAC	3 mA


* Customer to supply resistor for desired operating current.

ADDITIONNAL INFORMATION ON LED COMPONENTS

- The operating voltage must not be exceeded by more that 10% as this will result in reduced life expectancy
- Luminous intensity is measured at 20 mA on a discrete led unless otherwise stated.
- Luminous intensities and color shades of white LEDs may vary within a batch.
- Luminous intensity will be reduced with lower operating current.

CONNECTIONS

REAR EPOXY WIRES FOR RGB OPTION



Q14 series

Ø14 mm panel mount LED indicators



BUILD YOUR PART NUMBER

Q

SERIES

14

MOUNTING HOLE

Ø14mm

P

BEZEL STYLE

Prominent

R

Recessed

F

Flush

1

Solder Lug/
Fastons (2.8 x 0.8)

2

Pins

3

Wires

4

Rear epoxy Pins

5

Rear epoxy Wires

6

Short body Pins

7

Short body Wires

AR

ANODIZED
FLUSH

Red

AG

Green

AY

Yellow

AB

Blue

AN

Black

C

OTHERS

Bright Chrome

B

Black

G

Satin Grey

XX

TYPE OF ILLUMINATION

Fixed Light

KK

Flashing Light
(12V – 28VDC)

YY

Bi-color

ZZ

Tri-color

R

Red

G

Green

Y

Yellow

B

Blue

W

White

O

Orange

HR

Hyper Bright
Red

HG

LED COLOR

Hyper Bright
Green

HY

Hyper Bright
Yellow

HO

Hyper Bright
Orange

SR

Super Bright
Red

SG

Super Bright
Green

SY

Super Bright
Yellow

SB

Super Bright
Blue

SW

Super Bright
White

RG

Red/Green

RY

Red/Yellow

GY

Green/Yellow

RYG

Red/Yellow/
Green

RGB

Red/Green/
Blue*

02

VOLTAGE

no resistor

06

6 VDC

12

12 VDC

12A

12 VAC/DC

24

24 VDC

24A

24 VAC/DC

28

28 VDC

28A

28 VAC/DC

110

110 VAC

220

220 VAC

(Blank)

SEALING

Unsealed

E

IP67

(Blank)

Common cathode

-CA

Common anode

1

* Terminals option 5 and
common anode only

* Terminals option 5 and common anode only



ABOUT THIS SERIES



Notice: please note that not all combinations of above numbers are available.

- Gold faston terminal denotes anode (+), silver terminal denotes cathode (-)
- Standard wire length is 200 mm, 22 AWG UL1061, red wire denotes anode (+), black wire denotes cathode (-) for other wire lengths consult APEM
- For LEDs with alternative voltages and multi-voltage options consult APEM
- 110 VAC and 220 VAC, only available with terminal options 1, 3 and 5
- Bi-color leds, by connecting the gold faston (+) one color is produced, by reversing the supply voltage another color is produced – bi-colors are available up to 28 VDC

- Take care when soldering to the faston terminals (recommended solder temperature 300 °C - 3 sec)
- Body options 2 and 6 are only available without integral resistor (02).
- The Tri-color LED has red and green LEDs when both are connected yellow is produced
- Standard tri-color faston terminals are two anodes (+) and one cathode (-)
- Tri-color wires are one red (+) and one green (+) anode and one black (-) cathode
- Tri-color pins are center (-) cathode, shortest (+) anode pin green, longest (+) anode pin red
- We recommend using Hyperbright or Superbright LEDs for use at 110 VAC and 220 VAC


Q14 series

Ø14 mm panel mount LED indicators

PROMINENT BEZEL




WIRES




REAR EPOXY WIRES




SHORT BODY WIRES




SOLDER LUG/FASTON




PINS



REAR EPOXY PINS




SHORT BODY PINS




FLUSH BEZEL




WIRES




REAR EPOXY WIRES




SHORT BODY WIRES




SOLDER LUG/FASTON




PINS



REAR EPOXY PINS



SHORT BODY PINS



Q14 series

Ø14 mm panel mount LED indicators


RECESSED BEZEL



WIRES




REAR EPOXY WIRES




SHORT BODY WIRES



SOLDER LUG/FASTON



PINS



REAR EPOXY PINS



SHORT BODY PINS



Q14 series

Ø14 mm panel mount LED indicators



CUSTOM ENGRAVING

Some common codes are listed above, for your custom requirements please contact APEM.
Unless specified standard engraving with white infill will be supplied.
Suffix the part number with legend code :



High beam
-0AJ



Low beam
-097



Rear fog
-027



Front fog
-026



Windscreen
wiper
-021



Windscreen
washer
-022



Ventilator
fan
-023



Turn Signal
-0AH



Side lights
-098



Horn
-041



Hazard
warning
-013



Heating
-018



Brake test
-0BU



Arrow
-0K6



Battery
-0AG



Oil can
-0GP



Windscreen
heating
-020



ABS
-086



Engine coil
-0EL



Seat belt
-0SB



USB
connection
-0UB



Steam
-0ST



ECU
-0EU



Side step
-0AD



Air con
-012



Engine
-040



Boot/Trunk
Release
-0BR



CABLE LENGTH AND CONNECTOR



For custom cable length and connectors contact APEM.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[Q14F1ABXXB12E](#) [Q14F1ABXXB220E](#) [Q14F1AGXXHG220E](#) [Q14P6BXXG02E](#) [Q14P6BXXR02E](#) [Q14P6BXXY02E](#)
[Q14P6CXXY02E](#) [Q14F5ABXXB24E](#) [Q14F5AGXXHG220E](#) [Q14F5ARXXHR220E](#) [Q14F1AYXXHY220E](#)
[Q14F5ABXXB12E](#) [Q14F5ABXXB220E](#) [Q14P3BZZRYG12E](#) [Q14P1BXXSB220E](#)