

MF series

T1 3/4 Midget flange based LED's • single or multichip LED illumination



DISTINCTIVE FEATURES

- T1 3/4 Midget flange based LED for bulb replacement
- Operating & Storage Temperature Range: -20 °C to +70 °C (-4 °F to +158 °F)
- 12 VDC to 28 VAC/DC 14 mA, mcd range from 490 to 2,070 dependent on version



MATERIALS

- Body : Polycarbonate
- Base : Nickel plated brass



BUILD YOUR PART NUMBER



For other voltage options please contact APEM

LUMINOUS INTENSITY

	Voltage
Color	12 V, 24 V & 28 V
R - Red	1,750 mcd
G - Green	1,610 mcd
Y - Yellow	630 mcd
B - Blue	490 mcd
W - White	2,070 mcd

The company reserves the right to change specifications without notice.

MF series

T1 3/4 Midget flange based LED's •
single or multichip LED illumination



BUILD YOUR PART NUMBER

MF MULTI CHIP



SERIES	TYPE	COLOR	VOLTAGE & CURRENT AC/DC	OPTIONS
MF	M Multi Chip	R Red G Green Y Yellow	12 12 V - 30 mA 24 24 V - 14 mA 28 28 V - 14 mA	A AC/DC version

For other voltage options please contact APEM

LUMINOUS INTENSITY

	Voltage
Color	12 V, 24 V & 28 V
R - Red	40 mcd
G - Green	35 mcd
Y - Yellow	45 mcd

MF - SINGLE CHIP RED



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[MFSW24](#) [MFSB12](#) [MFSB24](#) [MFSG12](#) [MFSW28](#) [MFSR24](#) [MFSR12](#) [MFSB28](#) [MFSG28](#) [MFSR28](#) [MFSW12](#)
[MFSY12](#)