

M series

Proportional resistive fingertip controllers •
potentiometer technology



DISTINCTIVE FEATURES

One, two or three axis

Analog output

Low profile mounting depth

Friction centering option

Low profile design with multiple handle options



ENVIRONMENTAL SPECIFICATIONS

- Operating Temperature: -25 °C to +70 °C (-13 °F to +158 °F)
- Storage Temperature: -40 °C to +70 °C (-40 °F to +158 °F)



MECHANICAL SPECIFICATIONS (X & Y AXIS)

- Operating Force: 1.3 N (0.29 lbf)
- Maximum Vertical Load: 100 N (22.5 lbf)
- Maximum Horizontal Load: 100 N (22.5 lbf)
- Mechanical Angle of Movement: 56°
- Expected Life: See potentiometer options
- Mass/weight: Varies
- Lever Action (centering): Spring or friction



MECHANICAL SPECIFICATIONS (Z AXIS)

- Operating Torque: 0.040 Nm (0.35 lbf in)
- Break out Torque: 0.022 Nm (0.19 lbf in)
- Maximum Allowable Torque: 0.049 Nm (0.43 lbf in)
- Mechanical Angle of Movement: 90°
- Lever Action (centering): Spring

The company reserves the right to change specifications without notice.



M series

Proportional resistive fingertip controllers • potentiometer technology



MATERIALS


- Body: Nylon
- Actuator: Nylon



WIRING DIAGRAM

DEFAULT WIRE COLOR CODE *		
COLOR	FUNCTION	AWG
2 OR 3 AXIS JOYSTICK WITH 1 PUSHBUTTON: OPTIONS 5, E, G, H, 9, N		
Orange Orange	Switch 1 Switch Common	28
3 AXIS JOYSTICK WITH 2 PUSHBUTTONS: OPTION Q**		
Orange Brown Green	Switch 1 Switch 2 Switch Common	28
Z AXIS IN A 3 AXIS JOYSTICK: OPTION 8, 9, M, N, Q		
Red White Blue	Supply Signal Return	28

* Wires for the Z axis and the pushbuttons are 292 mm (11.5in) and stripped
 ** Handle Q pushbuttons are shown in the following drawing



OUTPUTS


POTENTIOMETER OPTIONS

POTENTIOMETER	P	M	R
Electrical Element	CONDUCTIVE PLASTIC		
Track Resistance	5K		
Linearity	±1.0%	±5.0%	±1.0%
Track Operating Angle	220°	56°	50°
CRV	±1.5%	±1.5%	±1.0%
Power Dissipation	0.25W@40 °C	0.5W@70 °C	1 W
Rotational Life	1,000,000	1,000,000	10,000,000



MOUNTING

INSTALLATION



FRONT MOUNTING BEZEL (FM)



C = Split Bezel
 Cutout dimensions = 39.70 mm (1.562 in)



L = Rubber Boot
 Cutout dimensions = 39.70 mm (1.562 in)

REAR MOUNTING BEZEL (RM)



F = Square Bezel
 Cutout dimensions = 30.15 mm (1.187 in)

MOUNTING ACCESSORIES
 Standard hardware includes:
 C=Ring, cup and 4 black Phl screws 2-56x 1/2 in
 L=Ring and 4 black Phl screws 2-56x 1/2 in
 F=Square bezel, 4 screws 2-56x1/2 in Phl and 4 screws 2-56x 1/2 in Phl





BUILD YOUR PART NUMBER

SERIES	MODEL	MOUNTING BEZEL	CENTERING	HANDLE	OUTPUT OPTIONS POTENTIOMETERS
M	1	C Split Bezel	0 Spring Centering	0 Tapered Convex	P 5KΩ, 220°
	2	F Square Bezel	6 Torque Set (Friction)	1 Concave Tip	M 5KΩ, 56°
	3	L Rubber Boot Kit		2 Flat Tip	R 5KΩ, 50°
	4			3 Concave Tip - Long	
				5 Pushbutton	
				6 Straight Tip - Short	
				8 3 Axis	
				9 3 Axis with pushbutton	
				A Straight Tip - Mid	
				B Straight Tip - Long	
				E Pushbutton	
				G Pushbutton	
				H Pushbutton	
				M 3 Axis / No Pushbutton	
				N 3 Axis with 1 Pushbutton	
				Q 3 Axis with 2 Pushbuttons	

M series

Proportional resistive fingertip controllers • potentiometer technology

2 AXIS - OPTION A HANDLE




Mechanical dimensions represent a joystick with the largest potentiometer option. Potentiometer size will vary according to selected option




HANDLE OPTIONS


TWO AXIS




TWO AXIS WITH PUSHBUTTONS



THREE AXIS




8




M


THREE AXIS WITH PUSHBUTTONS



9



N



O

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[M31C0M1P](#)