




INTERCONNECTS

SERIES 860 & 861 • 1mm GRID SURFACE MOUNT GULL WING HEADERS & SOCKETS • SINGLE ROW STRIPS




Coplanarity .005". For pin counts >20 positions, consult Technical Support.

FIG. 1




Coplanarity .005". For pin counts >20 positions, consult Technical Support.

FIG. 2



- Series 860 surface mount gull wing headers have .011" dia. pluggable pins for Surface Mount soldering to the P.C.B. (MM #3039). See page 208 for details
- Series 861 surface mount gull wing sockets uses MM #0439 receptacles that accept pin diameters from .008"-.013". See page 156 for details
- Receptacles use Hi-Rel, 3-finger BeCu #04 contact rated at 2 amps. See page 250 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION






FIG. 1	Series 860...002 Single Row Surface Mount Header	
	860-10-0-30-002000	
	Specify number of pins	03-26
<div>RoHS-2 2011/65/EU</div> <div>XX=Plating Code See Below</div> <div>For Electrical, Mechanical & Environmental Data, See page 264</div>		
SPECIFY PLATING CODE XX=		
Pin Plating 		
	10 	
	10 μ" Au	

FIG. 2	Series 861...002 Single Row Surface Mount Socket	
	861-13-0-30-002000	
	Specify number of pins	03-26
<div>RoHS-2 2011/65/EU</div> <div>XX=Plating Code See Below</div> <div>For Electrical, Mechanical & Environmental Data, See page 264</div>		
SPECIFY PLATING CODE XX=		
Sleeve (Pin) 		
Contact (Clip) 		
	13 	
	10 μ" Au	
	30 μ" Au	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[861-13-004-30-002000](#) [861-13-018-30-002000](#) [861-13-010-30-002000](#) [861-13-003-30-002000](#) [861-13-017-30-002000](#) [861-13-012-30-002000](#) [860-10-026-30-002000](#) [861-13-019-30-002000](#) [860-10-005-30-002000](#) [861-13-007-30-002000](#) [861-13-014-30-002000](#) [860-10-006-30-002000](#) [860-10-010-30-002000](#) [860-10-017-30-002000](#) [861-13-006-30-002000](#) [860-10-008-30-002000](#) [860-10-018-30-002000](#) [860-10-009-30-002000](#)