

IR series

Sealed pushbutton switches • bushing Ø 16 mm •
momentary • standard version



DISTINCTIVE FEATURES

- Screw version up to 4 A
- Tactile feedback
- Sealed to IP67
- Illuminated or non-illuminated
- Flat round actuator for optional marking



ENVIRONMENTAL SPECIFICATIONS

- Front panel sealing : IP67 according to IEC 60529
- Shock resistance : 100 g according to IEC 512-4, test 6c
- Vibration resistance : 10-500Hz - 10 g according to IEC 512-4, test 6d
- Salt spray : IEC 512-6, test 11f
- Operating temperature : -40°C to +85°C (-40 °F to +185 °F)



ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - Gold plated contacts: Code 4 : 200 mA 48 VDC, 500,000 cycles
Code 7 : 5 A 28 VDC, 70,000 cycles
 - Silver contacts (code 2) - screw terminals : 4 A 48 VDC, 500,000 cycles
- Initial contact resistance : 100 mΩ max.
- Insulation resistance : 1 GΩ min. at 500 VDC
- Dielectric strength : 1,500 Vrms



LED COMPONENT SPECIFICATIONS

LED color	Forward current	Typ. forward voltage	Max. forward voltage
Super red (0S)	20 mA	2.1 V	2.3 V
Yellow (0Y)	20 mA	2.1 V	2.3 V
Green (0G)	20 mA	2.1 V	2.3 V
Blue (0B)	20 mA	3.2 V	3.8 V
White (0W)	20 mA	3.35 V	4.25 V
Red/Green (SG)	20 mA	Red: 1.95 V / green: 2.1 V	2.5 V
Yellow/green (YG)	20 mA	Yellow: 2 V / green: 2.1 V	2.5 V

A resistor must be series-connected by the user.

$$\text{Resistor value} = \frac{\text{supply voltage} - \text{LED forward voltage}}{\text{LED forward current}}$$

On flying lead versions, the LED resistor can be integrated by APEM on request.

The company reserves the right to change specifications without notice.

IR series

Sealed pushbutton switches • bushing Ø 16 mm • momentary • standard version



GENERAL SPECIFICATIONS

- Panel thickness : 8 mm (.314) max.
- Total travel : 1.6 mm (.062) ± 0.3 mm
- Typical operating force : 4 N ± 2 N
- Low level or mechanical life : 1,000,000 cycles
- Torque : 0.8 Nm max. applied to nut
- Soldering : 320 °C (608 °F) max. for 3 sec.



MATERIALS


- Case : thermoplastic UL94-V0
- Actuator : polyamide 6/6
- Bushing/bezel : polyamide 6/6
- Contacts : 4 and 7 : silver, gold plated
2 : silver (screw terminals)
- Multi-wire lead AWG20, section 0.6 mm²
- LED wire : AWG26, section 0.12 mm²
- Lens : polycarbonate
- Terminal seal : epoxy

APEM products may be recycled at end-of-life for the re-claiming of valuable metal components.




MOUNTING

PANEL CUT-OUT



MATRIX MOUNTING




TERMINALS

ILLUMINATED MODELS




NON-ILLUMINATED MODELS




ELECTRICAL FUNCTIONS

ILLUMINATED MODELS



Function 3 (NO)


NON-ILLUMINATED MODELS



Function 3 (NO)



BUILD YOUR PART NUMBER



ABOUT THIS SERIES


On the following pages, you will find successively basic part numbers of switches and options in the same order as in above chart.

- Notice** : please note that not all combinations of above numbers are available. Refer to the following pages for further information.
- A sealing boot** is available to protect the switches against frost and sand (P/N U7125). Round models only.
See "Sealing Boot" section of website.
- Mounting accessories** : Standard hardware supplied : 1 hex nut 19 mm (.748) across flats and 1 flat seal. Hex nut P/N U6715.

IR series


Sealed pushbutton switches • bushing Ø 16 mm • momentary • standard version

ROUND - ILLUMINATED SOLDER LUG TERMINALS




Also available with straight PC terminals : **IR•3P**.
LED color is indicated by the bottom of the switch.

ROUND - ILLUMINATED FLYING LEAD TERMINALS




Wire colors : black : NO contact, red : LED anode (+), blue : LED cathode (-)

ROUND - NON-ILLUMINATED SOLDER LUG TERMINALS




Also available with straight PC terminals : **IR•3P**
and quick-connect terminals : **IR•3Z**.


ROUND - NON-ILLUMINATED FLYING LEAD TERMINALS




→ FLAT




→ FLAT



→ FLAT



→ FLAT



Sealed pushbutton switches • bushing Ø 16 mm •
momentary • standard version

ROUND - NON-ILLUMINATED SCREW TERMINALS



Curved actuator

IRR3V



Normally Open

Flat actuator

IRP3V



Normally Open

SQUARE - ILLUMINATED SOLDER LUG TERMINALS



IRC3S



Normally Open

Also available with straight PC terminals : **IRC3P**.
LED color is indicated by the bottom of the switch.

SQUARE - ILLUMINATED FLYING LEAD TERMINALS



IRC3F



Normally Open

Wire colors : black : NO contact, red : LED anode (+), blue : LED cathode (-)

SQUARE - NON-ILLUMINATED SOLDER LUG TERMINALS




IRC3S




Normally Open

Also available with straight PC terminals : **IRC3P**
and quick-connect terminals : **IRC3Z**.


→ FLAT




→ FLAT



→ FLAT



→ FLAT



IR series

Sealed pushbutton switches • bushing Ø 16 mm • momentary • standard version

SQUARE - NON-ILLUMINATED FLYING LEAD TERMINALS




IRC3F



Normally Open

→ FLAT



SQUARE - NON-ILLUMINATED SCREW TERMINALS




IRC3V



Normally Open

→ FLAT



CONTACTS

BASIC P/N

- 4 Silver, gold plated (200 mA 48 VDC)
- 7 Silver, gold plated (5 A 28 VDC)
- 2 Silver (screw terminals only)

ACTUATOR COLORS


BASIC P/N

- 1 Blue
- B Dark blue
- 2 Black
- 3 Green
- 4 Grey
- 5 Yellow
- 6 Red
- 7 White
- 8 Bright chrome
- 9 Orange
- A Satin chrome

IR series


Sealed pushbutton switches • bushing Ø 16 mm •
momentary • standard version

BUSHING AND BEZEL




- 2 Black (standard)
- 7 White
- 0 Transparent (round bezel only)

ILLUMINATION



- L Central lens
- B Bezel (round only)

LED COLORS



- 0S Super red
- 0Y Yellow
- 0G Green
- 0B Blue
- 0W White
- SG Red/green
- YG Yellow/green

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apem:

[IRC8Z222L0S](#) [IRR3F422](#) [IRR3F462](#) [IRR3F462L0B](#) [IRR3V212](#) [IRR3V262](#) [IRR8Z222](#) [IRC7Z222L0S](#)
[IRC7Z262L0S](#) [IRP3F422L0S](#) [IRP7Z262](#) [IRR1S422L0S](#) [IRR3F422000](#) [IRR3F462000](#) [IRR3F4B2](#) [IRR3S422000](#)
[IRR3S422L0S](#) [IRR3V222000](#) [IRR3V262000](#) [IRR7Z232L0G](#) [IRR8Z222000](#) [IRR8Z222L0S](#) [IRR3S422](#) [IRP3F422](#)
[IRR3F472](#) [IRP3F432](#) [IRR3F452](#) [IRR3F492](#) [IRR3S462](#) [IRR3S412](#) [IRR3F412](#) [IRC3S472](#) [IRR3S452](#) [IRR3S432](#)
[IRC3S452](#) [IRC3S412](#) [IRC3F432](#) [IRP3S462](#) [IRR3V232](#) [IRC3S472L0W](#) [IRR3S422L0B](#) [IRC3V272](#) [IRP3F462](#)
[IRR3Z462](#) [IRP3F420B0B](#) [IRR3V212000](#) [IRR3S462L0S](#) [IRR3S730B0G](#) [IRP3F492](#) [IRR3F422L0G](#) [IRR3S452L0Y](#)
[IRC3F412](#) [IRR3S432L0G](#) [IRC3S462L0S](#) [IRR3F462L0S](#) [IRP3S470B0S](#) [IRP3S422000](#) [IRR3S422L0G](#) [IRR3S492](#)
[IRC3S422L0S](#) [IRP3S460B0S](#) [IRR3S472](#) [IRC3S412L0B](#) [IRR3F422L0S](#) [IRR3F432L0G](#) [IRR3S422L0Y](#) [IRC3V232](#)
[IRP3S422L0S](#) [IRP3S420B0S](#) [IRP3V232](#) [IRR3F452L0Y](#) [IRR3S412L0B](#) [IRC3S432L0G](#) [IRC8Z222L0G](#) [IRR7Z232](#)
[IRC7Z222](#) [IRP7Z262000](#) [IRR1F422L0B](#) [IRR7Z222000](#) [IRR7Z262L0S](#)